

ABB BALDOR RELIANCE III

Customer information packet

IDVSM3665T-5

5HP, 1750RPM, 3PH, 60HZ, 184TC, 0640M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	184TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	5.200 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	90.2 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Encoder/Feedback Device
Front Shaft Indicator	No Key Or Flat
Heater Indicator	No Heater
High Voltage Full Load Amps	5.2 a
Insulation Class	F
Inverter Code	Inverter Duty

Part Detail

Revision	G
Type	AC
Mech. spec.	06H926
Base	
Status	PRD/A
Elec. spec.	06WGW357
Layout	06LYH926
Eff. date	06-18-2026
CD Diagram	CD0006
Poles	04
Leads	3#16
Proprietary	False
Created date	07-28-2016

KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	6000 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0640M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	20.23 IN
Power Factor	80
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.00
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1750 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4615L									
CAT NO	IDVSM3665T-5								
SPEC.	06H926W357G1						ENCL	TEFC	
FRAME	184TC		HP	5					
VOLTS	575								
MAG CUR	2.7			FLA	5.2				
RPM	1750		RPM MAX	6000					
HZ	60	PH	3	CLASS	F				
SER.F.	1.00		SL HZ	1.7					
NEMA-NOM-EFF	90.2		WK2	0.37					
RATING	40C AMB-CONT								
DE BRG	6206	ODE BRG	6206						
CC	010A	SN							
	1000:1 CT/VT								
	-								

NP VOLTS	575					WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)
NP AMPS	5.2	Base Volt	575	R1	2.040	X1 4.350
HP	5	NL AMPS	2.70	R2	1.650	X2 3.400
BASE SPEED	1755	Slip (HZ)	1.50			XM 123.000
PHASE/HZ	3/60	WK ² (lb-ft ²)	0.372			

Rated Full Load Data

	RPM	HP	Torque	Volts	Freq-Hz	Amps
Base Speed	1755	5.0	15.0	575	60	5.1
Max Speed	2632	5.0	10.0	575	90	4.7
CT Min Speed	1.755	0.005	15.0	0.58	0.06	5.1

Load Performance at Base Speed

	RPM	HP	Torque	Volts	Freq-Hz	Amps
No Load	1799	0.0	0.0	575	60	2.7
1/4	1789	1.3	3.8	575	60	2.9
1/2	1778	2.5	7.5	575	60	3.4
3/4	1767	3.8	11.3	575	60	4.2
Full Load	1755	5.0	15.0	575	60	5.1
O/L	1705	10.0	30.9	575	60	9.7

Blower Data

Volts	Ph/HZ	FL Amps	LR Amps	Frame	CFM

Remarks: Calculated Data

BALDOR • RELIANCE

DR BY USBRRAN1
CK BY CD
APP BY USBRRAN1
DATE 11/1/2024
**A-C MOTOR
PERFORMANCE
CURVES**
06WGW357

Record: 58461


NP VOLTS 575
NP AMPS 5.2
HP 5
BASE SPEED 1755
PHASE/HZ 3/60

Base Volt 575
NL AMPS 2.70
Slip (HZ) 1.50
WK² (lb-ft²) 0.372

WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)

R1	2.040	X1	4.350
R2	1.650	X2	3.400
		XM	123.000

Variable Speed AC Motor Curves



Calculated Data

Data Valid For Nameplate Speed Range only


BALDOR • RELIANCE

DR BY USBRRAN1
CK BY CD
APP BY USBRRAN1
DATE 11/1/2024
**A-C MOTOR
PERFORMANCE
CURVES**
06WGW357

Record: 58461

NP VOLTS	575	0	0	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)			
NP AMPS	5.2	Base Volt	575	R1	2.040	X1	4.350
HP	5	NL AMPS	2.70	R2	1.650	X2	3.400
BASE SPEED	1755	Slip (HZ)	1.50			XM	123.000
PHASE/HZ	3/60	WK2 (lb-ft2)	0.372				

Vector PWM Inverter Duty
Variable Speed AC Motor Curves



Calculated Data

Data Valid For Nameplate Speed Range only

BALDOR • RELIANCE

DR BY USBRRAN1

CK BY CD


APP BY USBRRAN1

DATE 11/1/2024



**A-C MOTOR
PERFORMANCE
CURVES**

06WGW357

Record: 58461



CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10:24:49 02/19/2019

BY: ENBRIRO

MTL: -


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1