

# **ABB BALDOR RELIANCE III**



## **Customer information packet** IDCRPM28604

60HP, 1800, 460V, FL2873, TEFC, F3

**Specifications**

<b>Enclosure</b>	TEFC
<b>Frame</b>	FL2873Z
<b>Frame Material</b>	Exposed Laminations
<b>Frequency</b>	60.00 Hz
<b>Output @ Frequency</b>	60.000 HP @ 60 HZ
<b>Phase</b>	3
<b>Synchronous Speed @ Frequency</b>	1800 RPM @ 60 HZ
<b>Voltage @ Frequency</b>	460.0 V @ 60 HZ
<b>Agency Approvals</b>	CCSA US NEMA PREMIUM
<b>Auxiliary Box</b>	NO AUXILLARY BOX
<b>Base Indicator</b>	Rigid
<b>Bearing Grease Type</b>	Polyrex EM (-20F +300F)
<b>Constant Torque Speed Range</b>	1-60
<b>Current @ Voltage</b>	60.000 A @ 460.0 V
<b>Duty Rating</b>	CONT
<b>Feedback Device</b>	NO FEEDBACK
<b>Frame Prefix</b>	FL
<b>Heater Indicator</b>	No Heater
<b>High Voltage Full Load Amps</b>	60.0 a
<b>Insulation Class</b>	H
<b>KVA Code</b>	G
<b>Motor Standards</b>	NEMA
<b>Mounting Arrangement</b>	F3
<b>Overall Length</b>	32.34 IN
<b>Product Family</b>	General Industrial
<b>Pulley End Bearing Type</b>	Ball
<b>Pulley Face Code</b>	Standard
<b>Service Factor</b>	1.15
<b>Shaft Diameter</b>	2.624 IN
<b>Shaft Ground Indicator</b>	Shaft Grounding
<b>Shaft Rotation</b>	Reversible

**Part Detail**

<b>Revision</b>	C
<b>Type</b>	AC
<b>Mech. spec.</b>	
<b>Base</b>	
<b>Status</b>	PRD/A
<b>Elec. spec.</b>	LS6573A
<b>Layout</b>	617512-073
<b>Eff. date</b>	09-09-2022
<b>CD Diagram</b>	422927-001
<b>Poles</b>	04
<b>Leads</b>	
<b>Proprietary</b>	False
<b>Created date</b>	10-27-2021

<b>Speed</b>	1800 rpm
<b>Starting Method</b>	Full Voltage
<b>Thermal Device - Bearing</b>	None
<b>Thermal Device - Winding</b>	Normally Closed Thermostat

**Nameplate**

**000613007QF**

	<b>DUTY</b>	<b>HP</b>	<b>RPM</b>	<b>AMPS</b>	<b>VOLTS</b>	<b>HZ</b>					
	CONT	60	1800	60	460	60					
<b>CAT.NO.</b>	IDCRPM28604		<b>SPEC. NO.</b>		F28-A000-0365						
<b>SER.NO.</b>			<b>FRAME SIZE</b>		FL2873Z	<b>TYPE PSM</b>					
<b>AMB.</b>	40	<b>S.F.</b>	1.15	<b>ENCL.</b>	TEFC	<b>PH</b>	3	<b>DESIGN</b>	B	<b>CODE</b>	G
<b>NEMA NOM. EFF</b>	97	<b>GUARANTEED EFFICIENCY</b>			96.4	<b>POWER FACTOR</b>		98.6	<b>INSUL. CLASS</b>		H
<b>D.E. BRG.</b>	75BC02J30X		<b>O.D.E. BRG.</b>		55BC02J30X						
<b>VPWM INVERTER DUTY @1.0SF</b>	<b>CHP HZ</b>	60-90		<b>CT HZ</b>	1-60		<b>VT HZ</b>	0-60			
	IP54 XT										

---

000692000VY

---

**MEAS OPEN CIRCUIT VOLTAGE**

---

IS  VOLTS AT  RPM.

---

S.O.	FRAME	HP	TYPE	PHASE	HERTZ	RPM
--	FL2873	60	PSM	3	60	1800
VOLTS	AMPS	DUTY	AMB <sup>o</sup> C	INSUL	S.F.	NEMA DESIGN
460	58.8	CONT	40	H	1.15	B
CODE LETTER	ENCL	ROTOR INERTIA (lb-ft <sup>2</sup> )	STATOR RES.@ 25 <sup>o</sup> C OHMS (BETWEEN LINES)			
G	TEFC	7.56	.1169		TYPICAL DATA	

PERFORMANCE

LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY
NO LOAD	0	25.1	1800	3.70	N/A
1/4	15.0	20.0	1800	74.6	94.0
2/4	30.0	30.6	1800	95.9	96.2
3/4	45.0	44.2	1800	98.4	96.8
4/4	60.0	58.8	1800	98.6	97.0
5/4	75.0	73.6	1800	98.1	97.0

SPEED TORQUE

	RPM	TORQUE (% FULL LOAD)	TORQUE (lb-ft)	AMPERES
LOCKED ROTOR	0	159	278.5	439.8
PULL OUT	1800	247	432.6	187.8
FULL LOAD	1800	100	175.2	58.8

THIS IS A PERMANENT MAGNET MOTOR

GENERATED OPEN CIRCUIT LINE-LINE VOLTAGE at 25<sup>o</sup>C = 21.1 VOLTS PER 100 RPM

REMARKS:




DR. BY CAD  
 CK. BY RFM  
 APP. BY RFM  
 DATE 05/25/2016

**LSPM MOTOR  
 PERFORMANCE LS6573A  
 DATA**

ISSUE DATE 05/25/2016

S.O.	--	HERTZ	60	AMB <sup>o</sup> C	40	CODE LETTER	G
FRAME	FL2873	RPM	1800	INSUL	H	WK <sup>2</sup> (lb-ft <sup>2</sup> )	7.56
HP	60	VOLTS	460	S.F.	1.15	NEMA DESIGN	B
TYPE	PSM	AMPS	58.8	ENCL	TEFC	STATOR RES. @ 25 <sup>o</sup> C	.1169
PHASE	3	DUTY	CONT			OHMS (BETWEEN LINES)	

### Amps & Torque vs. RPM During Acceleration



TYPICAL DATA



DR. BY	CAD
CK. BY	RFM
APP. BY	RFM
DATE	05/25/2016

**LSPM MOTOR  
PERFORMANCE  
CURVES**


LS6573A

ISSUE DATE

05/25/2016

S.O.	--	HERTZ	60	AMB <sup>o</sup> C	40	CODE LETTER	G
FRAME	FL2873	RPM	1800	INSUL	H	WK <sup>2</sup> (lb-ft <sup>2</sup> )	7.56
HP	60	VOLTS	460	S.F.	1.15	NEMA DESIGN	B
TYPE	PSM	AMPS	58.8	ENCL	TEFC	STATOR RES. @ 25 <sup>o</sup> C	.1169
PHASE	3	DUTY	CONT			OHMS (BETWEEN LINES)	

Performance Data vs. HP  
At Synchronous Speed



TYPICAL DATA




DR. BY CAD  
 CK. BY RFM  
 APP. BY RFM  
 DATE 05/25/2016

**LSPM MOTOR  
 PERFORMANCE  
 CURVES**

LS6573A


ISSUE DATE

05/25/2016



**INDUSTRIAL ALTERNATING CURRENT MOTORS**  
**RPM AC**

STEEL, CAST IRON, MILL AND TERMINAL BOARD CONDUIT BOX DIMENSIONS  
NEMA FRAMES RL210 thru RL280 and IEC FRAMES RDL132 thru RDL180  
NEMA FRAMES FL180 thru FL280 and IEC FRAMES FDL112 thru FDL180



FRAME	TYPE	TERMINAL STRIP	AMPS	C/BOX	Y	TA	T	AA
FL180	STEEL	N	40	706320003A	5.00	1.62	3.00	1.12
FL180	STEEL	N	75	706320003A	6.12	2.38	4.38	1.75/2.00
FL180	CAST IRON	N	208	706320007A	6.82	2.00	7.00	2.50/2.00
FL180 & FDL11	CAST IRON	Y/N	40	706320004B	5.75	2.38	4.38	1.50/1.75
FL180 & FDL11	MILL	Y	100	706310028A	7.75	2.30	4.40	PC29/PG16
FL210 & RL210	STEEL	N	61	0754520009B	6.34	2.00	4.12	1.75
FL210 & RL210	STEEL	N	121	0754520009B	7.69	2.38	5.25	1.94
FL210 & RL210	STEEL	N	336	706320016A	9.00	4.12	8.42	4.89
FL210 & RL210	CAST IRON	N	110	075460062B	7.25	2.50	5.25	1.5 TAP
FL210 & RL210	MILL	Y	100	706310229A	7.75	2.30	4.40	PC29/PG16
FL210 & RL210	MILL	Y	160	706310056A	9.00	3.06	5.40	PC36/PG16
FL210 & RL210	MILL	Y/N	235	706310056B	11.42	4.00	6.72	2.50
FL250 & RL250	STEEL	N	61	0754520009B	6.34	2.00	4.12	1.75
FL250 & RL250	STEEL	N	121	0754520009A	7.69	2.38	5.25	1.94
FL250 & RL250	CAST IRON	N	110	075460062B	7.25	2.50	5.25	1.5 TAP
FL250 & RL250	CAST IRON	N	210	706320016A	10.50	4.88	9.00	4.0 TAP
FL250 & RL250	MILL	Y	100	706310229A	7.75	2.30	4.40	PC29/PG16
FL250 & RL250	MILL	Y	160	706310056A	9.00	3.06	5.40	PC36/PG16
FL250 & RL250	MILL	Y/N	235	706310056B	11.42	4.00	6.72	2.50
FL250 & RL250	MILL	Y	400	706310063B	14.39	7.43	12.15	BLANK

FRAME SIZE	YAB	XX	XY	PART NUMBER	FRAME SIZE	YAB	XX	XY	PART NUMBER
FL120/FL160/FL200/FL180	7.38	4.25	4.25	602007-26-A	FL120/FL160/FL200/FL180	10.88	8.00	8.00	706310-3-B
FL250/FL180/FL280/FL180	8.44	4.25	4.25	602007-26-A	FL250/FL180/FL280/FL180	11.88	8.00	8.00	706310-3-B
FL280/FL180/FL280/FL180	9.12	4.25	4.25	602007-26-A	FL280/FL180/FL280/FL180	12.62	8.00	8.00	706310-3-B

FRAME SIZE	YAB	XX	XY	PART NUMBER	FRAME SIZE	YAB	XX	XY	PART NUMBER
FL120/FL160/FL200/FL180	7.38	4.25	4.25	602007-26-A	FL120/FL160/FL200/FL180	10.88	8.00	8.00	706310-3-B
FL250/FL180/FL280/FL180	8.44	4.25	4.25	602007-26-A	FL250/FL180/FL280/FL180	11.88	8.00	8.00	706310-3-B
FL280/FL180/FL280/FL180	9.12	4.25	4.25	602007-26-A	FL280/FL180/FL280/FL180	12.62	8.00	8.00	706310-3-B

(1) 1/4" PIPE TAP.  
(2) CUSTOMER TO PROVIDE WIRE TYPE CONDUIT.  
(3) 2" DIA. SA OR 1" DIA. DN -40.

TERMINAL BOX CAN BE ROTATED FOR LEAD INLET AT TOP, SIDES OR BOTTOM.  
TERMINAL BOX LOCATED ON OPPOSITE SIDE WHEN F-2, V-1, V-4, V-5, V-7,  
OR C-1 MOUNTING IS SPECIFIED. BOX LOCATED ON TOP WHEN SPECIFIED.


050-677919

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: ADD 706310-637 & 639 BOX	VERSION: 06	TDR: 000001180260
REV. LTR: F	REVISED: 11: 08: 56 10/26/2021	BY: RCGRWM
FILE: \RGG\00003\692		
MTL: -		

**BALDOR - RELIANCE®**  
DIM SHT NEMA RL210-RL280 FL180-FL280 IEC RDL132-RDL180  
SH 1 of 1

422927-001



NOTE:  
DATA TO BE SIZED  
SO THAT IT FITS INTO  
MATERIAL DECAL  
DIMENSIONS. MAKE  
LETTERS & NUMBERS  
AS LARGE AS POSSIBLE.

MATERIAL: CERAMATIC DGF-P4  
PERMA GRIP ADHESIVE

ALL LETTERS, NUMBERS  
AND LINES TO BE BLACK  
ON WHITE BACKGROUND.

422927-001

REV. DESC: CHANGE BACKGROUND COLOR FROM GOLD TO WHITE		
REV. LTR: B	VERSION: 02	TDR: 00000788708
FILE: \RGG\00000\203	REVISED: 08:09:29 03/04/2013	
MTL: -	BY: RGGWT	

**BALDOR**

EXTERNAL CONNECTION LABEL

SH 1 of 1