

ABB BALDOR RELIANCE III

Customer information packet

IDDRPM18254C

25HP, 1740RPM, 3PH, 60HZ, 1844C, DPG-FV, FT/2

Part Detail

Revision	D
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	L3346A
Layout	617233-023
Eff. date	01-21-2022
CD Diagram	422927-001
Poles	04
Leads	
Proprietary	False
Created date	04-10-2015

Nameplate

000613006MY							
	DUTY	HP	RPM	AMPS	VOLTS	HZ	
	CONT	25	1740	33	460	60	
	CONT	25	3150	32	460	109	
CAT.NO.	IDDRPM18254C		SPEC. NO.		P18T0330		
SER.NO			FR	FL 1844CZ	INSUL	H	
PH.	3	MAX SAFE SPEED		7200	AMB.	40	MIN. AMB.
DESIGN NO.	L3346A		TYPE		ENCL.	DP	
S.F.	1.0		D.E. BRG.	45BC02JPP30A			
ENCL MOD	FORCE VENT		O.D.E. BRG.	35BC02JPP30A			

000613006MY

	DUTY	HP	RPM	AMPS	VOLTS	HZ	
	CONT	25	1740	33	460	60	
	CONT	25	3150	32	460	109	
CAT.NO.	IDDRPM18254C		SPEC. NO.		P18T0330		
SER.NO			FR	FL 1844CZ	INSUL	H	
PH.	3	MAX SAFE SPEED		7200	AMB.	40	MIN. AMB. -25
DESIGN NO.	L3346A		TYPE		ENCL.	DP	
S.F.	1.0		D.E. BRG.	45BC02JPP30A			
ENCL MOD	FORCE VENT		O.D.E. BRG.	35BC02JPP30A			

REL S.O.	-	VOLTS	460	ENCLOSURE	DPFV	WYE CONN EQ CKT OHMS PER PHASE		
FRAME	FL1844	AMPS	33	MAX SAFE RPM	7200	(AT BASE RATING, 25 °C)		
HP	25	DUTY	CONT	IM (AMPS)	14	R1	.279	X1 .949
BASE SPEED	1740	S.F.	1.0	P.F.@NL/FL	.080/.839	R2	.198	X2 .903
PHASE/HERTZ	3/60	AMB °C/INSUL	40/H	WK ² (Lb-Ft ²)	.645			XM 15.4

RATED FULL LOAD DATA

	RPM	HP	TORQUE LB-FT	FUND VOLTS	FREQ-HZ	AMPS
BASE SPEED	1741	25.0	75	460	60	34.3
MAX SPEED	3152	25.0	42	460	109	31.6
MIN SPEED	0	0	75	28.1	1.97	34.3

LOAD PERFORMANCE AT BASE SPEED

	RPM	HP	TORQUE LB-FT	FUND VOLTS	FREQ-HZ	AMPS
NO LOAD	1800	0	0	460	60	17.6
1/4	1787	6.25	18	460	60	19.0
1/2	1773	12.5	37	460	60	22.6
3/4	1758	18.7	56	460	60	27.8
FULL LOAD	1741	25.0	75	460	60	34.3
O/L	1650	47.4	151	460	60	69.2

BLOWER DATA

VOLTS	PH/HZ	FL AMPS	LR AMPS	FRAME	CFM

REMARKS: TYPICAL DATA


BALDOR
A MEMBER OF THE ABB GROUP

DR. BY B. GRANT
CK. BY B. GRANT
APP. BY T. CUFR
DATE 7-24-06

**A-C MOTOR
PERFORMANCE DATA** **L3346A**
ISSUE DATE **7-24-06**

REL S.O.	-	VOLTS	460	ENCLOSURE	DPFV	WYE CONN EQ CKT OHMS PER PHASE	
FRAME	FL1844	AMPS	33	MAX SAFE RPM	7200	(AT BASE RATING, 25 °C)	
HP	25	DUTY	CONT	IM (AMPS)	14	R1 .279	X1 .949
BASE SPEED	1740	S.F.	1.0	P.F. @NL/FL	.080/.839	R2 .198	X2 .903
PHASE/HERTZ	3/60	AMB °C/INSUL	40/H	WK ² (Lb-Ft ²)	.645	XM 15.4	

VARIABLE SPEED AC MOTOR CURVES



REMARKS: TYPICAL DATA
DATA VALID FOR NAMEPLATE SPEED RANGE ONLY




DR. BY B GRANT
CK. BY B GRANT
APP. BY T. CUFR
DATE 7-24-06

**A-C MOTOR
PERFORMANCE
CURVES**

L3346A
SH 1 OF 2
ISSUE DATE 7-24-06

REL S.O.	-	VOLTS	460	ENCLOSURE	DPFV	WYE CONN EQ CKT OHMS PER PHASE	
FRAME	FL1844	AMPS	33	MAX SAFE RPM	7200	(AT BASE RATING, 25 °C)	
HP	25	DUTY	CONT	IM (AMPS)	14	R1 .279	X1 .949
BASE SPEED	1740	S.F.	1.0	P.F. @NL/FL	.080/.839	R2 .198	X2 .903
PHASE/HERTZ	3/60	AMB °C/INSUL	40/H	WK ² (Lb-Ft ²)	.645	XM 15.4	

LOAD PERFORMANCE (CONSTANT V/HZ RANGE)




REMARKS: TYPICAL DATA
DATA VALID FOR NAMEPLATE SPEED RANGE ONLY



DR. BY B GRANT
CK. BY B GRANT
APP. BY T. CUFR
DATE 7-24-06


**A-C MOTOR
PERFORMANCE
CURVES**

L3346A
SH 2 OF 2
ISSUE DATE 7-24-06



INDUSTRIAL ALTERNATING CURRENT MOTORS
RPM AC

STEEL, CAST IRON, MILL AND TERMINAL BOARD CONDUIT BOX DIMENSIONS
NEMA FRAMES RL210 thru RL280 and IEC FRAMES RDL132 thru RDL180
NEMA FRAMES FL180 thru FL280 and IEC FRAMES FDL112 thru FDL180



FRAME	TYPE	TERMINAL STRIP	AMPS	C/BOX	Y	TA	T	AA
FL180	STEEL	N	40	706320003A	5.00	1.62	3.00	1.12
FL180	STEEL	Y/N	75	706320003A	6.12	2.35	4.38	1.75/2.00
FL180	STEEL	N	208	706320007A	6.62	2.00	7.00	2.50/3.00
FL180	CAST IRON	Y/N	208	706320004C	6.75	2.50	4.38	1.50/1.75
FL180 & FDL11	MILL	Y	100	706310056A	7.75	2.30	4.40	PG29/PG16

FL210 & RL210	STEEL	N	61	075452000B	6.34	2.00	4.12	1.75
FL210 & RL210	STEEL	N	121	075452001A	7.69	2.38	5.25	1.94
FL210 & RL210	STEEL	N	305	706320016A	9.00	4.12	8.44	4.59
FL210 & RL210	CAST IRON	N	110	075460052B	7.25	2.50	5.25	1.5 TAP
FL210 & RL210	MILL	Y	100	706310229A	7.75	2.30	4.40	PG29/PG16
FL210 & RL210	MILL	Y	160	706310056A	9.00	3.06	5.40	PG36/PG16
FL210 & RL210	MILL	Y/N	235	706310056B	11.42	4.00	6.72	2.50

FL250 & RL250	STEEL	N	61	075452000B	6.34	2.00	4.12	1.75
FL250 & RL250	STEEL	N	121	075452001A	7.69	2.38	5.25	1.94
FL250 & RL250	STEEL	N	305	706320016A	9.00	4.12	8.44	4.59
FL250 & RL250	CAST IRON	N	110	075460052B	7.25	2.50	5.25	1.5 TAP
FL250 & RL250	CAST IRON	N	210	706320013A	10.50	4.88	9.00	4.0 TAP
FL250 & RL250	MILL	Y	100	706310229A	7.75	2.30	4.40	PG29/PG16
FL250 & RL250	MILL	Y	160	706310056B	9.00	3.06	5.40	PG36/PG16
FL250 & RL250	MILL	Y/N	235	706310057A	11.42	4.00	6.72	2.50
FL250 & RL250	MILL	Y	400	706310063B	14.39	7.43	12.15	BLANK

FL280 & RL280	STEEL	N	160	706320029A	7.25	3.50	7.06	2.50
FL280 & RL280	STEEL	N	305	706320016A	9.00	4.12	8.44	4.59
FL280 & RL280	STEEL	N	500	702658001C	14.62	7.56	12.70	5.00
FL280 & RL280	CAST IRON	N	140	706320012B	9.25	4.81	8.56	3.0 TAP
FL280 & RL280	CAST IRON	N	210	706320013A	10.50	4.88	9.00	4.0 TAP
FL280 & RL280	CAST IRON	N	510	706320014D	15.00	7.56	12.81	5.0 TAP
FL280 & RL280	MILL	Y	100	706310056A	7.75	2.30	4.40	PG29/PG16
FL280 & RL280	MILL	Y	160	706310056B	9.00	3.06	5.40	PG36/PG16
FL280 & RL280	MILL	Y/N	235	706310057A	11.42	4.00	6.72	2.50
FL280 & RL280	MILL	Y	400	706310063B	14.39	7.43	12.15	BLANK

FRAME SIZE	YAB	XA	XY	PART NUMBER	FRAME SIZE	YAB	XA	XY	PART NUMBER
FL210/RL210/FL112	7.38	4.25	4.25	602007-26-A	FL210/RL210/FL112	10.88	8.00	8.00	706310-3-B
FL250/RL250/FL160	8.44	4.25	4.25	602007-26-A	FL250/RL250/FL160	11.88	8.00	8.00	706310-3-B
FL280/RL280/FL280/180	9.12	4.25	4.25	602007-26-A	FL280/RL280/FL280/180	12.62	8.00	8.00	706310-3-B

- (1) 1"AW CONDUIT.
(2) 1"AW PIPE TAP.
(3) CUSTOMER TO PROVIDE HOLE PER CONDUIT.
(4) 2" DIA. SA OR 1" DIA. DIA. W/6

TERMINAL BOX CAN BE ROTATED FOR LEAD OUTLET AT TOP, SIDES OR BOTTOM.
TERMINAL BOX LOCATED ON OPPOSITE SIDE WHEN F-2, V-1, V-4, V-5, V-7,
OR C-1 MOUNTING IS SPECIFIED. BOX LOCATED ON TOP WHEN SPECIFIED.


CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: ADD 706310-637 & 639 BOX	VERSION: 06	TDR: 000001180260
REV. LTR: F	REVISED: 11:08:56 10/26/2021	BY: RCGRWM
FILE: \\RGG\00003\692		
MTL: -		

BALDOR - RELIANCE®

DIM SHT NEMA RL210-RL280 FL180-FL280 IEC RDL132-RDL180

422927-001



NOTE:
DATA TO BE SIZED
SO THAT IT FITS INTO
MATERIAL DECAL
DIMENSIONS. MAKE
LETTERS & NUMBERS
AS LARGE AS POSSIBLE.

MATERIAL: CERAMATIC DGF-P4
PERMA GRIP ADHESIVE

ALL LETTERS, NUMBERS
AND LINES TO BE BLACK
ON WHITE BACKGROUND.

422927-001

REV. DESC: CHANGE BACKGROUND COLOR FROM GOLD TO WHITE		
REV. LTR: B	VERSION: 02	TDR: 000000788708
FILE: \RGG\00000\203	REVISED: 08:09:29 03/04/2013	
MTL: -	BY: RGGWT	

BALDOR
EXTERNAL CONNECTION LABEL
SH 1 of 1