

ABB BALDOR RELIANCE III

Customer information packet

IDVSNM3534

.33HP, 1780RPM, 3PH, 60HZ, 56C, 3512M, TENV, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TENV
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.330 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	.850 A @ 460.0 V 1.500 A @ 208.0 V 1.700 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	75.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	0.9 a

Part Detail

Revision	E
Type	AC
Mech. spec.	35T995
Base	
Status	PRD/A
Elec. spec.	35WGG155
Layout	35LYT995
Eff. date	09-30-2025
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	01-10-2022

Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	S
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	6000 rpm
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3512M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.84 IN
Power Factor	49
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1780 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3301L									
CAT NO	IDVSNM3534								
SPEC.	35T995G155G3								
FRAME	56C		HP		.33	TE			
VOLTS	230/460								
MAG CUR	1.58/.79				FLA		1.7/.85		
RPM	1780				RPM MAX		6000		
HZ	60		PH	3		CLASS		F	
SER.F.	1.00				SL HZ		1		
NEMA-NOM-EFF	75.5		WK2		0.087				
RATING	40C AMB-CONT								
DE BRG	6205				ODE BRG		6203		
CC			SN						
	1000:1 CT/VT								

AC Induction Motor Performance Data

Record # 82226

Typical performance - not guaranteed values

Winding: 35WGG155-R018			Type: 3512M		Enclosure: TENV		
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		.33		Full Load Torque		0.977 LB-FT	
Volts		230/460		Start Configuration		direct on line	
Full Load Amps		1.7/.85		Breakdown Torque		6.28 LB-FT	
R.P.M.		1780		Pull-up Torque		3.26 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		4.04 LB-FT	
NEMA Design Code		B	KVA Code	S	Starting Current		6.71 A
Service Factor (S.F.)		1		No-load Current		0.792 A	
NEMA Nom. Eff.		75.5	Power Factor	49	Line-line Res. @ 25°C		43.2 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		49°C	
				Locked-rotor Power Factor		70.8	
				Rotor inertia		0.0866 lb-ft²	

Load Characteristics 460 V, 60 Hz, 0.33 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	22	31	41	49	57	63
Efficiency	47.4	63.1	70.8	75.1	77.6	79.1
Speed	1794	1789	1785	1780	1774	1769
Line amperes	0.786	0.791	0.814	0.839	0.878	0.933

ABB Motors and Mechanical Inc.

WINDING # 35WGG155

Typical performance - not guaranteed values.

0.33 HP 3 PH 60 HZ 1780 RPM 460 V 3512M

TORQUES (LB-FT) : PO=6.28 PU=3.26 LR=4.04 LRA=6.71





