


ENCLOSURE: DRIP PROOF
MOUNTING: FOOT
DRIVE METHOD: COUPLED OR BELTED

COOLING: FORCE VENTILATED

ACCESSORIES: PROVISIONS FOR
ENCODER MOUNTING
ONLY WHEN SPECIFIED



NOTE 3 MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED
AT END OF STD. SHAFT EXTENSION IS .002 T.I.R. UP TO AND
INCLUDING 1.625 DIA. AND .003 T.I.R. AND 1.625 TO 5 INCH DIA.

REV. DESC: REVISE CBOX AMPS FROM 800 TO 235			
REV: B	VERSION: 02	REVISED: 01:15:03 02/25/2022	TDR: 00000118681
MODEL NO. 617202-051			REF:
BY: MGHJMZ2	Material:		

DIM SHT RL2162Z DPFV STD F1 MILL BOX