



RPM-AC VARIABLE SPEED ALTERNATING CURRENT MOTOR
(U)RL2168Z

ENCLOSURE: DRIP PROOF
MOUNTING: FOOT
DRIVE METHOD: COUPLED OR BELTED

COOLING: FORCE VENTILATED
ACCESSORIES: PROVISIONS FOR
ENCODER MOUNTING
ONLY WHEN SPECIFIED



NOTE 1 ENCODER MOUNTING
1/2-13 TAP, .88 DEEP, ON A Ø7.25 BOLT CIRCLE
FACE RUNOUT AND ECCENTRICITY .004 MAX. T.I.R.

NOTE 2 SHAFT HEIGHT WILL NOT BE EXCEEDED.
SHIMS UP TO .03 INCHES IN THICKNESS ARE USUALLY
REQUIRED FOR COUPLED OR GEARED MOTORS.

NOTE 3 MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED
AT END OF STD. SHAFT EXTENSION IS .002 T.I.R. UP TO AND
INCLUDING 1.625 DIA. AND .003 T.I.R. AND 1.625 TO 5 INCH DIA.

235 AMP MILL CONDUIT BOX SHOWN
MOTOR WEIGHT: 345 LBS (MAY VARY 15%)
DIMENSIONS ARE IN INCHES SCALE 1:1

REV. DESC: REVISE CBOX AMPS FROM 800 TO 235			
REV: B	VERSION: 02	REVISED: 01:51:02 02/25/2022	TDR: 000001186811
MODEL NO. 617206-051		REF:	
BY: MGHJMZ2	Material:		

BALDOR - RELIANCE®

DIM SHT,RPMAC,DPFV,RL/URL2168Z,PROV FOR TACH,F1 MILL BOX

617206-051

617206-051