

RPMAC VARIABLE SPEED ALTERNATING CURRENT MOTOR
RL & URL2882Z

COOLING: FORCE VENTILATED

ACCESSORIES: PROVISIONS FOR
TACHOMETER MOUNTING
ONLY WHEN SPECIFIED

ENCLOSURE: DRIP PROOF

MOUNTING: FOOT

DRIVE METHOD: COUPLED OR BELTED

D

D

C



C

B

B

A

A



NOTE 1 TACHOMETER MOUNTING
1/2-13 TAP .88 DEEP, ON A 7.25 DIA. BOLT CIRCLE
FACE RUNOUT AND ECCENTRICITY .004 MAX T.I.R.

NOTE 2 SHAFT HEIGHT WILL NOT BE EXCEEDED.
SHIMS UP TO .03 INCHES IN THICKNESS ARE USUALLY
REQUIRED FOR COUPLED OR GEARED MACHINES.

NOTE 3 MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED
AT END OF STD. SHAFT EXTENSION IS .002 T.I.R. UP TO AND
INCLUDING 1.625 DIA. AND .003 T.I.R. 1.625 TO 5 INCH DIA.

235 AMP MILL TERMINAL BOX SHOWN
MOTOR WEIGHT 770 LBS. (MAY VARY 15%)
DIMENSIONS ARE IN INCHES SCALE 1:1

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: CORRECT NOTE 1			
REV: B	VERSION: 02	REVISED: 03:00:58 01/17/2023	TDR: 000001202572
MODEL NO. 617243-051		REF: -	
BY: USWATUR		B	

BALDOR - RELIANCE®

DIM SHT RPMAC DPFV RL & URL2882Z F1 MILL BOX

617243-051