ABB BALDOR RELIANCE

Customer information packet

IDVSNM3665T

5HP, 1750RPM, 3PH, 60HZ, 184TC, 0642M, TENV, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/19/2026 3:01:19 PM

Specifications

Enclosure	TENV
Frame	184TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	UR
	CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	13.200 A @ 230.0 V
	6.600 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Encoder/Feedback Device
Front Shaft Indicator	No Key Or Flat
Heater Indicator	No Heater
High Voltage Full Load Amps	6.6 a

Part Detail

Revision	L
Type	AC
Mech. spec.	06H927
Base	
Status	PRD/A
Elec. spec.	06WGX369
Layout	06LYH927
Eff. date	09-24-2026
CD Diagram	CD0005
Poles	04
Leads	9#16
Proprietary	False
Created date	09-04-2012

Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	6000 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0642M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	17.85 IN
Power Factor	80
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.00
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1750 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP4544L									
CAT.NO.	IDVSNM3665T								
SPEC.	06H927X369G1								
FRAME	184TC		**H.P.**	5					
VOLTS	230/460 1000:1 CT/VT								
MAG. CUR.	7.2/3.6			**F.L. AMPS**	13.2/6.6				
R.P.M.	1750			**R.P.M. MAX**	6000				
HZ.	60	**PH.**	3	**CLASS**	F				
SER.F.	1.00	**DES.**	A	**SL HZ**	1.6				
NEMA NOM. EFF.	89.5	**WK2**	0.39						
BLOWER		**V**		**PH**		**HZ**		**AMPS**	
RATING	40C AMB-CONT			**ENCL**	TENV				
DE	6206	**ODE**	6206						
CC	010A	**SN**							
	1.5:1 CHP PWM								

REL S.O.	IDVSNM3665T	VOLTS	460	ENCLOSURE	TEFC	WYE CONN EQ CKT OHMS PER PHASE			
FRAME	184TC	AMPS	6.6	MAX SAFE RPM	6000	(AT BASE RATING, 25^{0}C)			
HP	5	DUTY	CONT	In (AMPS)	3.6	R1	1.1200	X1	2.8100
BASE SPEED	1750	S.F.	1.0	P.F. @NL/FL	6/79	R2	0.9210	X2	2.3200
PHASE/HZ	3/60	AMB^{0}C/INSUL	40/F	WK^2 (lb-ft^2)	0.4			XM	68.7200

Rated Full Load Data

	RPM	HP	Torque	Volts	Freq-Hz	Amps
Base Speed	1751	5.0	15.00	460	60	6.54
Max Speed	2626	5.0	9.98	460	90	5.95
Min Speed	0	0.0	14.97	32.29	1.63	6.54

Load Performance at Base Speed

	RPM	HP	Torque	Volts	Freq-Hz	Amps
No Load	1799	0.0	0.00	460	60	3.60
1/4	1788	1.3	3.74	460	60	3.72
1/2	1777	2.5	7.52	460	60	4.37
3/4	1764	3.8	11.30	460	60	5.41
Full Load	1751	5.0	15.00	460	60	6.54
O/L	1708	10.0	30.70	460	60	12.00

Blower Data	Volts	Ph/Hz	FL Amps	LR Amps	Frame	CFM

Remarks: Calculated Data
Vector PWM Inverter Duty

BALDOR
A MEMBER OF THE ABB GROUP

DR BY Micheal Williamson
CK BY Micheal Williamson
APP BY Micheal Williamson
DATE 8/27/2012


A-C MOTOR
PERFORMANCE CURVES

06F551X369G1

ISSUE DATE 8/27/2012

REL S.O.	IDVSNM3665T	VOLTS	460	ENCLOSURE	TEFC	WYE CONN EQ CKT OHMS PER PHASE			
FRAME	184TC	AMPS	6.6	MAX SAFE RPM	6000	(AT BASE RATING, 25^{0}C)			
HP	5	DUTY	CONT	In (AMPS)	3.6	R1	1.1200	X1	2.8100
BASE SPEED	1750	S.F.	1.00	P.F. @NL/FL	6/79	R2	0.9210	X2	2.3200
PHASE/HZ	3/60	AMB^{0}C/INSUL	40/F	WK^2 (lb-ft^2)	0.4			XM	68.7200

Vector PWM Inverer Duty
Variable Speed AC Motor Curves




Calculated Data

Data Valid For Nameplate Speed Range only

BALDOR A MEMBER OF THE ABB GROUP	DR BY Micheal Williamson CK BY Micheal Williamson APP BY Micheal Williamson DATE 8/27/2012	A-C MOTOR PERFORMANCE CURVES	06F551X369G1 SH 1 of 2 ISSUE DATE 8/27/2012

REL S.O.	IDVSNM3665T	VOLTS	460	ENCLOSURE	TEFC	WYE CONN EQ CKT OHMS PER PHASE			
FRAME	184TC	AMPS	6.6	MAX SAFE RPM	6000	(AT BASE RATING, 25^{0}C)			
HP	5	DUTY	CONT	In (AMPS)	3.6	R1	1.1200	X1	2.8100
BASE SPEED	1750	S.F.	1.00	P.F. @NL/FL	6/79	R2	0.9210	X2	2.3200
PHASE/HZ	3/60	AMB^{0}C/INSUL	40/F	WK^2 (Lb-Ft^2)	0.4			XM	68.7200

Vector PWM Inverer Duty
Variable Speed AC Motor Curves



Calculated Data

Data Valid For Nameplate Speed Range only


BALDOR
A MEMBER OF THE ABB GROUP

DR BY Micheal Williamson
CK BY Micheal Williamson
APP BY Micheal Williamson
DATE 8/27/2012


A-C MOTOR
PERFORMANCE CURVES


06F551X369G1

SH 1 of 2
ISSUE DATE 8/27/2012


06LYH927
(614-643) = 17.85
8.85
2.62
.25
2.75
.25 KEY
1.75 LONG
AUX NAMEPLATE
(WHEN REQ'D)
GREASE FITTING
(EA. END)
1.88
(REF)
NOTE:
NO
KEYWAY
OR FLAT
NAMEPLATE
BALDOR
8.86
Ø 8.500
8.497
Ø 1.1250
1.1245
Ø 1.0000
.9995
8 HOLES
Ø.41
PROTECTIVE COVER
(MOUNT WITH
CONNECTOR OPENING
ON KOBX SIDE)
4.50
4.50
.50
5.50
3.50
6.50
11.85
7.12
4.73
2.04
45°
45°
9.23
4.50
4.44
LEAD
HOLE
Ø1.09
4 HOLES
.50-13 TAP
ON Ø7.25
B.C.
3.75
3.75
5.72
4.31
8.62
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOADING OF INOPC SWD MODEL & DRAWING FOR PKG 37
REV: E
VERSION: 05
REVISED: 10:42:29 09/19/2019
TDR: 000001120280
MODEL NO. 06LYH927
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
STD HORZ 182-4TC TENV V*S MASTER INVERTER
061LYH927

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS