

ABB BALDOR RELIANCE III

Customer information packet

IDVSWDM3542

.75HP, 1765RPM, 3PH, 60HZ, 56C, 3514M, TENV, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TENV
Frame	56C
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.210 A @ 460.0 V 2.420 A @ 208.0 V 2.420 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	82.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.2 a

Part Detail

Revision	B
Type	AC
Mech. spec.	35S639
Base	
Status	PRD/A
Elec. spec.	35WGG069
Layout	35LYS639
Eff. date	06-28-2023
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	03-11-2022

Insulation Class	H
Inverter Code	Inverter Duty
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	6000 rpm
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3514M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	11.06 IN
Power Factor	74
Product Family	Wash Down Paint Free
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1608L									
CAT NO	IDVSWDM3542								
SPEC.	35S639G069G1								
FRAME	56C			HP	.75 TE				
VOLTS	230/460								
MAG CUR	1.5/.75			FLA		2.28/1.14			
RPM	1765			RPM MAX			6000		
HZ	60	PH	3	CLASS			H		
SER.F.	1.00	DES	B	SL HZ			1.16		
NEMA-NOM-EFF	82.5		WK2	0.101					
BLWR V		PH		HZ		A			
RATING	40C AMB-CONT								
DE BRG	6205	ODE BRG			6203				
CC	SN								


ABB Motors and Mechanical Inc.

WINDING # 35WGG069

Typical performance - not guaranteed values.

0.75 HP 3 PH 60 HZ 1765 RPM 460 V 3514M

TORQUES (LB-FT) : PO=8 PU=4.4 LR=5.1 LRA=8.4



8/6/2026 ACPERF, record # 87333

