

# ABB BALDOR RELIANCE III

---

## Customer information packet

IDM2333T-5

44M 4P TEBC HOR 256TC T'STAT INV DUTY

Class - None

Division - Not Applicable

**Specifications**

<b>Enclosure</b>	TEBC
<b>Frame</b>	256TC
<b>Frame Material</b>	Iron
<b>Frequency</b>	60.00 Hz
<b>Haz Area Class and Group</b>	None
<b>Haz Area Division</b>	Not Applicable
<b>Motor Letter Type</b>	Three Phase
<b>Output @ Frequency</b>	15.000 HP @ 60 HZ
<b>Phase</b>	3
<b>Synchronous Speed @ Frequency</b>	1800 RPM @ 60 HZ
<b>Voltage @ Frequency</b>	575.0 V @ 60 HZ
<b>Agency Approvals</b>	UR CSA
<b>Ambient Temperature</b>	40 °C
<b>Auxiliary Box</b>	NO AUXILLARY BOX
<b>Auxiliary Box Lead Termination</b>	None
<b>Base Indicator</b>	Rigid
<b>Bearing Grease Type</b>	Polyrex EM (-20F +300F)
<b>Blower</b>	BLOWER
<b>Current @ Voltage</b>	14.600 A @ 575.0 V
<b>Design Code</b>	A
<b>Drip Cover</b>	No Drip Cover
<b>Duty Rating</b>	CONT
<b>Efficiency @ 100% Load</b>	92.4 %
<b>Electrically Isolated Bearing</b>	Not Electrically Isolated
<b>Feedback Device</b>	NO FEEDBACK
<b>Front Shaft Indicator</b>	None
<b>Heater Indicator</b>	No Heater
<b>High Voltage Full Load Amps</b>	14.6 a
<b>Insulation Class</b>	H
<b>Inverter Code</b>	Inverter Duty
<b>KVA Code</b>	H

**Part Detail**

<b>Revision</b>	H
<b>Type</b>	AC
<b>Mech. spec.</b>	09T110
<b>Base</b>	
<b>Status</b>	PRD/A
<b>Elec. spec.</b>	09WGT124
<b>Layout</b>	09LYT110
<b>Eff. date</b>	08-28-2025
<b>CD Diagram</b>	CD0006
<b>Poles</b>	04
<b>Leads</b>	3#12
<b>Proprietary</b>	False
<b>Created date</b>	03-19-2019

<b>Lifting Lugs</b>	<b>Standard Lifting Lugs</b>
<b>Locked Bearing Indicator</b>	Locked Bearing
<b>Max Speed</b>	5000 rpm
<b>Motor Lead Quantity/Wire Size</b>	3 @ 12 AWG
<b>Motor Lead Termination</b>	Flying Leads
<b>Motor Standards</b>	NEMA
<b>Motor Type</b>	0944M
<b>Mounting Arrangement</b>	F1
<b>Number of Poles</b>	4
<b>Overall Length</b>	29.41 IN
<b>Power Factor</b>	83
<b>Product Family</b>	General Purpose
<b>Pulley End Bearing Type</b>	Ball
<b>Pulley Face Code</b>	C-Face
<b>Pulley Shaft Indicator</b>	Standard
<b>Rodent Screen</b>	None
<b>RoHS Status</b>	ROHS COMPLIANT
<b>Service Factor</b>	1.00
<b>Shaft Diameter</b>	1.625 IN
<b>Shaft Ground Indicator</b>	No Shaft Grounding
<b>Shaft Rotation</b>	Reversible
<b>Shaft Slinger Indicator</b>	Shaft Slinger
<b>Speed</b>	1765 rpm
<b>Speed Code</b>	Single Speed
<b>Starting Method</b>	Direct on line
<b>Thermal Device - Bearing</b>	None
<b>Thermal Device - Winding</b>	Normally Closed Thermostat
<b>Vibration Sensor Indicator</b>	No Vibration Sensor
<b>Winding Thermal 1</b>	None
<b>Winding Thermal 2</b>	None

**Nameplate**

<b>NP1163L</b>	
<b>CAT NO</b>	IDM2333T-5
<b>SPEC.</b>	09T110T124G1
<b>FRAME</b>	256TC <b>HP</b> 15 TE
<b>VOLTS</b>	575
<b>MAG CUR</b>	6.1 <b>FLA</b> 14.6
<b>RPM</b>	1765 <b>RPM MAX</b> 5000
<b>HZ</b>	60 <b>PH</b> 3 <b>CLASS</b> H
<b>SER.F.</b>	1.00 <b>DES</b> A <b>SL HZ</b> 1.2
<b>NEMA-NOM-EFF</b>	92.4 <b>WK2</b> 1.93
<b>BLWR V</b>	<b>PH</b> <b>HZ</b> <b>A</b>
<b>RATING</b>	40C AMB-CONT
<b>DE BRG</b>	6309 <b>ODE BRG</b> 6208
<b>CC</b>	010A <b>SN</b>
	1000:1 CT, 1000:1 VT

NP VOLTS	575	MAX SAFE RPM	5000	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)		
NP AMPS	14.6	Base Volt	575	R1	0.457	X1 1.770
HP	15HP	NL AMPS	6.1	R2	0.372	X2 2.090
BASE SPEED	1765	Slips (Hz)	1.17			XM 52.900
PHASE/HZ	3/60	WK <sup>2</sup> (lb-ft <sup>2</sup> )	1.92			

**Rated Full Load Data**

	RPM	HP	Torque	Volts	Freq-Hz	Amps
Base Speed	1765	15.0	44.5	575	60	14.6
Max Speed	2646	15.0	29.7	575	90	13.9
Min Speed	0	0.0	44.5	32.31	1.17	14.6

**Load Performance at Base Speed**

	RPM	HP	Torque	Volts	Freq-Hz	Amps
No Load	1799	0.0	0.0	575	60	6.1
1/4	1791	3.7	10.8	575	60	6.9
1/2	1783	7.5	22.1	575	60	8.8
3/4	1774	11.3	33.3	575	60	11.6
Full Load	1765	15.0	44.5	575	60	14.6
O/L	1730	29.9	90.8	575	60	29.1

Blower Data	Volts	Ph/Hz	FL Amps	LR Amps	Frame	CFM

Remarks: Calculated Data  
Vector PWM Inverter Duty




DR BY BR  
CK BY  
APP BY BR  
DATE 3/28/2017

A-C MOTOR **09WGT124**  
PERFORMANCE  
CURVES

NP VOLTS	575	MAX SAFE RPM	5000	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)			
NP AMPS	14.6	Base Volt	575	R1	0.457	X1	1.770
HP	15HP	NL AMPS	6.05	R2	0.372	X2	2.090
BASE SPEED	1765	Slips (Hz)	1.17			XM	52.900
PHASE/HZ	3/60	WK2 (lb-ft)	1.92				

Vector PWM Inverter Duty  
Variable Speed AC Motor Curves



Calculated Data

Data Valid For Nameplate Speed Range only




DR BY BR  
 CK BY  
 APP BY BR  
 DATE 3/28/2017

A-C MOTOR **09WGT124**  
 PERFORMANCE  
 CURVES

NP VOLTS	575	MAX SAFE RPM	5000	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)			
NP AMPS	14.6	Base Volt	575	R1	0.457	X1	1.770
HP	15HP	NL AMPS	6.05	R2	0.372	X2	2.090
BASE SPEED	1765	Slips (Hz)	1.17			XM	52.900
PHASE/HZ	3/60	WK2 (lb-ft <sup>2</sup> )	1.92				

Vector PWM Inverter Duty  
Variable Speed AC Motor Curves



Calculated Data


Data Valid For Nameplate Speed Range only



DR BY BR  
 CK BY  
 APP BY BR  
 DATE 3/28/2017

A-C MOTOR  
 PERFORMANCE  
 CURVES

09WGT124



CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIRO
MTL: -		© □

**BALDOR - RELIANCE®**

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1