ABB BALDOR RELIANCE

Customer information packet

IDNM2334T

20HP, 1780RPM, 3PH, 60HZ, 284T, 1056M, TENV, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/17/2026 10:24:29 PM

Specifications

Enclosure	TENV
Frame	284T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	20.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	UR
	CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	26.000 A @ 460.0 V
	52.000 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Encoder/Feedback Device
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	26.0 a

Part Detail

Revision	AF
Type	AC
Mech. spec.	10F681
Base	
Status	PRD/A
Elec. spec.	10WGW586
Layout	10LYF681
Eff. date	08-18-2025
CD Diagram	CD0005
Poles	04
Leads	9#10
Proprietary	False
Created date	01-01-0001

Insulation Class	H
Inverter Code	Inverter Duty
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	4000 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1056M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	27.36 IN
Power Factor	77
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1780 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	NONE (OLD)
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1163L									
CAT NO	IDNM2334T								
SPEC.	10F681W586G1								
FRAME	284T			**HP**	20 TE				
VOLTS	230/460								
MAG CUR	29/14.5				**FLA**	52/26			
RPM	1780			**RPM MAX**	4000				
HZ	60	**PH**	3		**CLASS**	H			
SER.F.	1.00	**DES**	A			**SL HZ**	0.67		
NEMA-NOM-EFF	93		**WK2**	4.46					
BLWR V		**PH**		**HZ**		**A**			
RATING	40C AMB-CONT								
DE BRG	6311			**ODE BRG**	6309				
CC	010A	**SN**							
	1000:1 CT, 1000:1 VT								

INP AMPS	52/26	MAX SAFE RPM	2700	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)			
HP	20 HP	Base Volt	460	R1	0.131	X1	0.594
BASE SPEED	1784	NL AMPS	14.50	R2	0.644	X2	0.478
PHASE/HZ	3/60	Slips(HZ)	0.53	R2B	0.094	X2B	0.811
		WK2 (LB-FT2)	4.440	R2E	0.027	XM	17.600

Rated Full Load Data

	RPM	HP	Torque	Volts	Freq-Hz	Amps
Base Speed	1784	20.3	59.8	460	60	26.1
Max Speed	2676	20.3	39.8	460	90	23.5
Min Speed	0	0.0	59.8	13.24	0.53	26.1

Load Performance at Base Speed

	RPM	HP	Torque	Volts	Freq-Hz	Amps
No Load	1799	0.0	0.0	460	60	14.5
1/4	1796	5.1	15.0	460	60	15.6
1/2	1792	10.2	30.0	460	60	18.2
3/4	1788	15.3	44.8	460	60	21.7
Full Load	1784	20.3	59.8	460	60	26.1
O/L	1765	40.7	121.0	460	60	47.5

Blower Data	Volts	Ph/Hz	FL Amps	LR Amps	Frame	CFM

Remarks: Calculated Data
Vector PWM Inverter Duty

BALDOR®
A MEMBER OF THE ABB GROUP

DR BY USBRRAN1
CK BY
APP BY USBRRAN1
DATE 9/8/2017

A-C MOTOR PERFORMANCE CURVES

10WGW586

Record: 2299

IDNM2334T - 20HP, 1780RPM, 3PH, 60HZ, 284T, 1056M, TENV, F1

INT AMPS	52/26
HP	20 HP
BASE SPEED	1784
PHASE/HZ	3/60


MAX SAFE RPM	2700
Base Volt	460
NL AMPS	14.50
Slips(HZ)	0.53
WK2 (LB-FT2)	4.440

WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)

R1	0.131	X1	0.594
R2	0.644	X2	0.478
R2B	0.094	X2B	0.811
R2E	0.027	XM	17.600

Vector PWM Inverer Duty

Variable Speed AC Motor Curves



Calculated Data

Data Valid For Nameplate Speed Range only

BALDOR
A MEMBER OF THE ABB GROUP

DR BY USBRRAN1
CK BY
APP BY USBRRAN1
DATE 9/8/2017

A-C MOTOR PERFORMANCE CURVES

10WGW586

Record: 2299

ABB BALDOR / RELIANCE II


CUSTOMER INFORMATION PACKET

IDNM2334T - 20HP, 1780RPM, 3PH, 60HZ, 284T, 1056M, TENV, F1

VOLTS	208/460	MAX SAFE RPM	2700	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)			
NP AMPS	52/26	Base Volt	460	R1	0.131	X1	0.594
HP	20 HP	NL AMPS	14.50	R2	0.644	X2	0.478
BASE SPEED	1784	Slips(HZ)	0.53	R2B	0.094	X2B	0.811
PHASE/HZ	3/60	WK2 (LB-FT2)	4.440	R2E	0.027	XM	17.600

Vector PWM Inverer Duty

Vaiable Speed AC Motor Curves



Calculated Data

Data Valid For Nameplate Speed Range only

BALDOR®

A MEMBER OF THE ABB GROUP

DR BY USBRRAN1

CK BY


APP BY USBRRAN1

DATE 9/8/2017


A-C MOTOR PERFORMANCE CURVES


10WGW586

Record: 2299


10LYF681
(1030-1060) = 27.37
12.49
2.86
1.25
4.75
4.63
.50 KEY
3.25 LONG
1.000
.999
Ø 1.875
1.874
SLINGERS
AUTO DRAIN
(EA END)
8 HOLES
Ø .53
9.50
9.50
.92
11.00
4.75
12.84
15.50
13.18
7.59
GREASER
& RELIEF
(EA. END)
2.50
14.64
7.00 +.00 -.06
3.25
.88
LEAD HOLE
Ø 2.00
5.50
5.50
10.57
6.38
12.75
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT STOCK LAYOUTS FROM AUTOCAD TO SWD
REV: E
VERSION: 05
REVISED: 02:19:34 12/13/2023
TDR: 000001220227
MODEL NO. 10LYF681
REF: -
BY: USALMAZ
B
BALDOR
HORZ TENV 284-6T INV W/THRU SH ENCODER DESIGN & COVER
10LYF681

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS