

ABB BALDOR RELIANCE III

Customer information packet

IDVSM2333T

15HP, 1765RPM, 3PH, 60HZ, 254TC, 0944M, TEFC, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	254TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	18.100 A @ 460.0 V 36.200 A @ 230.0 V 38.000 A @ 208.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	18.1 a

Part Detail

Revision	G
Type	AC
Mech. spec.	09K146
Base	
Status	PRD/A
Elec. spec.	09WGT597
Layout	09LYK146
Eff. date	08-28-2025
CD Diagram	CD0005
Poles	04
Leads	9#12
Proprietary	False
Created date	02-02-2021

Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	9 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0944M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	26.84 IN
Power Factor	84
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3302L			
CAT NO	IDVSM2333T		
SPEC.	09K146T597G1		
FRAME	254TC	HP	15 TE
VOLTS	230/460		
MAG CUR	14.6/7.3	FLA	36.2/18.1
RPM	1765	RPM MAX	2700
HZ	60	PH	3 CLASS F
SER.F.	1.00	SL HZ	1.2
NEMA-NOM-EFF	92.4	WK2	1.93
RATING	40C AMB-CONT		
DE BRG	6309	ODE BRG	6208
CC	010A SN		
	1.5:1 CHP PWM		
	1000:1 CT, 1000:1 VT		

NP VOLTS	230/460	MAX SAFE RPM	2700	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)			
NP AMPS	36.2/18.1	Base Volt	460	R1	0.296	X1	1.130
HP	15HP	NL AMPS	7.6	R2	0.238	X2	1.330
BASE SPEED	1765	Slips	1.17			XM	33.900
PHASE/HZ	3/60	WK ² (lb-ft ²)	1.92				

Rated Full Load Data

	RPM	HP	Torque	Volts	Freq-Hz	Amps
Base Speed	1765	15.0	44.5	460	60	18.1
Max Speed	2646	15.0	29.7	460	90	17.2
Min Speed	0	0.0	44.5	23.08	1.17	18.1

Load Performance at Base Speed

	RPM	HP	Torque	Volts	Freq-Hz	Amps
No Load	1799	0.0	0.0	460	60	7.6
1/4	1791	3.7	10.8	460	60	8.6
1/2	1783	7.5	22.1	460	60	11.0
3/4	1774	11.3	33.3	460	60	14.5
Full Load	1765	15.0	44.5	460	60	18.1
O/L	1730	29.9	90.8	460	60	36.1

Blower Data	Volts	Ph/Hz	FL Amps	LR Amps	Frame	CFM

Remarks: Calculated Data
Vector PWM Inverter Duty




DR BY BR
 CK BY
 APP BY BR
 DATE 10/31/2024

A-C MOTOR **09WGT597**
 PERFORMANCE
 CURVES

NP VOLTS	230/460	MAX SAFE RPM	2700	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)		
NP AMPS	36.2/18.1	Base Volt	460	R1	0.296	X1 1.13
HP	15HP	NL AMPS	7.56	R2	0.238	X2 1.33
BASE SPEED	1765	Slips	1.16666667			XM 33.9000
PHASE/HZ	3/60	WK2 (lb-ft2)	1.92			

Vector PWM Inverter Duty
Variable Speed AC Motor Curves



Calculated Data

Data Valid For Nameplate Speed Range only




DR BY BR
 CK BY
 APP BY BR
 DATE 10/31/2024

A-C MOTOR **09WGT597**
 PERFORMANCE
 CURVES

NP VOLTS	230/460	MAX SAFE RPM	2700	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)			
NP AMPS	36.2/18.1	Base Volt	460	R1	0.296	X1	1.13
HP	15HP	NL AMPS	7.56	R2	0.238	X2	1.33
BASE SPEED	1765	Slips	1.16666667			XM	33.9
PHASE/HZ	3/60	WK2 (lb-ft ²)	1.92				

Vector PWM Inverter Duty
Variable Speed AC Motor Curves




Calculated Data

Data Valid For Nameplate Speed Range only



DR BY BR
 CK BY
 APP BY BR
 DATE 10/31/2024

A-C MOTOR **09WGT597**
 PERFORMANCE
 CURVES



CD0005



LOW VOLTAGE
(2Y)



LINE

HIGH VOLTAGE
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS

REV. LTR: E BY: JLP REVISED: 01/19/99 10:15 TDR: 0171435

500000

FILE: AAA00005140

MDL: -

MTL: -

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS