



---

# Customer information packet

## IDVSNM3584T-5

1.5HP, 1770RPM, 3PH, 60HZ, 145TC, 0530M, TENV

Class - None

Division - Not Applicable

## Specifications

Enclosure	TENV
Frame	145TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.700 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.7 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	M

## Part detail

Revision	A
Type	AC
Mech. spec.	05E534
Base	
Status	PRD/A
Elec. spec.	05WGX563
Layout	05LYE534
Eff. date	12-05-2023
CD Diagram	CD0006
Poles	04
Leads	3#18
Proprietary	False
Created date	02-23-2023

Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	3 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0530M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	14.65 IN
Power Factor	77
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

**Nameplate**

<b>NP3302L</b>			
<b>CAT NO</b>	IDVSNM3584T-5		
<b>SPEC.</b>	05E534X563G1		
<b>FRAME</b>	145TC	<b>HP</b>	1.5 TE
<b>VOLTS</b>	575		
<b>MAG CUR</b>	1	<b>FLA</b>	1.7
<b>RPM</b>	1765	<b>RPM MAX</b>	2700
<b>HZ</b>	60	<b>PH</b>	3 <b>CLASS</b> F
<b>SER.F.</b>	1.00	<b>SL HZ</b>	1.2
<b>NEMA-NOM-EFF</b>	86.5	<b>WK2</b>	0.217
<b>RATING</b>	40C AMB-CONT		
<b>DE BRG</b>	6205	<b>ODE BRG</b>	6203
<b>CC</b>	010A	<b>SN</b>	

**AC Induction Motor Performance Data**

Record # 82110

Typical performance - not guaranteed values

Winding: 05WGX563-R002		Type: 0530M	Enclosure: TENV	
<b>Nameplate Data</b>			<b>575 V, 60 Hz: Single Voltage Motor</b>	
Rated Output (HP)	1.5	Full Load Torque	4.44 LB-FT	
Volts	575	Start Configuration	direct on line	
Full Load Amps	1.7	Breakdown Torque	18.9 LB-FT	
R.P.M.	1765	Pull-up Torque	12.3 LB-FT	
Hz	60 Phase	3	Locked-rotor Torque	11.1 LB-FT
NEMA Design Code	B KVA Code	M	Starting Current	12.7 A
Service Factor (S.F.)	1	No-load Current	1 A	
NEMA Nom. Eff.	86.5 Power Factor	77	Line-line Res. @ 25°C	16.1 Ω
Rating - Duty	40C AMB-CONT		Temp. Rise @ Rated Load	55°C
			Locked-rotor Power Factor	55.3
			Rotor inertia	0.217 lb-ft <sup>2</sup>

**Load Characteristics 575 V, 60 Hz, 1.5 HP**

% of Rated Load	25	50	75	100	125	150
Power Factor	35	56	69	77	83	86
Efficiency	75.5	84.1	86.8	87.6	87.7	87.2
Speed	1793	1787	1781	1767	1768	1760
Line amperes	1.06	1.2	1.41	1.66	1.94	2.26


ABB Motors and Mechanical Inc.

WINDING # 05WGX563


1.5 HP 3 PH 60 HZ 1765 RPM 575 V 0530M

Typical performance - not guaranteed values.




TORQUES (LB-FT): PO=18.9 PU=12.3 LR=11.1 LRA=12.7



8/11/2024 ACPERF, record # 82110



CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIRO
MTL: -		© □

**BALDOR - RELIANCE®**

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1