Customer information packet

IDVSWDM3615T

5HP, 1750RPM, 3PH, 60HZ, 184TC, 3646M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/3/2026 6:51:38 AM

Specifications

Enclosure	TEFC
Frame	184TC
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	UR
	CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	13.000 A @ 230.0 V
	6.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	6.5 a

Part Detail

Revision	Q
Type	AC
Mech. spec.	36K606
Base	
Status	PRD/A
Elec. spec.	36WGS719
Layout	36LYK606
Eff. date	09-27-2024
CD Diagram	CD0005
Poles	04
Leads	9#16
Proprietary	False
Created date	06-04-2012

Insulation Class	H
Inverter Code	Inverter Duty
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	6000 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3646M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.06 IN
Power Factor	81
Product Family	Wash Down Paint Free
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1750 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3956L							
CAT.NO.	IDVSWDM3615T						
SPEC.	36K606S719G1						
FRAME	184TC		**H.P.**	5 TE			
VOLTS	230/460						
MAG. CUR.	5.8/2.9				**F.L. AMPS**	13/6.5	
R.P.M.	1750		**R.P.M. MAX**	6000			
HZ.	60	**PH.**	3	**CLASS**	H		
SER.F.	1.00	**DES.**	B	**SL HZ**	1.7		
NEMA NOM. EFF.	89.5	**WK2**	0.428				
BLWR V		**PH**		**HZ**		**AMPS**	
RATING	40C AMB-CONT						
DE BRG	6206		**ODE BRG**	6205			
CC	010A	**SN**					

AC Induction Motor Performance Data
Record # 38663
Typical performance - not guaranteed values

Winding: 36WGS719-R002	**Type:** 3646M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			5	**Full Load Torque**	15.2 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			13/6.5	**Breakdown Torque**	49.7 LB-FT
R.P.M.			1750	**Pull-up Torque**	27.7 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	32.3 LB-FT
NEMA Design Code	B	**KVA Code**	J	**Starting Current**	48.3 A
Service Factor (S.F.)			1	**No-load Current**	2.91 A
NEMA Nom. Eff.	89.5	**Power Factor**	81	**Line-line Res. @ 25ºC**	2.32 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	87°C
S.F. Amps				**Temp. Rise @ S.F. Load**	107°C
				Locked-rotor Power Factor	39
				Rotor inertia	0.428 LB-FT2

Load Characteristics 460 V, 60 Hz, 5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	42	64	75	81	83	84
Efficiency	86.7	90.5	90.8	90.1	88.4	86.6
Speed	1788	1776	1763	1748	1732	1714
Line amperes	3.27	4.1	5.2	6.49	8.02	9.69


ABB Motors and Mechanical Inc.


WINDING # 36WGS719

5 HP 3 PH 60 HZ 1750 RPM 460 V 3646M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=49.7 PU=27.7 LR=32.3 LRA=48.3




36LYK606
614-623 = 15.12
624-634 = 16.50
635-646 = 18.00
(635-646) ONLY
.25
2.62
2.75
Ø8.38
NAMEPLATE
.25 KEY
1.75 LONG
Ø8.500
8.497
8.85
Ø1.1250
1.1245
4 HOLES
3 W/PLUGS
EA. END
4.53
6.62
45°
45°
6.17
LEAD HOLE
.75 N.P.T.
4 HOLES
.50-13 TAP ON
Ø7.25 B.C.
5.38
FORSHEDA
SLINGER
INSTALL DUBO-LOK WASHER
UNDER RETAINER RING
SCREW HEAD.
FRONT END DETAIL
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD INOPC CREATED SWD DRG INTO BUS - PACKAGE 37
REV: G
VERSION: 07
REVISED: 03:25:17 09/19/2019
TDR: 000001120280
MODEL NO. 36LYK606
REF: -
BY: ENSTEK0
B
BALDOR - RELIANCE®
VERT 182-4TC TEFC 36M WD2 (PAINT FREE)
36LYK606

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS