ABB BALDOR RELIANCE

Customer information packet

IDXM7544T-C

5HP, 1750RPM, 3PH, 60HZ, 184T, 0642M, XPFC, F1
Class - CLI GP C,D; CLII GP F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/17/2026 11:25:27 PM

Specifications

Enclosure	XPFC
Frame	184T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	15
Current @ Voltage	6.600 A @ 460.0 V
	14.000 A @ 208.0 V
	13.200 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK

Part Detail

Revision	K
Type	AC
Mech. spec.	06K965
Base	
Status	INA/A
Elec. spec.	06WGX182
Layout	06LYK965
Eff. date	03-08-2021
CD Diagram	CD0005
Poles	04
Leads	9#16
Proprietary	False
Created date	11-07-2016

Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	6.6 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Max Speed	2700 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	X0642M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	17.56 IN
Power Factor	79
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1750 rpm
Speed Code	Single Speed

Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP0681XPSLEV												
NO.				**CC**	010A							
S/N				**TEMP CODE**	T3C							
SPEC.	06K965X182G1			**INV.TYPE**	PWM							
CAT.NO.				**C HP FR**	60		**C HP TO**	90				
HP	5			**CT HZ FROM**	15				**CT HZ TO**	60		
VOLTS	230/460			**VT HZ FROM**	6				**VT HZ TO**	60		
AMPS	13.2/6.6			**MAG CUR**	6/3							
RPM	1750			**MX RPM**	2700							
HZ	60	**PH**	3	**CL**	F	**NOM.EFF.**	89.5					
SER.F.	1.00	**DES**	B	**SL HZ**	1.7	**WK2**	0.39					
FRAME	184T	**RATING**	40C AMB-CONT									
	1.15SF SINEWAVE											

AC Induction Motor Performance Data
Record # 47867
Typical performance - not guaranteed values

Winding: 06WGX182-R036	**Type:** 0642M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			5	**Full Load Torque**	15 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			13.2/6.6	**Breakdown Torque**	53.9 LB-FT
R.P.M.			1750	**Pull-up Torque**	22.4 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	31.8 LB-FT
NEMA Design Code	B	**KVA Code**	J	**Starting Current**	46.6 A
Service Factor (S.F.)			1	**No-load Current**	3.02 A
NEMA Nom. Eff.	89.5	**Power Factor**	79	**Line-line Res. @ 25ºC**	2.63 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	53°C
S.F. Amps				**Temp. Rise @ S.F. Load**	65°C
				Locked-rotor Power Factor	40.5
				Rotor inertia	0.391 LB-FT2

Load Characteristics 460 V, 60 Hz, 5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	41	63	75	81	84	85
Efficiency	85.2	89.8	90.3	89.8	88.4	86.9
Speed	1789	1777	1765	1752	1737	1721
Line amperes	3.35	4.14	5.21	6.45	7.91	9.47


ABB Motors and Mechanical Inc.


WINDING # 06WGX182

5 HP 3 PH 60 HZ 1750 RPM 460 V 0642M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=53.9 PU=22.4 LR=31.8 LRA=46.6




06LYK965
614–643 = 17.56
8.56
3.26
2.75
UL NAMEPLATE
10.12 DIA.
.25 KEY 1.75 LONG
HAZARDOUS LOCATIONS
GRD LOC
1.1250 1.1245
DRAIN FITTING (EA END)
4.50
2.75
5.50
.50
6 HOLES .41 DIA.
8.00
13.61
5.03
5.06
1.88
9.56
4.50 +.00 -.06
LEAD HOLE .75–14 N.P.T.
3.75
3.75
6.53
4.31
8.63
06LYK965
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.
REV. DESC: NEW
REV. LTR: –
VERSION: 00
TDR: 000001003421
FILE: \AAA\00231\424
REVISED: 01:16:20 11/07/2016
BY: ENMICW1
MTL: –
BALDOR
HORZ 182–4T XPFC X306M CL I–GP C&D–CL II–GP F&G, W/DRAINS
SH 1 of 1

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS