ABB BALDOR RELIANCE

Customer information packet

IDXM7556T-C

20HP, 1770RPM, 3PH, 60HZ, 256T, 0960M, XPFC, F1
Class - CLI GP C,D; CLII GP F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/10/2026 5:06:20 AM

Specifications

Enclosure	XPFC
Frame	256T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	20.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	15
Current @ Voltage	52.000 A @ 208.0 V
	48.000 A @ 230.0 V
	24.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK

Part Detail

Revision	L
Type	AC
Mech. spec.	09G469
Base	
Status	INA/A
Elec. spec.	09WGT459
Layout	09LYG469
Eff. date	03-09-2021
CD Diagram	CD0180
Poles	04
Leads	9#10
Proprietary	False
Created date	11-20-2017

Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	24.0 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	X0960M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	25.44 IN
Power Factor	83
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed

Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP0681XPSLEV

NO.				**CC**	010A				
S/N				**TEMP CODE**	T3C				
SPEC.	09G469T459G1			**INV.TYPE**	PWM				
CAT.NO.				**C HP FR**	60	**C HP TO**	90		
HP	20			**CT HZ FROM**	15			**CT HZ TO**	60
VOLTS	230/460			**VT HZ FROM**	6			**VT HZ TO**	60
AMPS	48/24			**MAG CUR**	20.8/10.4				
RPM	1770			**MX RPM**	2700				
HZ	60	**PH**	3	**CL**	F	**NOM.EFF.**	93		
SER.F.	1.00	**DES**	A	**SL HZ**	1	**WK2**	2.62		
FRAME	256T	**RATING**	40C AMB-CONT						
	1.15SF ON SINEWAVE								

AC Induction Motor Performance Data
Record # 68068
Typical performance - not guaranteed values

Winding: 09WGT459-R009	**Type:** 0960M	**Enclosure:** XPFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			20	**Full Load Torque**	59.27 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			48/24	**Breakdown Torque**	232 LB-FT
R.P.M.			1770	**Pull-up Torque**	126 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	141 LB-FT
NEMA Design Code	A	**KVA Code**	J	**Starting Current**	198 A
Service Factor (S.F.)			1	**No-load Current**	10.4 A
NEMA Nom. Eff.	93	**Power Factor**	83	**Line-line Res. @ 25ºC**	0.33814 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	58°C
				Locked-rotor Power Factor	26.5

Load Characteristics 460 V, 60 Hz, 20 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	45	67	78	83	86	87
Efficiency	89.2	93	93.7	93.6	93.1	92.4
Speed	1793.2	1786.4	1779.1	1771.9	1763.7	1755.3
Line amperes	11.8	15	19.2	24	29.3	34.9


ABB Motors and Mechanical Inc.

WINDING # 09WGT459


20 HP 3 PH 60 HZ 1770 RPM 460 V 0960M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=232 PU=126 LR=141 LRA=198




11/10/2026 ACPERF, record # 68068


09LYG469
(922–964)
25.44
12.19
4.20
4.00
PLUG
.38 KEY
2.88 LONG
1.625
1.624
DRAIN FITTING
HW4505A02
(EA. END)
8 HOLES
ø.53
8.25
8.25
.75
10.00
4.25
11.50
13.44
12.63
6.75
2.72
45°
45°
12.96
6.25 +.00 −.06
3.25
.81
LEAD HOLE
1.25 NPT
5.00
5.00
9.49
5.75
11.50
1 PIN
HW3023E06
(EA. END)
09LYG469
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.
REV. DESC: ADDED 64 STACK
REV. LTR: C
VERSION: 03
TDR: 000001167927
FILE: \AAA\00118\343
REVISED: 04:54:40 05/12/2021
BY: ENSHAB0
MTL: –
BALDOR - RELIANCE®
HOR XPFC 254–6T–CLI GP C&D,CLII GP F&G, W/XPFC BREATHER DRN
SH 1 of 1

CD0180





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1