ABB BALDOR RELIANCE

Customer information packet

JMEWDM41906T

60M 2P TEFC HOR 256JM SP9 HOSE DOWN SE
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/1/2026 5:15:48 AM

Specifications

Enclosure	TEFC
Frame	256JM
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	20.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	NEMA PREMIUM
	UR
	CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	21.500 A @ 460.0 V
	43.000 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	S
Type	AC
Mech. spec.	39K68
Base	
Status	PRD/A
Elec. spec.	39WGX632
Layout	39LYK068
Eff. date	07-31-2025
CD Diagram	CD0005
Poles	02
Leads	9#10
Proprietary	False
Created date	10-23-2018

High Voltage Full Load Amps	21.5 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3960M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	25.06 IN
Power Factor	93
Product Family	Wash Down
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.250 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3525 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1669L									
CAT.NO.	JMEWDM41906T								
SPEC.	39K068X632G1								
HP	20								
VOLTS	230/460								
AMP	43/21.5								
RPM	3525								
FRAME	256JM	**HZ**	60			**PH**	3		
SER.F.	1.00	**CODE**	G	**DES**	A	**CLASS**	F		
NEMA-NOM-EFF	91	**PF**	93						
RATING	40C AMB-CONT								
CC	010A								
DE	6309	**ODE**	6208						
ENCL	TEFC	**SN**							
BLANK	20:1CT, 20:1VT, 1.00SF								

AC Induction Motor Performance Data
Record # 26903
Typical performance - not guaranteed values

Winding: 39WGX632-R001	**Type:** 3960M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			20	**Full Load Torque**	29.6 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			43/21.5	**Breakdown Torque**	114 LB-FT
R.P.M.			3525	**Pull-up Torque**	35.3 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	51 LB-FT
NEMA Design Code	B	**KVA Code**	G	**Starting Current**	152 A
Service Factor (S.F.)			1.15	**No-load Current**	4.75 A
NEMA Nom. Eff.	91	**Power Factor**	93	**Line-line Res. @ 25ºC**	0.437 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	75°C
S.F. Amps				**Temp. Rise @ S.F. Load**	97°C
				Locked-rotor Power Factor	27
				Rotor inertia	1.53 LB-FT2

Load Characteristics 460 V, 60 Hz, 20 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	71	88	92	93	93	92	93
Efficiency	91	93.5	93.3	92.5	91.2	89.7	91.7
Speed	3581	3562	3541	3519	3492	3465	3503
Line amperes	6.84	11.2	16.2	21.5	27.6	33.8	25.2


ABB Motors and Mechanical Inc.


WINDING # 39WGX632

20 HP 3 PH 60 HZ 3525 RPM 460 V 3960M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=114 PU=35.3 LR=51 LRA=152




39LYK068
(3924-3956) = 25.12
(3958-3964) = 26.12
5.250±.031
CHECK W/ GUAGE
T-9041
3.000±.015
.625±.015
.25
6.47
Ø12.93
Ø8.500
8.497
Ø1.3750
1.3745
1.2495
1.2490
Ø1.750
1.748
9.51
6 HOLES
Ø.53
8.25
.63
10.00
4.75
11.25
SLINGER
(EA. END)
.50-13 TAP
CL 3 R.H.
1.25 DEEP
12.07
9.93
5.99
2.50
45°
45°
12.86
6.25 +.00 -.06
3.50
.25
LEAD HOLE
1.25 N.P.T.
5.00
5.00
7.88
5.58
11.15
Ø.054
.043
Ø.054
.043
1.328
1.322
1.202
1.196
UNDERCUT DETAIL
APPLY COAT OF
SEALER TO
HOUSING BEFORE
PRESSING SEAL IN
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD DRW TO SWD
REV: M
VERSION: 09
REVISED: 08:28:33 05/23/2023
TDR: 000001208005
MODEL NO. 39LYK068
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
HORZ TEFC 254-6JM WD
39LYK068

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS