

ABB BALDOR RELIANCE III

Customer information packet

JMFSWDM23934T-E

60M 4P TEFC HOR 256JM S/P9-12 SE ENCAP

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	256JM
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	20.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA NEMA PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	24.000 A @ 460.0 V 48.000 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	24.0 a

Part Detail

Revision	N
Type	AC
Mech. spec.	39E754
Base	
Status	PRD/A
Elec. spec.	39WGY400
Layout	39LYE754
Eff. date	02-10-2025
CD Diagram	CD0180
Poles	04
Leads	9#12
Proprietary	False
Created date	05-09-2018

Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3960M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	26.68 IN
Power Factor	84
Product Family	WD All SS Encapsulated
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.250 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4427AAA05										
CAT #	JMFSWDM23934T-E			WGT		LBS				
SPEC	39E754Y400G1			ENCL	TEFC					
SER #		CC	010A	IP	69					
HP	20	MAG CUR	19.4/9.7							
VOLTS	230/460			NEMA NOM. EFF	93					
AMPS	48/24			PF	84					
RATING	40C AMB-CONT									
RPM	1765			MAX RPM	2700					
FRAME	256JM	HZ	60	CODE	J	CLASS	H			
SER.F.	1.00	SF AMP		PH	3	DES	A			
DE	6309		ODE	6309						
LUBRICATION	POLYREX EM									
ID LOGO	INV TYPE:	VPWM	CHP	60	TO	90	1.5:1			
ID LOGO	WK2	2.52	CT	30	TO	60	2:1			
ID LOGO	SL HZ	1.2	VT	6	TO	60	10:1			
YR							QR			


ABB Motors and Mechanical Inc.

WINDING # 39WGY400


Typical performance - not guaranteed values.

20 HP 3 PH 60 HZ 1765 RPM 460 V 3960M

TORQUES (LB-FT): PO=226 PU=109 LR=139 LRA=188




7/8/2026 ACPERF, record # 69070




CD0180



LOW VOLTAGE
(2D)



HIGH VOLTAGE
(1D)



NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIRO
MTL: -	© □	

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1