ABB BALDOR RELIANCE

Customer information packet

JMFSWDM3711T-E

10HP, 3500RPM, 3PH, 60HZ, 215JM, 3744M, TEFC, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/3/2026 5:46:54 AM

Specifications

Enclosure	TEFC
Frame	215JM
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	NEMA PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	23.000 A @ 208.0 V
	21.200 A @ 230.0 V
	10.600 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part Detail

Revision	T
Type	AC
Mech. spec.	37Q257
Base	
Status	PRD/A
Elec. spec.	37WGS137
Layout	37LYQ257
Eff. date	07-06-2026
CD Diagram	CD0005
Poles	02
Leads	9#14
Proprietary	False
Created date	10-13-2017

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	10.6 a
Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	L
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3744M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	21.81 IN
Power Factor	94
Product Family	WD All SS Encapsulated
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3500 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4427AAA01												
CAT #	JMFSWDM3711T-E			**WT**	189	**LBS**						
SPEC	37Q257S137G1			**ENCL**	TEFC							
SER #				**CC**	010A	**IP**	69					
HP	10			**MAG CUR**	7/3.5							
VOLTS	230/460					**NEMA NOM. EFF**	91					
AMPS	21.2/10.6					**PF**	94					
RATING	40C AMB-CONT											
RPM	3500				**MAX RPM**	5400						
FRAME	215JM	**HZ**	60	**CODE**	L	**CLASS**	H					
SER.F.	1.15	**SF AMP**	26/13			**PH**	3	**DES**	A			
DE	6309			**ODE**	6307							
LUBRICATION	POLYREX EM											
ID LOGO	**INVERTER TYPE**			**VPWM**		**CHP**	60	**TO**	90	1.5:1		
ID LOGO	**WK2**	0.4	**CT**	15	**TO**	60		4:1				
ID LOGO	**SL HZ**	1.7	**VT**	6	**TO**	60		10:1				
						QR						
YR												

AC Induction Motor Performance Data
Record # 57389
Typical performance - not guaranteed values

Winding: 37WGS137-R011	**Type:** 3744M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			10	**Full Load Torque**	15 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			21.2/10.6	**Breakdown Torque**	89.4 LB-FT
R.P.M.			3500	**Pull-up Torque**	39 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	46.5 LB-FT
NEMA Design Code	A	**KVA Code**	L	**Starting Current**	124 A
Service Factor (S.F.)			1.15	**No-load Current**	4.28 A
NEMA Nom. Eff.	91	**Power Factor**	94	**Line-line Res. @ 25ºC**	0.659 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	67°C
S.F. Amps			26/13	**Temp. Rise @ S.F. Load**	82°C
				Locked-rotor Power Factor	31.5
				Rotor inertia	0.402 lb-ft²

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	56	77	86	91	91	92	91
Efficiency	81.8	88.7	90.2	91	90.1	89.7	90.5
Speed	3579	3557	3535	3510	3486	3459	3496
Line amperes	4.99	6.82	8.93	11.3	14.2	17	13


ABB Motors and Mechanical Inc.


WINDING # 37WGS137

10 HP 3 PH 60 HZ 3500 RPM 460 V 3744M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=89.4 PU=39 LR=46.5 LRA=124




37LYQ257
717-735 = 20.62[524]
736-744 = 21.81[554]
745-750 = 22.51[572]
751-756 = 23.25[590]
4.281
4.219[108]
2.890
2.860[73]
.640
.610[16]
[6]
.26
LASER ETCHED WARNING LABEL
LASER ETCHED NAMEPLATE
[153]
6.03
10.18
[259]
.19 KEY
1.38[35] LONG
Ø8.500
8.497
Ø8.97
Ø 1.0000
.9995
Ø .8745
.8740
Ø 1.250
1.248
.38-16 R.H. TAP
CLS 3 .88[99] DEEP
4 DRAIN HOLES
W/PLUGS
90° APART (EACH END)
6 HOLES
Ø.38[10]
5.50[140]
.50[13]
7.00[178]
[114]
4.50
8.00[203]
9.56 [242]
9.24
[235]
5.09
[129]
45°
45°
TOP OF WARNING LABEL
TOP OF NAMEPLATE
1.99
[51]
9.99
[254]
5.22
[133]
4 HOLES
.50-13 TAP
.88 DEEP
Ø7.25 [184] B.C.
LEAD HOLE
1.00 N.P.T.
4.25[108]
4.25[108]
7.38[179]
4.75[121]
9.50[241]
.177±.020
(EA. END)
6307
FRONT END DETAIL
SNAP RING
BRG. RETAINER
LIP SEAL
(EA. END)
AXIAL FACE SEAL
(EA. END)
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD DIM TO AXIAL SEAL LOCATION
REV: F
VERSION: 06
REVISED: 07:33:44 07/28/2026
TDR: 000001276312
MODEL NO. 37LYQ257
REF: -
BY: USALMAZ
B
BALDOR - RELIANCE®
STD HORZ 213-5JM TEFC M WD11/12
37LYQ257

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS