

BALDOR • RELIANCE

Customer information packet

JML1508T

5HP, 1745RPM, 1PH, 60HZ, 213JM, 3727L, OPSB, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	213JM
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	5.000 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	27.000 A @ 230.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	77.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	27.0 a
Insulation Class	B
Inverter Code	Not Inverter

Part detail

Revision	Y
Type	AC
Mech. spec.	37K238
Base	
Status	PRD/A
Elec. spec.	37WGT912
Layout	37LYK238
Eff. date	05-13-2024
CD Diagram	CD0017A01
Poles	04
Leads	2#12 A PH,2#14 B PH
Proprietary	False
Created date	06-22-2006

KVA Code	G
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	2 @ 12 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3727L
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.19 IN
Power Factor	78
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	Included
Service Factor	1.15
Shaft Diameter	1.000 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Nameplate

NP1256L									
CAT.NO.	JML1508T								
SPEC.	37K238T912								
HP	5								
VOLTS	230								
AMP	27								
RPM	1725								
FRAME	213JM		HZ	60		PH	1		
SER.F.	1.15	CODE	G	DES	L	CLASS	B		
NEMA-NOM-EFF	77	PF	78						
RATING	40C AMB-CONT								
CC									
DE	6309		ODE	6206					
ENCL	OPSB	SN							

AC Induction Motor Performance Data

Record # 37146

Typical performance - not guaranteed values

Winding: 37WGT912-R001		Type: 3727L		Enclosure: OPSB	
Nameplate Data			230 V, 60 Hz: Single Voltage Motor		
Rated Output (HP)	5	Full Load Torque	15.3 LB-FT		
Volts	230	Start Configuration	direct on line		
Full Load Amps	27	Breakdown Torque	43 LB-FT		
R.P.M.	1725	Pull-up Torque	30.8 LB-FT		
Hz	60	Locked-rotor Torque	46.9 LB-FT		
NEMA Design Code	L	Starting Current	132 A		
Service Factor (S.F.)	1.15	No-load Current	14.3 A		
NEMA Nom. Eff.	77	Line-line Res. @ 25°C	0.352 Ω A Ph 1.48 Ω B Ph		
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	68°C		
S.F. Amps		Temp. Rise @ S.F. Load	81°C		

Load Characteristics 230 V, 60 Hz, 5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	38	58	72	78	81	82	80
Efficiency	71.2	79.4	78	77.3	74	67.1	75.3
Speed	1781	1766	1749	1728	1699	1653	1711
Line amperes	14.9	17.5	21.9	27.1	33.9	44.4	31.2


ABB Motors and Mechanical Inc.

WINDING # 37WGT912


Typical performance - not guaranteed values.

5 HP 1 PH 60 HZ 1725 RPM 230 V 3727L


TORQUES (LB-FT): PO=43 PU=30.8 LR=46.9 LRA=132



7/23/2024 ACPERF, record # 37146



CD0017A01



	LINE A	LINE B
STD	1,8	4,5
OPP	1,5	4,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: B	BY: JLP	REVISED: 04/08/99 1:18	TDR: 0178636
10VZ1000		FILE: AAA00007513	MDL: -
CD0017A01		MTL: -	

BALDOR ELECTRIC Co.

TYPE L, SV, REV, 4 LEADS

CD0017A01