



---

# Customer information packet

## JML1510T

7.5HP, 1750RPM, 1PH, 60HZ, 3740LC, N

Class - None

Division - Not Applicable

## Specifications

Enclosure	OPEN
Frame	213JM
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	7.500 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	33.000 A @ 230.0 V 35.500 A @ 208.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	85.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	33.0 a
Insulation Class	F
Inverter Code	Not Inverter

## Part detail

Revision	H
Type	AC
Mech. spec.	37K266
Base	
Status	PRD/A
Elec. spec.	37WGW003
Layout	37LYK266
Eff. date	05-13-2024
CD Diagram	CD0017A02
Poles	04
Leads	2#10 A PH,2#14 B PH
Proprietary	False
Created date	11-20-2020

<b>KVA Code</b>	E
<b>Lifting Lugs</b>	No Lifting Lugs
<b>Locked Bearing Indicator</b>	Locked Bearing
<b>Motor Lead Quantity/Wire Size</b>	2 @ 10 AWG, A PH
<b>Motor Lead Termination</b>	Flying Leads
<b>Motor Standards</b>	NEMA
<b>Motor Type</b>	3740LC
<b>Mounting Arrangement</b>	F1
<b>Number of Poles</b>	4
<b>Overall Length</b>	19.31 IN
<b>Power Factor</b>	87
<b>Product Family</b>	General Purpose
<b>Pulley End Bearing Type</b>	Ball
<b>Pulley Face Code</b>	C-Face
<b>Pulley Shaft Indicator</b>	Tapped & Key
<b>Rodent Screen</b>	Included
<b>Service Factor</b>	1.15
<b>Shaft Diameter</b>	0.875 IN
<b>Shaft Ground Indicator</b>	No Shaft Grounding
<b>Shaft Rotation</b>	Reversible
<b>Shaft Slinger Indicator</b>	Shaft Slinger
<b>Speed</b>	1750 rpm
<b>Speed Code</b>	Single Speed
<b>Starting Method</b>	Direct on line
<b>Thermal Device - Bearing</b>	None
<b>Thermal Device - Winding</b>	None
<b>Vibration Sensor Indicator</b>	No Vibration Sensor
<b>Winding Thermal 1</b>	None
<b>Winding Thermal 2</b>	None

**Nameplate**

<b>NP1256L</b>									
<b>CAT.NO.</b>	JML1510T								
<b>SPEC.</b>	37K266W003G1								
<b>HP</b>	7.5								
<b>VOLTS</b>	230								
<b>AMP</b>	33								
<b>RPM</b>	1750								
<b>FRAME</b>	215JM		<b>HZ</b>	60		<b>PH</b>	1		
<b>SER.F.</b>	1.15	<b>CODE</b>	E	<b>DES</b>	L	<b>CLASS</b>	F		
<b>NEMA-NOM-EFF</b>	85.5	<b>PF</b>	87						
<b>RATING</b>	40C AMB-CONT								
<b>CC</b>									
<b>DE</b>	6309		<b>ODE</b>	6206					
<b>ENCL</b>	OPEN	<b>SN</b>							

**AC Induction Motor Performance Data**

Record # 85588

Typical performance - not guaranteed values

Winding: 37WGW003-R001		Type: 3740LC	Enclosure: OPSB	
<b>Nameplate Data</b>		<b>230 V, 60 Hz: Single Voltage Motor</b>		
Rated Output (HP)	7.5	Full Load Torque	22.52 LB-FT	
Volts	230	Start Configuration	direct on line	
Full Load Amps	33	Breakdown Torque	49.18 LB-FT	
R.P.M.	1750	Pull-up Torque	39.04 LB-FT	
Hz	60 Phase	1	Locked-rotor Torque	49.82 LB-FT
NEMA Design Code	L KVA Code	E	Starting Current	181 A
Service Factor (S.F.)		1.15	No-load Current	11.57 A
NEMA Nom. Eff.	85.5 Power Factor	87	Line-line Res. @ 25°C	0.318 Ω A Ph 1.82 Ω B Ph
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load	73°C
S.F. Amps			Temp. Rise @ S.F. Load	91°C
			Locked-rotor Power Factor	76.5
			Rotor inertia	0.984 lb-ft <sup>2</sup>

**Load Characteristics 230 V, 60 Hz, 7.5 HP**

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	58	77	85	89	90	90	90
Efficiency	77.7	85	86	84.4	81.3	77.2	82.5
Speed	1788	1777	1765	1751	1732	1711	1740
Line amperes	13.69	18.43	24.76	32.37	41.61	52.25	37.9


ABB Motors and Mechanical Inc.

WINDING # 37WGW003


Typical performance - not guaranteed values.

7.5 HP 1 PH 60 HZ 1750 RPM 230 V 3740LC


TORQUES (LB-FT): PO=49.18 PU=39.04 LR=49.82 LRA=181



8/15/2024 ACPERF, record # 85588



CD0017A02



	LINE A	LINE B
STD	1,8	4,5
OPP	1,5	4,8

**NOTES:**

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0017A02

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: B	BY: JLP	REVISED: 04/09/99 11:30	TDR: 0178636
CD0017A02		FILE: AAA00007514	MDL: -
		MTL: -	

**BALDOR ELECTRIC Co.**

TYPE LC, SV, REV, 4 LEADS