

ABB BALDOR RELIANCE III

Customer information packet

JPDRX18344T-5

3HP, 1755RPM, 3PH, 60HZ, 182JP, XPFC, F1

Class - CLI GP C,D

Division - Division I

Specifications

Enclosure	XPFC
Frame	182JP
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	3.300 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	3.3 a
Insulation Class	F
Inverter Code	Inverter Duty

Part Detail

Revision	B
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	06WGX319
Layout	06LYH458
Eff. date	02-28-2024
CD Diagram	CD0006
Poles	04
Leads	3#16
Proprietary	False
Created date	08-02-2019

IP Rating	NONE
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0632M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	22.09 IN
Power Factor	77
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1755 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1401XPSLEV											
NO.						CC	010A				
S/N						TEMP CODE		T3C			
SPEC.	06-0000-0194					INV.TYPE		PWM			
CAT.NO.	JPDRX18344T-5					C HP FR	60	C HP TO	90		
HP	3					CT HZ FROM	6	CT HZ TO	60		
VOLTS	575					VT HZ FROM	6	VT HZ TO	60		
AMPS	3.3			MAG CUR		1.7					
RPM	1755			MX RPM		2700					
HZ	60	PH	3	CL	F	NOM.EFF.	89.5				
SER.F.	1.00	DES	B	SL HZ	1.5	WK2	0.3				
FRAME	182JP	RATING		40C AMB-CONT							
	55C AMB @ 1.0 SF										
	1.15 SF ON SINEWAVE					NEMA MG-1 PT 5,IP55					

AC Induction Motor Performance Data

Record # 77531

Typical performance - not guaranteed values

Winding: 06WGX319-R028			Type: 0632M		Enclosure: XPFC		
Nameplate Data			575 V, 60 Hz: Single Voltage Motor				
Rated Output (HP)		3	Full Load Torque		9.05 LB-FT		
Volts		575	Start Configuration		direct on line		
Full Load Amps		3.3	Breakdown Torque		33 LB-FT		
R.P.M.		1755	Pull-up Torque		18.2 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		20.3 LB-FT	
NEMA Design Code		B	KVA Code	J	Starting Current		23.8 A
Service Factor (S.F.)		1	No-load Current		1.7 A		
NEMA Nom. Eff.		89.5	Power Factor	77	Line-line Res. @ 25°C		6.2 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		35°C	
				Locked-rotor Power Factor		41.5	
				Rotor inertia		0.298 LB-FT2	

Load Characteristics 575 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	38	59	71	77	81	83
Efficiency	83	88.4	89.7	89.6	89	87.6
Speed	1790	1779	1769	1757	1744	1730
Line amperes	1.86	2.22	2.71	3.27	3.92	4.69


ABB Motors and Mechanical Inc.


WINDING # 06WGX319

Typical performance - not guaranteed values.

3 HP 3 PH 60 HZ 1755 RPM 575 V 0632M

TORQUES (LB-FT): PO=33 PU=18.2 LR=20.3 LRA=23.8





CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10:24:49 02/19/2019

BY: ENBRIRO

MTL: -


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1