

ABB BALDOR RELIANCE III

Customer information packet

JM3154

1.5HP, 1725RPM, 3PH, 60HZ, 56J, 3520M, OPEN, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	OPEN
Frame	56J
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ 208.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	5.600 A @ 230.0 V 5.200 A @ 208.0 V 2.800 A @ 460.0 V
Design Code	B
Drip Cover	Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	77.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Drip Cover Mounting
Front Shaft Indicator	None

Part Detail

Revision	P
Type	AC
Mech. spec.	34F038
Base	
Status	PRD/A
Elec. spec.	34WGX116
Layout	34LYF038
Eff. date	08-10-2026
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	01-01-0001

Heater Indicator	No Heater
High Voltage Full Load Amps	2.8 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	M
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3432M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.72 IN
Power Factor	65
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Ext Thread
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L											
CAT.NO.	JM3154										
SPEC.	34F038X116G1										
HP	1.5										
VOLTS	208-230/460										
AMP	5.2-5.6/2.8										
RPM	1725										
FRAME	56J		HZ	60			PH	3			
SER.F.	1.15		CODE	M	DES	B	CLASS	B			
NEMA-NOM-EFF	77		PF	65							
RATING	40C AMB-CONT										
CC											
DE	6203		ODE	6203							
ENCL	OPEN		SN								

AC Induction Motor Performance Data

Record # 20837

Typical performance - not guaranteed values

Winding: 34WGX116-R002			Type: 3432M		Enclosure: OPEN		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		1.5	Full Load Torque		4.56 LB-FT		
Volts		208-230/460	Start Configuration		direct on line		
Full Load Amps		5.2-5.6/2.8	Breakdown Torque		21.7 LB-FT		
R.P.M.		1725	Pull-up Torque		17.8 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		19.3 LB-FT	
NEMA Design Code		B	KVA Code	M	Starting Current		19.6 A
Service Factor (S.F.)		1.15		No-load Current		2.17 A	
NEMA Nom. Eff.		77	Power Factor	65	Line-line Res. @ 25°C		8.69 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		70°C	
S.F. Amps				Temp. Rise @ S.F. Load		80°C	
				Locked-rotor Power Factor		54	
				Rotor inertia		0.0762 LB-FT2	

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	27	43	55	65	72	77	69
Efficiency	58.7	72.3	76.6	78.1	77.9	76.8	78
Speed	1780	1762	1744	1724	1701	1677	1710
Line amperes	2.16	2.3	2.51	2.8	3.14	3.54	3


ABB Motors and Mechanical Inc.

WINDING # 34WGX116


Typical performance - not guaranteed values.

1.5 HP 3 PH 60 HZ 1725 RPM 460 V 3432M

TORQUES (LB-FT): PO=21.7 PU=17.8 LR=19.3 LRA=19.6



34LYF038



CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: CHG'D BAND TO 34SB3981, SHAFT TO 34SH3C22

REV: L VERSION: 04 REVISED: 08:37:38 07/28/2026 TDR: 000001281747

34LYF038

MODEL NO. 34LYF038

BY: ENJEFD0

REF: -

BALDOR - RELIANCE®

STD VERT 56J OPEN 34M W/DRIP CVR

34LYF038

