ABB BALDOR RELIANCE

Customer information packet

JXL050522A

.5HP, 3450RPM, 1PH, 60HZ, 56J, 3513L, XPFC, F1
Class - CLI GP D; CLII GP F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/17/2026 1:43:32 AM

Specifications

Enclosure	XPFC
Frame	56J
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	.500 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CSA
	UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.900 A @ 230.0 V
	7.800 A @ 115.0 V
Design Code	N
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	55.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	3.9 a
Insulation Class	B

Part Detail

Revision	D
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	35WG0763
Layout	35LYE382
Eff. date	05-01-2024
CD Diagram	CD0008
Poles	02
Leads	6#18,1#16 #4TH
Proprietary	False
Created date	03-29-2021

Inverter Code	Not Inverter
IP Rating	NONE
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3513L
Mounting Arrangement	F1
Number of Poles	2
Overall Length	14.78 IN
Power Factor	69
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 1 Location	EP
Winding Thermal 2	None

Nameplate

NP0016XPSL							
NO.			**CC**				
SER. #							
SPEC	35-0000-1063						
CAT.NO.	JXL050522A						
H.P.	.5		**T. CODE**		T3C		
VOLTS	115/230						
AMPS	7.8/3.9						
R.P.M.	3450						
HZ	60	**PH**	1		**CLASS**	B	
SER.F.	1.00		**DES**	N	**CODE**	L	
RATING	40C AMB-CONT						
FRAME	56J				**NEMA NOM. EFF**	55	
		PF	69				
BLANK	NEMA MG-1 PART 5, IP54						

AC Induction Motor Performance Data
Record # 20947
Preliminary Data Sheet

Winding: 35WG0763-R002	**Type:** 3513L	**Enclosure:** XPFC

Nameplate Data				**115 V, 60 Hz: Low Voltage Connection**	
Rated Output (HP)			.5	**Full Load Torque**	0.751 LB-FT
Volts			115/230	**Start Configuration**	direct on line
Full Load Amps			7.8/3.9	**Breakdown Torque**	1.85 LB-FT
R.P.M.			3450	**Pull-up Torque**	1.84 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	2.9 LB-FT
NEMA Design Code	N	**KVA Code**	L	**Starting Current**	41.6 A
Service Factor (S.F.)			1	**No-load Current**	5.99 A
NEMA Nom. Eff.	55	**Power Factor**	69	**Line-line Res. @ 25ºC**	1.21 Ω A Ph 3.33 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	41°C
S.F. Amps				**Temp. Rise @ S.F. Load**	47°C

Load Characteristics 115 V, 60 Hz, 0.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	44	55	64	71	76	80
Efficiency	30.1	44.9	53	57.9	60.3	61.2
Speed	3557	3534	3508	3480	3447	3408
Line amperes	6.24	6.61	7.18	7.86	8.75	9.76


ABB Motors and Mechanical Inc.

WINDING # 35WG0763


0.5 HP 1 PH 60 HZ 3450 RPM 115 V 3513L

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=1.85 PU=1.84 LR=2.9 LRA=41.6



11/17/2026 ACPERF, record # 20947


35LYE382
510-520 = 14.78
521-528 = 15.66
529-535 = 16.54
536-546 = 17.92
2.57
1.88±.03
CHECK W/GAGE
T-6338
.12
.69
Ø7.19
PLUG
.09
SLOT
.16
Ø6.45
X-PROOF NAMEPLATE
BALDOR
PT. NO. 35CB3500
Ø4.500
4.497
Ø.6250
.6245
.44-20 UNF
2A RH THRD
4.72
6.97
45°
45°
LEAD HOLE
.50 N.P.T.
5.39
4 HOLES
.38-16 TAP
.56 DEEP
Ø5.88 B.C.
.09
(.08 MIN)
.44
(.38 MIN)
.0015 MAX.
CLEARANCE
(EA. END)
.006
.004
1.08
(1.00 MIN)
PULLEY END DETAIL
REV. DESC: CREATE SW DWG FOR 2D TO 3D CONVERSION
REV: H
VERSION: 03
REVISED: 12:31:56 08/16/2019
TDR: 000001112747
MODEL NO. 35LYE382
REF: -
BY: ENSTEK0
Material: -
B
BALDOR - RELIANCE®
VERT 56J XPFC 35L W/CL I GP D, CL II GP F&G & ATO
35LYE382

CD0008



	LINE A	LINE B	JOIN	JOIN
HIGH STD	1	4	2,3,8	J,5
HIGH OPP	1	4	2,3,5	J,8
LOW STD	1,3,8	4	—	2,J,5
LOW OPP	1,3,5	4	—	2,J,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0008

REV. DESC: REMOVE 2—TERMINAL THERMAL DETAIL, SEE CD0008A02			BALDOR ELECTRIC Co.
REV. LTR: F	VERSION: 01	TDR: 000000360649	
CD0008	FILE: \AAA\00007\408	REVISED: 10:56:54 04/18/2005	TYPE L, DV, REV, THERMAL, 7 LEADS
	MTL: —	BY: ENJOEP0	