

ABB BALDOR RELIANCE III

Customer information packet

KENM3535

.33HP, 1185RPM, 3PH, 60HZ, 56C, 3522M, TENV, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TENV
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.330 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	C UR US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.800 A @ 230.0 V 1.700 A @ 208.0 V .900 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	78.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	0.9 a
Insulation Class	F

Part Detail

Revision	D
Type	AC
Mech. spec.	35E010
Base	
Status	PRD/A
Elec. spec.	35WGG338
Layout	35LYE010
Eff. date	01-05-2026
CD Diagram	CD0005
Poles	06
Leads	9#18
Proprietary	False
Created date	02-23-2023

Inverter Code	Inverter Ready
KVA Code	M
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3522M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	12.06 IN
Power Factor	57
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1185 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2116L												
CAT.NO.	KENM3535											
SPEC.	35E010G338G2											
HP	.33											
VOLTS	230/460											
AMP	1.8/.9											
RPM	1185											
FRAME	56C				HZ		60		PH		3	
SER.F.	1.15		CODE	M	DES		B	CL	F			
NEMA-NOM-EFF	78.5		PF	57								
RATING	40C AMB-CONT											
CC												
DE	6205		ODE		6203							
ENCL	TENV		SN									
	SFA 2.2/1.1											

AC Induction Motor Performance Data

Record # 87761

Preliminary Data Sheet

Winding: 35WGG338-R003			Type: 3522M		Enclosure: TENV	
Nameplate Data				460 V, 60 Hz: High Voltage Connection		
Rated Output (HP)		.33		Full Load Torque		1.47 LB-FT
Volts		230/460		Start Configuration		direct on line
Full Load Amps		1.8/.9		Breakdown Torque		8.81 LB-FT
R.P.M.		1185		Pull-up Torque		4.83 LB-FT
Hz	60	Phase	3	Locked-rotor Torque		5.16 LB-FT
NEMA Design Code		B	KVA Code	Starting Current		6.64 A
Service Factor (S.F.)		1.15		No-load Current		0.789 A
NEMA Nom. Eff.		78.5	Power Factor	Line-line Res. @ 25°C		30 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		57°C
S.F. Amps		2.2/1.1		Temp. Rise @ S.F. Load		61°C
				Locked-rotor Power Factor		50.7
				Rotor inertia		0.16 lb-ft²

Load Characteristics 460 V, 60 Hz, 0.33 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	19	28	37	44	51	56	48
Efficiency	53.9	68.2	73.7	77.8	79.2	79.4	78.6
Speed	1195	1193	1189	1186	1182	1177	1184
Line amperes	0.794	0.825	0.861	0.905	0.965	1.04	0.941

ABB Motors and Mechanical Inc.

WINDING # 35WGG338

Typical performance - not guaranteed values.

0.33 HP 3 PH 60 HZ 1185 RPM 460 V 3522M

TORQUES (LB-FT) : PO=8.81 PU=4.83 LR=5.16 LRA=6.64





