

BALDOR • RELIANCE

Customer information packet

L1208-50

.5 /KW .37, 2870RPM, 1PH, 50HZ, 48, 3420LC, OP

Class - None

Division - Not Applicable

Specifications

Enclosure	OPEN
Frame	48
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	.500 HP @ 50 HZ
Phase	1
Synchronous Speed @ Frequency	3000 RPM @ 50 HZ
Voltage @ Frequency	110.0 V @ 50 HZ 220.0 V @ 50 HZ
Agency Approvals	UR CE CSA WEEE
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Design Code	N
Drip Cover	No Drip Cover
Duty Rating	CONT
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
Insulation Class	B
Inverter Code	Not Inverter
Lifting Lugs	No Lifting Lugs

Part detail

Revision	D
Type	AC
Mech. spec.	34F351
Base	
Status	PRD/A
Elec. spec.	34WGR748
Layout	34LYF351
Eff. date	10-25-2024
CD Diagram	CD0055
Poles	02
Leads	6#18
Proprietary	False
Created date	02-14-2023

Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3420LC
Mounting Arrangement	F1
Number of Poles	2
Overall Length	9.76 IN
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.500 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	2850 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1372L									
CAT.NO.	L1208-50								
SPEC.	34F351R748G1								
HP	.5 /KW .37								
VOLTS	110/220								
AMP	4.8/2.4								
R.P.M. (1/MIN)	2870								
FRAME	48	HZ	50	PH	1				
SER.F.	1.25	CODE	J	DES	-	CL	B		
NEMA-NOM-EFF	74	PF	91						
RATING	40C AMB-S1 CONT								
CC	IP23 12KG IC01								
DE	6203	ODE	6203						
ENCL	OPEN	SN							
	SFA 6/3								

AC Induction Motor Performance Data

Record # 101550

Typical performance - not guaranteed values

Winding: 34WGR748-R001		Type: 3420LC	Enclosure: OPEN	
Nameplate Data			220 V, 50 Hz: High Voltage Connection	
Rated Output (KW)	.37	Full Load Torque	0.9146 LB-FT	
Volts	110/220	Start Configuration	direct on line	
Full Load Amps	4.8/2.4	Breakdown Torque	2.85 LB-FT	
R.P.M.	2870	Pull-up Torque	1.51 LB-FT	
Hz	50 Phase	Locked-rotor Torque	2.84 LB-FT	
NEMA Design Code	- KVA Code	Starting Current	16.5 A	
Service Factor (S.F.)	1.25	No-load Current	1.17 A	
NEMA Nom. Eff.	74 Power Factor	Line-line Res. @ 25°C	5.1212 Ω A Ph 3.7762 Ω B Ph	
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	19°C	
S.F. Amps	6/3	Temp. Rise @ S.F. Load	24°C	

Load Characteristics 220 V, 50 Hz, 0.37 KW

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	66	81	88	91	94	95	94
Efficiency	50.2	67.1	73.8	76.7	76.6	74.9	76.6
Speed	2962.8	2936.8	2904.8	2874.3	2835	2788.6	2835
Line amperes	1.32	1.59	1.96	2.42	2.94	3.56	2.94


ABB Motors and Mechanical Inc.

WINDING # 34WGR748


Typical performance - not guaranteed values.

0.37 KW 1 PH 50 HZ 2870 RPM 220 V 3420LC


TORQUES (LB-FT): PO=2.85 PU=1.51 LR=2.84 LRA=16.5



12/2/2024 ACPERF, record # 101550



CD0055



CD0055

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: D	BY: JLP	REVISED: 04/08/99 1:17	TDR: 0178636
C00000		FILE: AAA00007414	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

TYPE LC, DV, REV, 6 LEADS