



Customer information packet

JML1512T

10HP, 1725RPM, 1PH, 60HZ, 215JM, 3744LC, ODTF

Class - None

Division - Not Applicable

Specifications

Enclosure	ODTF
Frame	215JM
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	10.000 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
XP Class and Group	None
XP Division	Not Applicable
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	45.000 A @ 208.0 V 41.000 A @ 230.0 V
Design Code	L
Drip Cover	Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	84.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Drip Cover Mounting
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	41.0 a
Insulation Class	F

Part detail

Revision	Z
Type	AC
Mech. spec.	37F842
Base	
Status	PRD/A
Elec. spec.	37WGY497
Layout	37LYF842
Eff. date	05-10-2024
CD Diagram	CD0086
Poles	04
Leads	2#8 A PH,2#14 B PH
Proprietary	False
Created date	01-01-0001

Inverter Code	Not Inverter
KVA Code	F
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Cap Box
Motor Lead Quantity/Wire Size	2 @ 8 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3744LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	20.95 IN
Power Factor	94
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	Included
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.	JML1512T								
SPEC.	37F842Y497								
HP	10								
VOLTS	230								
AMP	41								
RPM	1725								
FRAME	215JM		HZ	60		PH	1		
SER.F.	1.15	CODE	F	DES	L	CLASS	F		
NEMA-NOM-EFF	84	PF	94						
RATING	40C AMB-CONT								
CC									
DE	6309		ODE	6206					
ENCL	ODTF	SN							

AC Induction Motor Performance Data

Record # 34220

Typical performance - not guaranteed values

Winding: 37WGY497-R001		Type: 3744LC	Enclosure: ODTF	
Nameplate Data			230 V, 60 Hz: Single Voltage Motor	
Rated Output (HP)	10	Full Load Torque	30.3 LB-FT	
Volts	230	Start Configuration	direct on line	
Full Load Amps	41	Breakdown Torque	78.7 LB-FT	
R.P.M.	1725	Pull-up Torque	57.9 LB-FT	
Hz	60	Phase	1	Locked-rotor Torque
NEMA Design Code	L	KVA Code	F	Starting Current
Service Factor (S.F.)	1.15	Power Factor	94	No-load Current
NEMA Nom. Eff.	84	Rating - Duty	40C AMB-CONT	Line-line Res. @ 25°C
S.F. Amps		S.F. Amps		Temp. Rise @ Rated Load
				Temp. Rise @ S.F. Load

Load Characteristics 230 V, 60 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	80	92	95	95	94	92	94
Efficiency	75.1	84.6	85.8	83.9	79.7	74.8	81.4
Speed	1785.6	1770.4	1753.1	1728.9	1700	1666.3	1712
Line amperes	13.5	20.6	29.7	40.8	53.9	70.5	48.7


ABB Motors and Mechanical Inc.

WINDING # 37WGY497


Typical performance - not guaranteed values.

10 HP 1 PH 60 HZ 1725 RPM 230 V 3744LC


TORQUES (LB-FT): PO=78.7 PU=57.9 LR=69.1 LRA=225



5/22/2024 ACPERF, record # 34220



CD0086



REV. DESC: ADDED CK TO PLANT CODE			
REV. LTR: F	BY: JD	REVISED: 16:01:12 01/07/2002	TDR: 259409
980000		FILE: AAA00026904	REF: CD0086
		MTL: -	

BALDOR ELECTRIC Co.

TYPE L OR LC, SV, REV, 4 LEADS, CAPS MAY BE SEP MTD

CD0086