

**BALDOR • RELIANCE**

---

# Customer information packet

## L1317-50

2/1.5KW, 2910RPM, 1PH, 50HZ, 56, 3536LC, OPEN

Class - None

Division - Not Applicable

## Specifications

Enclosure	OPEN
Frame	56
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	1.500 KW @ 50 HZ
Phase	1
Synchronous Speed @ Frequency	3000 RPM @ 50 HZ
Voltage @ Frequency	220.0 V @ 50 HZ
Agency Approvals	C UR US WEEE UKCA CURUS CE
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	8.100 A @ 220.0 V
Design Code	-
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	84.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	8.1 a

## Part detail

Revision	D
Type	AC
Mech. spec.	35M497
Base	
Status	PRD/A
Elec. spec.	35WGG773
Layout	35LYM497
Eff. date	05-14-2024
CD Diagram	CD0017A02
Poles	02
Leads	4#14 A PH
Proprietary	False
Created date	05-25-2023

<b>Insulation Class</b>	F
<b>Inverter Code</b>	Not Inverter
<b>KVA Code</b>	J
<b>Lifting Lugs</b>	No Lifting Lugs
<b>Locked Bearing Indicator</b>	No Locked Bearing
<b>Motor Lead Quantity/Wire Size</b>	4 @ 14 AWG, A PH
<b>Motor Lead Termination</b>	Flying Leads
<b>Motor Standards</b>	NEMA
<b>Motor Type</b>	3536LC
<b>Mounting Arrangement</b>	F1
<b>Number of Poles</b>	2
<b>Overall Length</b>	14.32 IN
<b>Power Factor</b>	98
<b>Product Family</b>	General Purpose
<b>Pulley End Bearing Type</b>	Ball
<b>Pulley Face Code</b>	Standard
<b>Pulley Shaft Indicator</b>	Standard
<b>Rodent Screen</b>	None
<b>RoHS Status</b>	ROHS COMPLIANT
<b>Service Factor</b>	1.15
<b>Shaft Diameter</b>	0.625 IN
<b>Shaft Ground Indicator</b>	No Shaft Grounding
<b>Shaft Rotation</b>	Reversible
<b>Shaft Slinger Indicator</b>	No Slinger
<b>Speed</b>	2910 rpm
<b>Speed Code</b>	Single Speed
<b>Starting Method</b>	Direct on line
<b>Thermal Device - Bearing</b>	None
<b>Thermal Device - Winding</b>	None
<b>Vibration Sensor Indicator</b>	No Vibration Sensor
<b>Winding Thermal 1</b>	None
<b>Winding Thermal 2</b>	None

**Nameplate**

<b>NP1372L</b>										
<b>CAT.NO.</b>	L1317-50									
<b>SPEC.</b>	35M497G773G1									
<b>HP</b>	2/1.5KW									
<b>VOLTS</b>	220									
<b>AMP</b>	8.1									
<b>R.P.M. (1/MIN)</b>	2910									
<b>FRAME</b>	56	<b>HZ</b>	50	<b>PH</b>	1					
<b>SER.F.</b>	1.15	<b>CODE</b>	J	<b>DES</b>	-	<b>CL</b>	F			
<b>NEMA-NOM-EFF</b>	84	<b>PF</b>	98							
<b>RATING</b>	40C AMB-S1 CONT									
<b>CC</b>	IP22 KG27 IC01									
<b>DE</b>	6205	<b>ODE</b>	6203							
<b>ENCL</b>	OPEN	<b>SN</b>								

**Accessories**

<b>Part number</b>	<b>Description</b>	<b>Multiplier</b>
35-8764	C FACE KIT	A8
35EP1604A01SP	D-FLANGE KIT	A8

**AC Induction Motor Performance Data**

Record # 101571

Typical performance - not guaranteed values

Winding: 35WGG773-R001		Type: 3536LC	Enclosure: OPEN	
<b>Nameplate Data</b>			<b>220 V, 50 Hz: Single Voltage Motor</b>	
Rated Output (KW)	1.5	Full Load Torque	3.626 LB-FT	
Volts	220	Start Configuration	direct on line	
Full Load Amps	8.1	Breakdown Torque	11.1 LB-FT	
R.P.M.	2910	Pull-up Torque	7.34 LB-FT	
Hz	50	Phase	1	Locked-rotor Torque
NEMA Design Code	-	KVA Code	J	Starting Current
Service Factor (S.F.)	1.15			No-load Current
NEMA Nom. Eff.	84	Power Factor	98	Line-line Res. @ 25°C
Rating - Duty	40C	AMB-CONT		Temp. Rise @ Rated Load
S.F. Amps				Temp. Rise @ S.F. Load
				0.93588 Ω A Ph 2.4611 Ω B Ph
				28°C
				34°C

**Load Characteristics 220 V, 50 Hz, 1.5 KW**

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	95	98	98	98	98	98	98
Efficiency	69	81.6	85.1	85.7	84.8	83	85.2
Speed	2977.6	2959.7	2939.2	2917	2891.9	2862.3	2902
Line amperes	2.61	4.27	6.13	8.09	10.2	12.6	9.36


ABB Motors and Mechanical Inc.

WINDING # 35WGG773


Typical performance - not guaranteed values.

1.5 KW 1 PH 50 HZ 2910 RPM 220 V 3536LC

TORQUES (LB-FT): PO=11.1 PU=7.34 LR=10 LRA=68.8




8/11/2024 ACPERF, record # 101571





CD0017A02



	LINE A	LINE B
STD	1,8	4,5
OPP	1,5	4,8

**NOTES:**

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0017A02

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: B	BY: JLP	REVISED: 04/09/99 11:30	TDR: 0178636
CD0017A02		FILE: AAA00007514	MDL: -
		MTL: -	

**BALDOR ELECTRIC Co.**

TYPE LC, SV, REV, 4 LEADS