ABB BALDOR RELIANCE

Customer information packet

L1407

1HP, 1140RPM, 1PH, 60HZ, 184, 3628L, OPEN, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/17/2026 10:59:58 PM

Specifications

Enclosure	ODP
Frame	184
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	1.000 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	RG
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	8.400 A @ 208.0 V
	8.000 A @ 230.0 V
	16.000 A @ 115.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	65.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	AC
Type	AC
Mech. spec.	36D011
Base	
Status	NLA/A
Elec. spec.	36WG0988
Layout	36LYD011
Eff. date	04-08-2016
CD Diagram	CD0001
Poles	06
Leads	6#16
Proprietary	False
Created date	01-01-0001

High Voltage Full Load Amps	8.0 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3628L
Mounting Arrangement	F1
Number of Poles	6
Overall Length	14.13 IN
Power Factor	62
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1140 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.									
SPEC.	36D11-988								
HP	1								
VOLTS	115/230								
AMP	16/8								
RPM	1140								
FRAME	184	**HZ**	60			**PH**	1		
SER.F.	1.15	**CODE**	K	**DES**	L	**CLASS**	B		
NEMA-NOM-EFF	65	**PF**	62						
RATING	40C AMB-CONT								
CC									
DE	6206	**ODE**	6205						
ENCL	OPEN	**SN**							

Accessories

Part number	Description	Multiplier
36-486	C FACE KIT	A8
36EP1405A09SP	D-FLANGE KIT	

AC Induction Motor Performance Data
Record # 10497
Typical performance - not guaranteed values

Winding: 36WG0988-R001	**Type:** 3628L	**Enclosure:** OPEN

Nameplate Data				**230 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			1	**Full Load Torque**	4.5 LB-FT
Volts			115/230	**Start Configuration**	direct on line
Full Load Amps			16/8	**Breakdown Torque**	11 LB-FT
R.P.M.			1140	**Pull-up Torque**	10.5 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	12.8 LB-FT
NEMA Design Code	L	**KVA Code**	K	**Starting Current**	39 A
Service Factor (S.F.)			1.15	**No-load Current**	7.6 A
NEMA Nom. Eff.	65	**Power Factor**	62	**Line-line Res. @ 25ºC**	1.87 Ω A Ph 1.57 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	55°C
S.F. Amps				**Temp. Rise @ S.F. Load**	61°C

Load Characteristics 230 V, 60 Hz, 1 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	28	38	48	56	62	67	60
Efficiency	39	54	60	62	63	62	62.6
Speed	1188	1180	1169	1158	1144	1127	1150
Line amperes	7.7	8	8.5	9.3	10.1	11.4	9.78


ABB Motors and Mechanical Inc.


WINDING # 36WG0988

1 HP 1 PH 60 HZ 1140 RPM 230 V 3628L


Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=11 PU=10.5 LR=12.8 LRA=39




36LYD011
614-623 = 12.75
624-634 = 14.12
635-646 = 15.63
2.72
2.69
2.25
.19 KEY
1.38 LONG
NAMEPLATE
Ø .8750
.8745
6 HOLES
.41 DIA.
4.50
2.75
5.50
.50
6.50
7.88
6.74
3.93
2.22
8.43
4.50 +.00 -.06
LEAD HOLE
Ø 1.09
3.75
3.75
5.68
4.31
8.63
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD DRW TO SWD DRW
REV: J
VERSION: 04
REVISED: 10:16:50 02/01/2023
TDR: 000001203217
MODEL NO. 36LYD011
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
STD HORZ 182-4 OPEN 36L
36LYD011

CD0001



	LINE A	LINE B	JOIN
HIGH STD	1	4,5	2,3,8
HIGH OPP	1	4,8	2,3,5
LOW STD	1,3,8	2,4,5	–
LOW OPP	1,3,5	2,4,8	–

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0001

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: D	BY: JLP	REVISED: 04/08/99 1:16	TDR: 0178636
CD0001		FILE: AAA00007405	MDL: –
		MTL: –	TYPE L, DV, REV, 6 LEADS