

ABB BALDOR RELIANCE III

Customer information packet

L3507M

.75HP, 1725RPM, 1PH, 60HZ, 56, 3428LC, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	.750 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 115.0 V @ 60 HZ
Agency Approvals	C UR US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	8.200 A @ 115.0 V 5.400 A @ 208.0 V 4.100 A @ 230.0 V
Design Code	N
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	74.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	4.1 a

Part Detail

Revision	AB
Type	AC
Mech. spec.	34G426
Base	
Status	PRD/A
Elec. spec.	34WGW982
Layout	34LYG426
Eff. date	10-25-2024
CD Diagram	CD0320
Poles	04
Leads	6#18,1#16 #4TH
Proprietary	False
Created date	01-01-0001

Insulation Class	B
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3428LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	12.47 IN
Power Factor	80
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Manual Thermal Overload
Winding Thermal 1 Location	SB

Winding Thermal 2

None

Nameplate

NP1257L									
CAT.NO.	L3507M								
SPEC.	34G426W982								
HP	.75								
VOLTS	115/230								
AMP	8.2/4.1								
RPM	1725								
FRAME	56			HZ	60			PH	1
SER.F.	1.25		CODE	L		DES	N	CL	B
NEMA-NOM-EFF	74		PF	80					
RATING	40C AMB-CONT								
CC									
DE	6203		ODE	6203					
ENCL	TEFC		SN						
	SFA 9.8/4.9								

Accessories

Part number	Description	Multiplier
34-171	C FACE KIT	A8

AC Induction Motor Performance Data

Record # 7171

Typical performance - not guaranteed values

Winding: 34WGW982-R001			Type: 3428LC		Enclosure: TEFC	
Nameplate Data					230 V, 60 Hz: High Voltage Connection	
Rated Output (HP)		.75		Full Load Torque		2.27 LB-FT
Volts		115/230		Start Configuration		direct on line
Full Load Amps		8.2/4.1		Breakdown Torque		5.5 LB-FT
R.P.M.		1725		Pull-up Torque		4.25 LB-FT
Hz	60	Phase	1	Locked-rotor Torque		8.62 LB-FT
NEMA Design Code		N	KVA Code	Starting Current		32.2 A
Service Factor (S.F.)		1.25		No-load Current		2.87 A
NEMA Nom. Eff.		74	Power Factor	Line-line Res. @ 25°C		3.08 Ω A Ph 1.75 Ω B Ph
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		62°C
S.F. Amps		9.8/4.9		Temp. Rise @ S.F. Load		80°C

Load Characteristics 230 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	40	59	70	78	83	86	83
Efficiency	50.3	67	71.8	73.6	72.9	71	72.9
Speed	1785	1770	1757	1740	1721	1698	1721
Line amperes	2.92	3.16	3.64	4.2	4.97	5.84	4.97


ABB Motors and Mechanical Inc.


WINDING # 34WGW982


Typical performance - not guaranteed values.

0.75 HP 1 PH 60 HZ 1725 RPM 230 V 3428LC

TORQUES (LB-FT): PO=5.5 PU=4.25 LR=8.62 LRA=32.2







1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

BALDOR

TYPE LC, DV, REV, THERMAL, B PH AMPS THRU HTR HVC, 7 LEAD
SH 1 of 1