



Customer information packet

L1508T-50

5/3.7KW, 1450RPM, 1PH, 50HZ, 213T, 3740LC, OPS

Class - None

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	213T
Frame Material	Steel
Frequency	50.00 Hz
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	3.700 KW @ 50 HZ
Phase	1
Synchronous Speed @ Frequency	1500 RPM @ 50 HZ
Voltage @ Frequency	220.0 V @ 50 HZ
XP Class and Group	None
XP Division	Not Applicable
Agency Approvals	C UR US WEEE UKCA CURUS CE
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	20.400 A @ 220.0 V
Design Code	-
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.3 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	20.4 a

Part detail

Revision	B
Type	AC
Mech. spec.	37K214
Base	
Status	PRD/A
Elec. spec.	37WGQ165
Layout	37LYK214
Eff. date	11-17-2023
CD Diagram	CD0017A02
Poles	04
Leads	2#12 A PH,2#14 B PH
Proprietary	False
Created date	10-03-2023

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	2 @ 12 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3740LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.20 IN
Power Factor	96
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.00
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1372L	
CAT.NO.	L1508T-50
SPEC.	37K214Q165
HP	5/3.7KW
VOLTS	220
AMP	20.4
R.P.M. (1/MIN)	1450
FRAME	213T HZ 50 PH 1
SER.F.	1.00 CODE G DES - CL F
NEMA-NOM-EFF	86.3 PF 96
RATING	40C AMB-S1 CONT
CC	IP23 IC01 15KG
DE	6307 ODE 6206
ENCL	OPSB SN
	IE2-50HZ 86(75%),83(50%)

Accessories

Part number	Description	Multiplier
37-1404	C FACE KIT	A8

AC Induction Motor Performance Data

Record # 101595

Typical performance - not guaranteed values

Winding: 37WGQ165-R001		Type: 3740LC		Enclosure: OPEN	
Nameplate Data			220 V, 50 Hz: Single Voltage Motor		
Rated Output (KW)	3.7	Full Load Torque	17.82 LB-FT		
Volts	220	Start Configuration	direct on line		
Full Load Amps	20.4	Breakdown Torque	53.5 LB-FT		
R.P.M.	1450	Pull-up Torque	26.2 LB-FT		
Hz	50	Locked-rotor Torque	37.7 LB-FT		
NEMA Design Code	-	Starting Current	136 A		
Service Factor (S.F.)	1	No-load Current	4.77 A		
NEMA Nom. Eff.	86.3	Line-line Res. @ 25°C	0.39132 Ω A Ph 1.2312 Ω B Ph		
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	73°C		

Load Characteristics 220 V, 50 Hz, 3.7 KW

% of Rated Load	25	50	75	100	125	150
Power Factor	82	91	94	95	95	95
Efficiency	72.8	83.8	86.7	86.8	85.2	82.5
Speed	1491.2	1482.5	1473	1462.2	1449.2	1433.2
Line amperes	7.01	11	15.4	20.3	25.9	32.2


ABB Motors and Mechanical Inc.


WINDING # 37WGQ165

3.7 KW 1 PH 50 HZ 1450 RPM 220 V 3740LC


Typical performance - not guaranteed values.

TORQUES (LB-FT): PO=53.5 PU=26.2 LR=37.7 LRA=136





CD0017A02



	LINE A	LINE B
STD	1,8	4,5
OPP	1,5	4,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0017A02

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: B	BY: JLP	REVISED: 04/09/99 11:30	TDR: 0178636
CD0017A02		FILE: AAA00007514	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

TYPE LC, SV, REV, 4 LEADS