ABB BALDOR RELIANCE

Customer information packet

L1509T

7.5HP, 3450RPM, 1PH, 60HZ, 213T, 3640LC, OPEN
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/17/2026 10:41:06 PM

Specifications

Enclosure	ODTF
Frame	213T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	7.500 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
Agency Approvals	C UR US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	30.000 A @ 230.0 V 33.000 A @ 208.0 V
Design Code	L
Drip Cover	Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	82.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	30.0 a
Insulation Class	F
Inverter Code	Not Inverter

Part Detail

Revision	Z
Type	AC
Mech. spec.	36H282
Base	
Status	PRD/A
Elec. spec.	36WGY373
Layout	36LYH282
Eff. date	05-09-2024
CD Diagram	CD0017A02
Poles	02
Leads	2#10 A PH,2#16 B PH
Proprietary	False
Created date	01-01-0001

KVA Code	H
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	2 @ 10 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3640LC
Mounting Arrangement	F1
Number of Poles	2
Overall Length	18.36 IN
Power Factor	96
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L											
CAT.NO.	L1509T										
SPEC.	36H282Y373G2										
HP	7.5										
VOLTS	230										
AMP	30										
RPM	3450										
FRAME	213T		**HZ**	60			**PH**	1			
SER.F.	1.15	**CODE**	H	**DES**	L	**CLASS**	F				
NEMA-NOM-EFF	82.5	**PF**	96								
RATING	40C AMB-CONT										
CC											
DE	6207		**ODE**	6205							
ENCL	ODTF	**SN**									

Accessories

Part number	Description	Multiplier
36-1206B	C FACE KIT 213-5TC ODP	A8

AC Induction Motor Performance Data
Record # 23623
Typical performance - not guaranteed values

Winding: 36WGY373-R003	**Type:** 3640LC	**Enclosure:** OPAO

Nameplate Data				**230 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			7.5	**Full Load Torque**	11.4 LB-FT
Volts			208-230	**Start Configuration**	direct on line
Full Load Amps			33-30	**Breakdown Torque**	31.6 LB-FT
R.P.M.			3450	**Pull-up Torque**	24.6 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	30.9 LB-FT
NEMA Design Code	L	**KVA Code**	H	**Starting Current**	215 A
Service Factor (S.F.)			1.15	**No-load Current**	7.35 A
NEMA Nom. Eff.	82.5	**Power Factor**	96	**Line-line Res. @ 25ºC**	0.25 Ω A Ph 0.881 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	60°C
S.F. Amps				**Temp. Rise @ S.F. Load**	74°C

Load Characteristics 230 V, 60 Hz, 7.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	82	92	94	96	96	96	96
Efficiency	65.8	78.7	82.9	82	80.4	77.2	81
Speed	3562	3531	3498	3458	3413	3358	3431
Line amperes	11.1	16.7	23.3	31.1	39.6	49.7	36.2


ABB Motors and Mechanical Inc.


WINDING # 36WGY373

7.5 HP 1 PH 60 HZ 3450 RPM 230 V 3640LC


Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=31.6 PU=24.6 LR=30.9 LRA=215




36LYH282
(614-646) = 18.36
4.27
GREASE FITTING (EA. END)
3.51
3.38
.31 KEY 2.38 LONG
Ø8.60
Ø 1.3750 1.3745
6 HOLES .41 DIA.
5.50
.50
7.00
3.50
8.00
Ø7.86
6.72
LIFTING LUG (EA. END)
2.63
Ø8.60
9.15
5.25 5.19
LEAD HOLE 1.09 DIA.
4.25
4.25
5.68
4.75
9.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD DRAWING TO SOLIDWORKS
REV: G
VERSION: 05
REVISED: 12:32:16 05/10/2022
TDR: 000001190082
MODEL NO. 36LYH282
REF: -
BY: ENALEM0
B
BALDOR
STD HORZ 213-5T ODTF 36LC W/TANDEM FAN
36LYH282

CD0017A02



	LINE A	LINE B
STD	1,8	4,5
OPP	1,5	4,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: B	BY: JLP	REVISED: 04/09/99 11:30	TDR: 0178636
CD0017A02		FILE: AAA00007514	MDL: –
		MTL: –	TYPE LC, SV, REV, 4 LEADS

CD0017A02