ABB BALDOR RELIANCE

Customer information packet

L5005A

.5HP, 1140RPM, 1PH, 60HZ, 56, X3528L, XPFC, F1
Class - CLI GP D; CLII GP F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/17/2026 8:12:42 PM

Specifications

Enclosure	XPFC
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	.500 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	UL
	CSA
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.000 A @ 230.0 V
	8.000 A @ 115.0 V
Design Code	N
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	59.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T4

Part Detail

Revision	AX
Type	AC
Mech. spec.	35E353
Base	
Status	NLA/A
Elec. spec.	35WG0528
Layout	35LYE353
Eff. date	02-13-2023
CD Diagram	CD0008
Poles	06
Leads	6#18,1#16 #4TH
Proprietary	False
Created date	01-01-0001

Heater Indicator	No Heater
High Voltage Full Load Amps	4.0 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3528L
Mounting Arrangement	F1
Number of Poles	6
Overall Length	15.17 IN
Power Factor	63
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1140 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Do Not Use Eve-Not Valiid
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Automatic Thermal Overload

Winding Thermal 1 Location	SB
Winding Thermal 2	None

Nameplate

NP0016XPSL					
NO.		**CC**			
SER. #					
SPEC	35E353-528				
CAT.NO.	L5005A				
H.P.	.5	**T. CODE**	T4		
VOLTS	115/230				
AMPS	8/4				
R.P.M.	1140				
HZ	60	**PH**	1	**CLASS**	B
SER.F.	1.00	**DES**	N	**CODE**	L
RATING	40C AMB-CONT				
FRAME	56	**NEMA NOM. EFF**			59
PF	63				
BLANK					

AC Induction Motor Performance Data
Record # 20315
Typical performance - not guaranteed values

Winding: 35WG0528-R003	**Type:** 3528L	**Enclosure:** XPFC

Nameplate Data				**230 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			.5	**Full Load Torque**	2.25 LB-FT
Volts			115/230	**Start Configuration**	direct on line
Full Load Amps			8/4	**Breakdown Torque**	5 LB-FT
R.P.M.			1140	**Pull-up Torque**	4.75 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	6.5 LB-FT
NEMA Design Code	N	**KVA Code**	L	**Starting Current**	19 A
Service Factor (S.F.)			1	**No-load Current**	3.5 A
NEMA Nom. Eff.	59	**Power Factor**	63	**Line-line Res. @ 25ºC**	4.83 Ω A Ph 3.14 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	48°C

Load Characteristics 230 V, 60 Hz, 0.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	28	41	49	59	65	69	65
Efficiency	39.7	57	62.3	64.7	64.9	63.4	64.9
Speed	1189	1178	1170	1156	1144	1130	1144
Line amperes	3.5	3.7	3.9	4.3	4.8	5.3	4.8


ABB Motors and Mechanical Inc.


WINDING # 35WG0528

0.5 HP 1 PH 60 HZ 1140 RPM 230 V 3528L


Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=5 PU=4.75 LR=6.5 LRA=19




35LYE353
510-520=14.28
521-528=15.15
529-535=16.03
536-546=17.40
2.40
1.88
.19 KEY
1.38 LONG
X-PROOF NAMEPLATE
BALDOR
PT. NO. 35CB3500
Ø .6250
.6245
4 SLOTS
.34 WIDE
.66
3.00
2.75
4.72
4.32
6.98
6.83
3.50
3.44
LEAD HOLE
.50 N.P.T.
2.49
2.49
5.39
3.31
6.62
.086
(.047 MIN)
(EA. END)
FRONT END DETAIL
.44
(MIN)
.0015 MAX.
CLEARANCE
(EA. END)
1.10
(1.00 MIN)
.006
.004
.38
PULLEY END DETAIL
REV. DESC: ADD T-BOLT THREADS EXTENDING PAST NUT PU END
REV: J
VERSION: 04
REVISED: 08:11:45 03/26/2020
TDR: 000001127865
MODEL NO. 35LYE353
REF: -
BY: USJOCUR
Material: -
B
BALDOR - RELIANCE®
STD HORZ 56 XPFC L-LC CL-I GP-D, CL-II GP-F&G
35LYE353

CD0008



	LINE A	LINE B	JOIN	JOIN
HIGH STD	1	4	2,3,8	J,5
HIGH OPP	1	4	2,3,5	J,8
LOW STD	1,3,8	4	–	2,J,5
LOW OPP	1,3,5	4	–	2,J,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0008

REV. DESC: REMOVE 2–TERMINAL THERMAL DETAIL, SEE CD0008A02			BALDOR ELECTRIC Co.
REV. LTR: F	VERSION: 01	TDR: 000000360649	
CD0008	FILE: \AAA\00007\408	REVISED: 10:56:54 04/18/2005	TYPE L, DV, REV, THERMAL, 7 LEADS
	MTL: –	BY: ENJOEP0	