Customer information packet

L5007A

.75HP, 1725RPM, 1PH, 60HZ, 56, X3524L, XPFC, F1
Class - CLI GP D; CLII GP F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/18/2026 3:12:09 AM

Specifications

Enclosure	XPFC
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	.750 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	UR
	UL
	CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	10.600 A @ 115.0 V
	5.300 A @ 230.0 V
Design Code	N
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	66.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T4

Part Detail

Revision	BA
Type	AC
Mech. spec.	35E353
Base	
Status	NLA/A
Elec. spec.	35WG0526
Layout	35LYE353
Eff. date	02-13-2023
CD Diagram	CD0008
Poles	04
Leads	6#18,1#14 #4TH
Proprietary	False
Created date	01-01-0001

Heater Indicator	No Heater
High Voltage Full Load Amps	5.3 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3524L
Mounting Arrangement	F1
Number of Poles	4
Overall Length	15.17 IN
Power Factor	68
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Do Not Use Eve-Not Valiid
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	Automatic Thermal Overload
Winding Thermal 1 Location	SB
Winding Thermal 2	None

Nameplate

NP0016XPSL							
NO.		**CC**					
SER. #							
SPEC	35E353-526						
CAT.NO.	L5007A						
H.P.	.75	**T. CODE**	T4				
VOLTS	115/230						
AMPS	10.6/5.3						
R.P.M.	1725						
HZ	60	**PH**	1	**CLASS**	B		
SER.F.	1.00	**DES**	N	**CODE**	L		
RATING	40C AMB-CONT						
FRAME	56	**NEMA NOM. EFF**	66				
PF	68						
BLANK							


AC Induction Motor Performance Data
Record # 20314
Typical performance - not guaranteed values

Winding: 35WG0526-R002	**Type:** 3524L	**Enclosure:** XPFC

Nameplate Data				**230 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			.75	**Full Load Torque**	2.25 LB-FT
Volts			115/230	**Start Configuration**	direct on line
Full Load Amps			10.6/5.3	**Breakdown Torque**	6.5 LB-FT
R.P.M.			1725	**Pull-up Torque**	5.2 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	7 LB-FT
NEMA Design Code	N	**KVA Code**	L	**Starting Current**	34 A
Service Factor (S.F.)			1	**No-load Current**	4.4 A
NEMA Nom. Eff.	66	**Power Factor**	68	**Line-line Res. @ 25ºC**	2.84 Ω A Ph 1.57 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	64°C

Load Characteristics 230 V, 60 Hz, 0.75 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	32	45	56	65	72	78	0
Efficiency	42.5	58.2	65.4	68.7	69.9	69.6	0
Speed	1784	1771	1757	1742	1724	1704	0
Line amperes	4.45	4.65	5	5.45	6.05	6.75	6.05


ABB Motors and Mechanical Inc.
WINDING # 35WG0526
Typical performance - not guaranteed values.
0.75 HP 1 PH 60 HZ 1725 RPM 230 V 3524L
TORQUES(LB-FT): PO=6.5 PU=5.2 LR=7 LRA=34
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
PERCENT OF RATED OUTPUT (0.75 HP)
11/18/2026 ACPERF, record # 20314

AC Induction Motor Performance Data
Record # 51898
Typical performance - not guaranteed values


Winding: 35WG0526-R002 **Type:** 3524L **Enclosure:** XPFC


Nameplate Data			
Rated Output (HP)			.75
Volts			115/230
Full Load Amps			10.6/5.3
R.P.M.			1725
Hz	60	**Phase**	1
NEMA Design Code	N	**KVA Code**	L
Service Factor (S.F.)			1
NEMA Nom. Eff.	66	**Power Factor**	68
Rating - Duty			40C AMB-CONT
S.F. Amps			

115 V, 60 Hz: Low Voltage Connection	
Full Load Torque	2.25 LB-FT
Start Configuration	direct on line
Breakdown Torque	6.5 LB-FT
Pull-up Torque	5.2 LB-FT
Locked-rotor Torque	7 LB-FT
Starting Current	68 A
No-load Current	8.8 A
Line-line Res. @ 25ºC	0.712 Ω A Ph 1.5 Ω B Ph
Temp. Rise @ Rated Load	64°C
Temp. Rise @ S.F. Load	76°C
Locked-rotor Power Factor	97
Rotor inertia	0.142 LB-FT2


Load Characteristics 115 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	33	45	56	65	71	76
Efficiency	42.6	58.5	65.5	68.8	69.9	69.7
Speed	1784	1771	1757	1742	1724	1704
Line amperes	8.9	9.3	10	10.9	12.1	13.5


ABB Motors and Mechanical Inc.
WINDING # 35WG0526
Typical performance - not guaranteed values.
0.75 HP 1 PH 60 HZ 1725 RPM 115 V 3524L
TORQUES(LB-FT): PO=6.5 PU=5.2 LR=7 LRA=68
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
PERCENT OF RATED OUTPUT (0.75 HP)
11/18/2026 ACPERF, record # 51898


35LYE353
510-520=14.28
521-528=15.15
529-535=16.03
536-546=17.40
2.40
1.88
.19 KEY
1.38 LONG
X-PROOF NAMEPLATE
BALDOR
PT. NO. 35CB3500
Ø .6250
.6245
4 SLOTS
.34 WIDE
.66
3.00
2.75
4.72
4.32
6.98
6.83
3.50
3.44
LEAD HOLE
.50 N.P.T.
2.49
2.49
5.39
3.31
6.62
.086
(.047 MIN)
(EA. END)
FRONT END DETAIL
.44
(MIN)
.0015 MAX.
CLEARANCE
(EA. END)
1.10
(1.00 MIN)
.006
.004
.38
PULLEY END DETAIL
REV. DESC: ADD T-BOLT THREADS EXTENDING PAST NUT PU END
REV: J
VERSION: 04
REVISED: 08:11:45 03/26/2020
TDR: 000001127865
MODEL NO. 35LYE353
REF: -
BY: USJOCUR
Material: -
B
BALDOR - RELIANCE®
STD HORZ 56 XPFC L-LC CL-I GP-D, CL-II GP-F&G
35LYE353

CD0008



	LINE A	LINE B	JOIN	JOIN
HIGH STD	1	4	2,3,8	J,5
HIGH OPP	1	4	2,3,5	J,8
LOW STD	1,3,8	4	–	2,J,5
LOW OPP	1,3,5	4	–	2,J,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0008

REV. DESC: REMOVE 2–TERMINAL THERMAL DETAIL, SEE CD0008A02			BALDOR ELECTRIC Co.
REV. LTR: F	VERSION: 01	TDR: 000000360649	
CD0008	FILE: \AAA\00007\408	REVISED: 10:56:54 04/18/2005	TYPE L, DV, REV, THERMAL, 7 LEADS
	MTL: –	BY: ENJOEP0	