

ABB BALDOR RELIANCE III

Customer information packet

M1509T

7.5/3.8HP, 1740/860RPM, 3PH, 60HZ, 215T, 3754

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	215T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ 3.800 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	18.900 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	16.6 a
Insulation Class	F
Inverter Code	Not Inverter

Part Detail

Revision	P
Type	AC
Mech. spec.	37A001
Base	
Status	PRD/A
Elec. spec.	37WGS296
Layout	37LYA001
Eff. date	11-05-2025
CD Diagram	CD0011
Poles	04/08
Leads	6#14
Proprietary	False
Created date	02-06-2007

KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3754M
Mounting Arrangement	F1
Number of Poles	4
	8
Overall Length	20.51 IN
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1740 rpm
	860 rpm
Speed Code	2S-1W-CT
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.	M1509T								
SPEC.	37A001S296								
HP	7.5/3.8								
VOLTS	230								
AMP	18.9/16.6								
RPM	1740/860								
FRAME	215T		HZ	60			PH	3	
SER.F.	1.15		CODE	K	DES	B	CLASS	F	
NEMA-NOM-EFF			PF						
RATING	40C AMB-CONT								
CC									
DE	6307		ODE	6206					
ENCL	TEFC		SN						

Accessories

Part number	Description	Multiplier
37-3301	C FACE KIT	P1

AC Induction Motor Performance Data

Record # 23678

Typical performance - not guaranteed values

Winding: 37WGS296-R001		Type: 3754M	Enclosure: TEFC
Nameplate Data		230 V, 60 Hz: High Speed Connection	
Rated Output (HP)	7.5/3.8	Full Load Torque	22.4 LB-FT
Volts	230	Start Configuration	direct on line
Full Load Amps	18.9/16.6	Breakdown Torque	114 LB-FT
R.P.M.	1740/860	Pull-up Torque	29.3 LB-FT
Hz	60 Phase	Locked-rotor Torque	67 LB-FT
NEMA Design Code	B KVA Code	Starting Current	163 A
Service Factor (S.F.)	1.15	No-load Current	8.18 A
NEMA Nom. Eff.	0 Power Factor	Line-line Res. @ 25°C	0.489 Ω
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	75°C
S.F. Amps		Temp. Rise @ S.F. Load	94°C

Load Characteristics 230 V, 60 Hz, 7.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	46	69	80	85	88	89	87
Efficiency	83.9	88.4	88.6	87.4	85.7	83.5	86.4
Speed	1788	1775	1761	1746	1730	1710	1736
Line amperes	9.11	11.6	15	18.9	23.3	28.3	21.5


ABB Motors and Mechanical Inc.

WINDING # 37WGS296

Typical performance - not guaranteed values.

7.5 HP 3 PH 60 HZ 1746 RPM 230 V 3754M

TORQUES (LB-FT): PO=114 PU=29.3 LR=67 LRA=163



AC Induction Motor Performance Data

Record # 23679

Typical performance - not guaranteed values

Winding: 37WGS296-R001			Type: 3754M		Enclosure: TEFC		
Nameplate Data				230 V, 60 Hz: Low Speed Connection			
Rated Output (HP)		7.5/3.8		Full Load Torque		23.1 LB-FT	
Volts		230		Start Configuration		direct on line	
Full Load Amps		18.9/16.6		Breakdown Torque		95.2 LB-FT	
R.P.M.		1740/860		Pull-up Torque		38 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		58.3 LB-FT	
NEMA Design Code		B	KVA Code	K	Starting Current		85.8 A
Service Factor (S.F.)		1.15		No-load Current		13.3 A	
NEMA Nom. Eff.		0	Power Factor	0	Line-line Res. @ 25°C		0.645 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		84°C	
S.F. Amps				Temp. Rise @ S.F. Load		98°C	

Load Characteristics 230 V, 60 Hz, 3.8 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	20	33	44	52	59	64	56
Efficiency	65.8	77.3	80.9	81.8	81.3	80.1	81.5
Speed	892	884	876	867	857	845	861
Line amperes	13.4	14.1	15.1	16.6	18.4	20.7	17.7


ABB Motors and Mechanical Inc.

WINDING # 37WGS296


Typical performance - not guaranteed values.

3.8 HP 3 PH 60 HZ 867 RPM 230 V 3754M


TORQUES (LB-FT): PO=95.2 PU=38 LR=58.3 LRA=85.8




CD0011



LOW SPEED
(1D)



HIGH SPEED
(2Y)



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: F	BY: JLP	REVISED: 01/21/99 5:04	TDR: 0171435
110000		FILE: DWG\142.wg	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, SV, 6 LEADS, 2-SPEED 1-WINDING CONSTANT TORQUE

CD0011