

ABB BALDOR RELIANCE III

Customer information packet

L3514TM

1.5HP, 1725RPM, 1PH, 60HZ, 145T, 3532LC, TEFC

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	145T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	1.500 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ 208.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	C UR US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	12.200 A @ 115.0 V 5.500 A @ 230.0 V 6.200 A @ 208.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	80.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	5.5 a

Part Detail

Revision	D
Type	AC
Mech. spec.	35HH612
Base	
Status	PRD/A
Elec. spec.	35WGG398
Layout	35LYHH612
Eff. date	06-19-2025
CD Diagram	CD0016A02
Poles	04
Leads	7#18,1#16 #4TH
Proprietary	False
Created date	02-23-2023

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	H
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	7 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3532LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	14.16 IN
Power Factor	90
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.00
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Manual Thermal Overload
Winding Thermal 1 Location	SB
Winding Thermal 2	None

Nameplate

NP1257L											
CAT.NO.	L3514TM										
SPEC.	35HH612G398										
HP	1.5										
VOLTS	115/208-230										
AMP	12.2/6.2-5.5										
RPM	1725										
FRAME	145T			HZ	60			PH	1		
SER.F.	1.00	CODE	H	DES	L	CL	F				
NEMA-NOM-EFF	80	PF	90								
RATING	40C AMB-CONT										
CC											
DE	6205	ODE	6203								
ENCL	TEFC	SN									

Accessories

Part number	Description	Multiplier
35-8762	C FACE KIT	A8
35EP1506A01SP	D-FLANGE KIT	A8

AC Induction Motor Performance Data

Record # 89151

Typical performance - not guaranteed values

Winding: 35WGG398-R001			Type: 3532LC		Enclosure: TEFC	
Nameplate Data			230 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		1.5	Full Load Torque		4.56 LB-FT	
Volts		115/208-230	Start Configuration		direct on line	
Full Load Amps		13.4/6.8-6.7	Breakdown Torque		9.9 LB-FT	
R.P.M.		1725	Pull-up Torque		8.06 LB-FT	
Hz	60 Phase	1	Locked-rotor Torque		12.98 LB-FT	
NEMA Design Code		L KVA Code	Starting Current		43.97 A	
Service Factor (S.F.)		1	No-load Current		0.877 A	
NEMA Nom. Eff.		80 Power Factor	Line-line Res. @ 25°C		0.517 Ω A Ph 1.32 Ω B Ph	
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		67°C	
			Locked-rotor Power Factor		91.1	
			Rotor inertia		0.232 lb-ft²	

Load Characteristics 230 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	95	98	98	98	97	96
Efficiency	68.1	80.4	82.5	81.1	76.9	69.8
Speed	1782	1765	1746	1723	1690	1641
Line amperes	1.83	3.08	4.5	6.1	8.12	10.79


ABB Motors and Mechanical Inc.


WINDING # 35WGG398

Typical performance - not guaranteed values.


1.5 HP 1 PH 60 HZ 1725 RPM 230 V 3532LC

TORQUES (LB-FT): PO=9.9 PU=8.06 LR=12.98 LRA=43.97





CD0016A02



	LINE A	LINE B	JOIN	JOIN	JOIN
HIGH STD	1	4	2,3	8,9	J,5
HIGH OPP	1	4	2,3	5,9	J,8
LOW STD	1,3	4	8,9	2,J,5	—
LOW OPP	1,3	4	5,9	2,J,8	—

- NOTES:
1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
 2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
 3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REMOVE OPTIONAL THERMAL CONNECTION		
REV. LTR: F	VERSION: 01	TDR: 000000373039
CD0016A02	FILE: \AAA\00007\411	REVISED: 10:13:25 08/11/2005
	MTL: —	BY: ENJOEPO

BALDOR ELECTRIC Co.

TYPE LC, DV, REV, OIL CAP ACR. LINE, THERMAL, 8 LEADS

CD0016A02