

BALDOR • RELIANCE

Customer information packet

M1524T

5/2.2HP, 1725/1140RPM, 3PH, 60HZ, 215T, 3740M

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	215T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ 2.200 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	12.800 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	7.0 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K

Part detail

Revision	E
Type	AC
Mech. spec.	37T397
Base	
Status	PRD/A
Elec. spec.	37WGX673
Layout	37LYT397
Eff. date	05-14-2024
CD Diagram	CD0013
Poles	04/06
Leads	6#14
Proprietary	False
Created date	06-11-2019

Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	6 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3740M
Mounting Arrangement	F1
Number of Poles	4 6
Overall Length	19.01 IN
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1140 rpm 1725 rpm
Speed Code	2S-2W-VT
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.	M1524T								
SPEC.	37T397X673G1								
HP	5/2.2								
VOLTS	230								
AMP	12.8/7								
RPM	1725/1140								
FRAME	215T		HZ	60		PH	3		
SER.F.	1.15	CODE	K	DES	B	CLASS	F		
NEMA-NOM-EFF		PF							
RATING	40C AMB-CONT								
CC									
DE	6307		ODE	6206					
ENCL	TEFC	SN							

Accessories

Part number	Description	Multiplier
37-3301	C FACE KIT	P1

AC Induction Motor Performance Data

Record # 37160

Typical performance - not guaranteed values

Winding: 37WGX673-R002		Type: 3740M		Enclosure: TEFC	
Nameplate Data			230 V, 60 Hz: High Speed Connection		
Rated Output (HP)	5/2.2	Full Load Torque	15 LB-FT		
Volts	230	Start Configuration	direct on line		
Full Load Amps	12.8/7	Breakdown Torque	51 LB-FT		
R.P.M.	1725/1140	Pull-up Torque	36 LB-FT		
Hz	60 Phase	3	Locked-rotor Torque	51 LB-FT	
NEMA Design Code	B KVA Code	K	Starting Current	115 A	
Service Factor (S.F.)		1.15	No-load Current	5.3 A	
NEMA Nom. Eff.	0 Power Factor	0	Line-line Res. @ 25°C	0.825 Ω	
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load	80°C	
S.F. Amps			Temp. Rise @ S.F. Load	96°C	

Load Characteristics 230 V, 60 Hz, 5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	51	70	80	83	85	85	84
Efficiency	75.9	82.2	83.2	81.4	79.4	76	80.2
Speed	1780	1761	1743	1721	1697	1665	1707
Line amperes	6.2	8.2	10.6	13.6	16.9	20.8	15.6


ABB Motors and Mechanical Inc.

WINDING # 37WGX673

5 HP 3 PH 60 HZ 1721 RPM 230 V 3740M

Typical performance - not guaranteed values.

TORQUES (LB-FT): PO=51 PU=36 LR=51 LRA=115



7/25/2024 ACPERF, record # 37160

AC Induction Motor Performance Data

Record # 37161

Typical performance - not guaranteed values

Winding: 37WGX673-R002		Type: 3740M		Enclosure: TEFC	
Nameplate Data			230 V, 60 Hz: Low Speed Connection		
Rated Output (HP)	5/2.2	Full Load Torque	15 LB-FT		
Volts	230	Start Configuration	direct on line		
Full Load Amps	12.8/7	Breakdown Torque	51 LB-FT		
R.P.M.	1725/1140	Pull-up Torque	36 LB-FT		
Hz	60 Phase	3	Locked-rotor Torque	51 LB-FT	
NEMA Design Code	B KVA Code	K	Starting Current	115 A	
Service Factor (S.F.)		1.15	No-load Current	5.3 A	
NEMA Nom. Eff.	0 Power Factor	0	Line-line Res. @ 25°C	2.15 Ω	
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load	80°C	
S.F. Amps			Temp. Rise @ S.F. Load	95°C	

Load Characteristics 230 V, 60 Hz, 2.2 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	51	70	80	83	85	85	84
Efficiency	75.9	82.2	83.2	81.4	79.4	76	80.2
Speed	1780	1761	1743	1721	1697	1665	1707
Line amperes	6.2	8.2	10.6	13.6	16.9	20.8	15.6


ABB Motors and Mechanical Inc.


WINDING # 37WGx673

2.2 HP 3 PH 60 HZ 1721 RPM 230 V 3740M



Typical performance - not guaranteed values.

TORQUES (LB-FT): PO=51 PU=36 LR=51 LRA=115





CD0013



NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: D	BY: JLP	REVISED: 01/22/99 8:50	TDR: 0171435
FILE: AAA00005143		MDL: -	
MTL: -			

BALDOR ELECTRIC Co.

3PH, SV, 6 LEADS, 2-SPEED 2-WINDING

CD0013