

ABB BALDOR RELIANCE III

Customer information packet

L3565M

.75HP, 1725RPM, 1PH, 60HZ, 66, 3524L, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	66
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	.750 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	C UR US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	10.600 A @ 115.0 V 5.300 A @ 230.0 V
Design Code	N
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	66.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	5.3 a
Insulation Class	B

Part Detail

Revision	AL
Type	AC
Mech. spec.	35E030
Base	
Status	NLA/A
Elec. spec.	35WG0282
Layout	35LYE030
Eff. date	05-07-2024
CD Diagram	CD0008
Poles	04
Leads	6#18,1#14 #4TH
Proprietary	False
Created date	01-01-0001

Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3524L
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.62 IN
Power Factor	68
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.25
Shaft Diameter	0.750 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Do Not Use
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Manual Thermal Overload
Winding Thermal 1 Location	SB
Winding Thermal 2	None

Nameplate

NP1257L										
CAT.NO.										
SPEC.	35E30-282									
HP	.75									
VOLTS	115/230									
AMP	10.6/5.3									
RPM	1725									
FRAME	66			HZ		60		PH 1		
SER.F.	1.25	CODE	L	DES		N	CL	B		
NEMA-NOM-EFF	66	PF	68							
RATING	40C AMB-CONT									
CC										
DE	6205	ODE		6203						
ENCL	TEFC	SN								
	SFA 12.2/6.1									

Accessories

Part number	Description	Multiplier
35-8762	C FACE KIT	A8
35EP1506A01SP	D-FLANGE KIT	A8

AC Induction Motor Performance Data

Record # 8055

Typical performance - not guaranteed values

Winding: 35WG0282-R001			Type: 3524L		Enclosure: TEFC	
Nameplate Data				230 V, 60 Hz: High Voltage Connection		
Rated Output (HP)		.75		Full Load Torque		2.25 LB-FT
Volts		115/230		Start Configuration		direct on line
Full Load Amps		10.6/5.3		Breakdown Torque		6.5 LB-FT
R.P.M.		1725		Pull-up Torque		5.2 LB-FT
Hz	60	Phase	1	Locked-rotor Torque		7 LB-FT
NEMA Design Code		N	KVA Code	Starting Current		34 A
Service Factor (S.F.)		1.25		No-load Current		4.4 A
NEMA Nom. Eff.		66	Power Factor	Line-line Res. @ 25°C		2.84 Ω A Ph 1.57 Ω B Ph
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		64°C
S.F. Amps		12.2/6.1		Temp. Rise @ S.F. Load		81°C

Load Characteristics 230 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	32	45	56	65	72	78	0
Efficiency	42.5	58.2	65.4	68.7	69.9	69.6	0
Speed	1784	1771	1757	1742	1724	1704	0
Line amperes	4.45	4.65	5	5.45	6.05	6.75	6.05


ABB Motors and Mechanical Inc.

WINDING # 35WG0282


Typical performance - not guaranteed values.

0.75 HP 1 PH 60 HZ 1725 RPM 230 V 3524L

TORQUES (LB-FT) : PO=6.5 PU=5.2 LR=7 LRA=34



CD0008



	LINE A	LINE B	JOIN	JOIN
HIGH STD	1	4	2,3,8	J,5
HIGH OPP	1	4	2,3,5	J,8
LOW STD	1,3,8	4	—	2,J,5
LOW OPP	1,3,5	4	—	2,J,8

- NOTES:
- 1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
 - 2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
 - 3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REMOVE 2-TERMINAL THERMAL DETAIL, SEE CD0008A02		
REV. LTR: F	VERSION: 01	TDR: 000000360649
800000	FILE: \AAA\00007\408	REVISED: 10:56:54 04/18/2005
	MTL: —	BY: ENJOEPO

BALDOR ELECTRIC Co.

TYPE L, DV, REV, THERMAL, 7 LEADS

CD0008