ABB BALDOR RELIANCE

Customer information packet

M1723T

3/1.3HP, 1725/1140RPM, 3PH, 60HZ, 184T, 3634M
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/9/2026 11:01:15 AM

Specifications

Enclosure	TEFC
Frame	184T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
	1.300 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	UR
	CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.6 a
Insulation Class	F
Inverter Code	Not Inverter

Part Detail

Revision	AB
Type	AC
Mech. spec.	36A001
Base	
Status	PRD/A
Elec. spec.	36WGY048
Layout	36LYA001
Eff. date	05-20-2025
CD Diagram	CD0013
Poles	04/06
Leads	6#16
Proprietary	False
Created date	01-01-0001

KVA Code	G
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3634M
Mounting Arrangement	F1
Number of Poles	4
	6
Overall Length	16.54 IN
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1140 rpm
	1725 rpm
Speed Code	2S-2W-VT
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L											
CAT.NO.	M1723T										
SPEC.	36A01Y48										
HP	3/1.3										
VOLTS	460										
AMP	4/2.6										
RPM	1725/1140										
FRAME	184T		**HZ**	60			**PH**	3			
SER.F.	1.15	**CODE**	G	**DES**	B	**CLASS**	F				
NEMA-NOM-EFF		**PF**									
RATING	40C AMB-CONT										
CC											
DE	6206		**ODE**	6205							
ENCL	TEFC	**SN**									

Accessories

Part number	Description	Multiplier
36-3301	C FACE KIT	A8
36EP1304A62SP	FLANGE MTD ENDPLATE 182-4TD -ENCL (LESS	A8


AC Induction Motor Performance Data
Record # 15218
Typical performance - not guaranteed values

Winding: 36WGY048-R002	**Type:** 3634M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Speed Connection**	
Rated Output (HP)			3/1.3	**Full Load Torque**	9.2 LB-FT
Volts			460	**Start Configuration**	direct on line
Full Load Amps			4/2.6	**Breakdown Torque**	28 LB-FT
R.P.M.			1725/1140	**Pull-up Torque**	13 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	19 LB-FT
NEMA Design Code	B	**KVA Code**	G	**Starting Current**	24 A
Service Factor (S.F.)			1.15	**No-load Current**	1.5 A
NEMA Nom. Eff.	0	**Power Factor**	0	**Line-line Res. @ 25ºC**	9.85 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	54	75	85	90	92	92	91
Efficiency	74.3	81.5	82.4	81.2	78.7	75.2	79.7
Speed	1781	1763	1742	1718	1690	1655	1701
Line amperes	1.75	2.3	3	3.85	4.85	6.1	4.45


ABB Motors and Mechanical Inc.
WINDING # 36WGY048
Typical performance - not guaranteed values.
3 HP 3 PH 60 HZ 1718 RPM 460 V 3634M
TORQUES(LB-FT): PO=28 PU=13 LR=19 LRA=24
TORQUE
RPM
KW
AMPS
EFF
PF
%EFF
%PF
TORQUE (LB-FT)
RPM
KW
AMPS
PERCENT OF RATED OUTPUT (3 HP)
11/9/2026 ACPERF, record # 15218


AC Induction Motor Performance Data
Record # 15219
Typical performance - not guaranteed values


Winding: 36WGY048-R002	**Type:** 3634M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: Low Speed Connection**	
Rated Output (HP)			3/1.3	**Full Load Torque**	5.9 LB-FT
Volts			460	**Start Configuration**	direct on line
Full Load Amps			4/2.6	**Breakdown Torque**	17 LB-FT
R.P.M.			1725/1140	**Pull-up Torque**	9.2 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	10.3 LB-FT
NEMA Design Code	B	**KVA Code**	G	**Starting Current**	12 A
Service Factor (S.F.)			1.15	**No-load Current**	1.95 A
NEMA Nom. Eff.	0	**Power Factor**	0	**Line-line Res. @ 25ºC**	17.7 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	


Load Characteristics 460 V, 60 Hz, 1.3 HP


% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	29	43	55	65	72	78	69
Efficiency	52.3	66.9	72.7	75	75.5	74.9	75.3
Speed	1190	1181	1172	1161	1150	1137	1154
Line amperes	2	2.1	2.25	2.5	2.8	3.1	2.7


ABB Motors and Mechanical Inc.
WINDING # 36WGY048
1.3 HP 3 PH 60 HZ 1161 RPM 460 V 3634M
Typical performance - not guaranteed values.
TORQUES(LB-FT): PO=17 PU=9.2 LR=10.3 LRA=12
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
PERCENT OF RATED OUTPUT (1.3 HP)
11/9/2026 ACPERF, record # 15219


36LYA001
614 - 623 = 15.17
624 - 634 = 16.54
635 - 646 = 18.04
635-646
OR WHEN REQ'D
GREASE FITTING
(EACH END)
4.27
3.56
2.75
.25 KEY
1.75 LONG
NAMEPLATE
Ø8.60
Ø 1.1250
1.1245
6 HOLES
Ø.44
4.50
2.75
5.50
.50
6.50
Ø7.87
6.88
2.24
8.43
4.50
4.44
LEAD HOLE
Ø1.09
3.75
3.75
5.76
4.31
8.63
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD "WHEN REQ'D" TO LIFTING CALLOUT
REV: Y
VERSION: 08
REVISED: 02:20:29 01/16/2026
TDR: 000001270424
MODEL NO. 36LYA001
REF: -
BY: USTRTAY1
B
BALDOR - RELIANCE®
STD HORZ 182-4T TEFC 36M
36LYA001

CD0013





NOTES:
1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: D	BY: JLP	REVISED: 01/22/99 8:50	TDR: 0171435
CD0013		FILE: AAA00005143	MDL: –
		MTL: –	3PH, SV, 6 LEADS, 2–SPEED 2–WINDING

CD0013