

ABB BALDOR RELIANCE III

Customer information packet

L4003A

.25HP, 1725RPM, 1PH, 60HZ, 48, X3411L, XPFC, F1

Class - CLI GP D; CLII GP F,G

Division - Division I

Specifications

Enclosure	XPFC
Frame	48
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	.250 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ 208.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	UL CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.500 A @ 230.0 V 2.600 A @ 208.0 V 5.000 A @ 115.0 V
Design Code	N
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	55.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part Detail

Revision	AJ
Type	AC
Mech. spec.	34-5426
Base	
Status	PRD/A
Elec. spec.	34WG368
Layout	34LY5426
Eff. date	05-01-2024
CD Diagram	CD0885
Poles	04
Leads	7#18
Proprietary	False
Created date	01-01-0001

Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	2.5 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	7 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3411L
Mounting Arrangement	F1
Number of Poles	4
Overall Length	12.85 IN
Power Factor	57
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.00
Shaft Diameter	0.500 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None

Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Automatic Thermal Overload
Winding Thermal 1 Location	SB

Nameplate

NP0016XPSL					
NO.		CC			
SER. #					
SPEC	34-5426W368				
CAT.NO.	L4003A				
H.P.	.25	T. CODE	T3C		
VOLTS	115/208-230				
AMPS	5/2.6-2.5				
R.P.M.	1725				
HZ	60	PH	1	CLASS	B
SER.F.	1.00	DES	N	CODE	L
RATING	40C AMB-CONT				
FRAME	48	NEMA NOM. EFF			55
	PF	57			
BLANK					

AC Induction Motor Performance Data

Record # 6961

Typical performance - not guaranteed values

Winding: 34WGW368-R001				Type: 3411L		Enclosure: XPFC	
Nameplate Data				230 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		.25		Full Load Torque		0.781 LB-FT	
Volts		115/208-230		Start Configuration		direct on line	
Full Load Amps		5/2.6-2.5		Breakdown Torque		3.72 LB-FT	
R.P.M.		1725		Pull-up Torque		2.15 LB-FT	
Hz	60	Phase	1	Locked-rotor Torque		2.79 LB-FT	
NEMA Design Code		N	KVA Code	Starting Current		11 A	
Service Factor (S.F.)		1		No-load Current		2.34 A	
NEMA Nom. Eff.		55	Power Factor	Line-line Res. @ 25°C		8.77 Ω A Ph 6.84 Ω B Ph	
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load			

Load Characteristics 230 V, 60 Hz, 0.25 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	36	45	53	60	66	72
Efficiency	31.6	42.2	50	54.7	56.3	56.5
Speed	1767	1752	1738	1719	1698	1672
Line amperes	2.32	2.36	2.42	2.53	2.7	2.93


ABB Motors and Mechanical Inc.


WINDING # 34WG368

Typical performance - not guaranteed values.

0.25 HP 1 PH 60 HZ 1725 RPM 230 V 3411L

TORQUES (LB-FT): PO=3.72 PU=2.15 LR=2.79 LRA=11





CD0885

