

ABB BALDOR RELIANCE III

Customer information packet

M3112-57

.75HP, 1425 IP23RPM, 3PH, 50HZ, 56, 3420M, O

Class - None

Division - Not Applicable

Specifications

Enclosure	OPEN
Frame	56
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	1500 RPM @ 50 HZ
Voltage @ Frequency	230.0 V @ 50 HZ 400.0 V @ 50 HZ
Agency Approvals	C UR US CE CURUS UKCA WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.200 A @ 230.0 V 1.900 A @ 400.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	70.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part Detail

Revision	J
Type	AC
Mech. spec.	34F779
Base	
Status	PRD/A
Elec. spec.	34WG2382
Layout	34LYF779
Eff. date	10-25-2024
CD Diagram	CD0022
Poles	04
Leads	6#18
Proprietary	False
Created date	09-08-2011

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.9 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3420M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	10.14 IN
Power Factor	58
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1425 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1372L									
CAT.NO.	M3112-57								
SPEC.	34F779-2382G1								
HP	.75/KW .56								
VOLTS	230/400								
AMP	3.2/1.9 SFA 3.6/2.1								
R.P.M. (1/MIN)	1425								
FRAME	56	HZ		50	PH		3		
SER.F.	1.25	CODE		K	DES	B	CL	F	
NEMA-NOM-EFF	70	PF		58					
RATING	40C AMB-S1 CONT								
CC			IP23 12KG IC01						
DE	6203	ODE		6203					
ENCL	OPEN	SN							
	IE2-70.0(75%)64.9(50%)								

AC Induction Motor Performance Data

Record # 35180

Typical performance - not guaranteed values

Winding: 34WG2382-R002			Type: 3420M		Enclosure: TEFC	
Nameplate Data			400 V, 50 Hz: High Voltage Connection			
Rated Output (HP)		.75	Full Load Torque		2.71 LB-FT	
Volts		230/400	Start Configuration		direct on line	
Full Load Amps		3.2/1.9	Breakdown Torque		11.9 LB-FT	
R.P.M.		1425	Pull-up Torque		11.6 LB-FT	
Hz	50 Phase	3	Locked-rotor Torque		15.7 LB-FT	
NEMA Design Code		B KVA Code	Starting Current		12.3 A	
Service Factor (S.F.)		1.25	No-load Current		1.63 A	
NEMA Nom. Eff.		70 Power Factor	Line-line Res. @ 25°C		17.1 Ω	
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		78°C	
S.F. Amps		3.6/2.1	Temp. Rise @ S.F. Load		98°C	

Load Characteristics 400 V, 50 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	25	37	48	58	64	70	64
Efficiency	50.7	64.9	70	71.8	71.4	69.9	71.4
Speed	1483	1466	1449	1431	1409	1386	1409
Line amperes	1.63	1.69	1.8	1.9	2.14	2.38	2.14


ABB Motors and Mechanical Inc.

WINDING # 34WG2382

Typical performance - not guaranteed values.



0.75 HP 3 PH 50 HZ 1425 RPM 400 V 3420M

TORQUES (LB-FT): PO=11.9 PU=11.6 LR=15.7 LRA=12.3



8/24/2026 ACPERF, record # 35180

34LYF779



CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: LOAD TO SOLIDWORKS

REV: E

VERSION: 05

REVISED: 04:43:07 09/21/2022

TDR: 000001194274

34LYF779

MODEL NO. 34LYF779

BY: ENFRAJ0


REF: -

BALDOR - RELIANCE®


HORZ 34M NEMA 56 OPEN

34LYF779

CD0022




LOW VOLTAGE
(1D)



LINE

HIGH VOLTAGE
(1Y)



LINE

- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: F	BY: JLP	REVISED: 01/21/99 3:54	TDR: 0171435
CD0022		FILE: AAA00005144	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 6 LEADS, DELTA/WYE CONNECTION

CD0022