ABB BALDOR RELIANCE

Customer information packet

L5000A-C

.25HP, 1725RPM, 1PH, 60HZ, 56, 3414L, XPFC, F1
Class - CLI GP C,D; CLII GP F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/19/2026 10:31:00 PM

Specifications

Enclosure	XPFC
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	.250 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ
	208.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	UR
	CSA
	UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.200 A @ 115.0 V
	2.100 A @ 230.0 V
	2.000 A @ 208.0 V
Design Code	N
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	62.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part Detail

Revision	U
Type	AC
Mech. spec.	34-6864
Base	
Status	PRD/A
Elec. spec.	34WGY855
Layout	34LY6864
Eff. date	02-27-2026
CD Diagram	CD0565
Poles	04
Leads	7#18
Proprietary	False
Created date	12-05-2007

Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	2.0 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	7 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3414L
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.22 IN
Power Factor	64
Product Family	Hazardous Location Motor
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Do Not Use Eve-Not Valiid

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1 Location	EP

Nameplate

NP0301XPSL							
NO.		**CC**					
SER.							
SPEC.	34-6864Y855G1						
CAT.NO.	L5000A-C						
HP	.25	**T. CODE**	T3C				
VOLTS	115/208-230						
AMPS	4.2/2-2.1						
RPM	1725						
HZ	60	**PH**	1	**CL**	B		
SER.F.	1.00	**DES**	N	**CODE**	L		
RATING	40C AMB-CONT						
FRAME	56			**NEMA-NOM-EFF**	62		
		PF	64				
BLANK							


AC Induction Motor Performance Data
Record # 36349
Typical performance - not guaranteed values

Winding: 34WGY855-R006	**Type:** 3414L	**Enclosure:** XPFC

Nameplate Data				**230 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			.25	**Full Load Torque**	0.762 LB-FT
Volts			115/208-230	**Start Configuration**	direct on line
Full Load Amps			4.2/2-2.1	**Breakdown Torque**	2.38 LB-FT
R.P.M.			1725	**Pull-up Torque**	1.68 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	2.83 LB-FT
NEMA Design Code	N	**KVA Code**	L	**Starting Current**	10.8 A
Service Factor (S.F.)			1	**No-load Current**	1.67 A
NEMA Nom. Eff.	62	**Power Factor**	64	**Line-line Res. @ 25ºC**	9.23 Ω A Ph 8.97 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	43°C

Load Characteristics 230 V, 60 Hz, 0.25 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	35	47	54	64	69	72
Efficiency	35.2	50	60.6	61.8	65.7	71.6
Speed	1780	1767	1753	1738	1722	1711
Line amperes	1.69	1.78	1.88	2.07	2.23	2.35


ABB Motors and Mechanical Inc.
WINDING # 34WGY855
Typical performance - not guaranteed values.
0.25 HP 1 PH 60 HZ 1725 RPM 230 V 3414L
TORQUES(LB-FT): PO=2.38 PU=1.68 LR=2.83 LRA=10.8
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
PERCENT OF RATED OUTPUT (0.25 HP)
11/19/2026 ACPERF, record # 36349

AC Induction Motor Performance Data
Record # 41431
Typical performance - not guaranteed values

Winding: 34WGY855-R006	**Type:** 3414L	**Enclosure:** XPFC

Nameplate Data				**115 V, 60 Hz: Low Voltage Connection**	
Rated Output (HP)			.25	**Full Load Torque**	0.762 LB-FT
Volts			115/208-230	**Start Configuration**	direct on line
Full Load Amps			4.2/2-2.1	**Breakdown Torque**	2.38 LB-FT
R.P.M.			1725	**Pull-up Torque**	1.68 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	2.83 LB-FT
NEMA Design Code	N	**KVA Code**	L	**Starting Current**	21.6 A
Service Factor (S.F.)			1	**No-load Current**	3.34 A
NEMA Nom. Eff.	62	**Power Factor**	64	**Line-line Res. @ 25ºC**	2.22 Ω A Ph 8.87 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	

Load Characteristics 115 V, 60 Hz, 0.25 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	35	47	55	64	69	72
Efficiency	35.2	50	60.6	61.9	65.6	71.2
Speed	1780	1767	1753	1738	1722	1711
Line amperes	3.38	3.56	3.76	4.14	4.46	4.7


ABB Motors and Mechanical Inc.

WINDING # 34WGY855


0.25 HP 1 PH 60 HZ 1725 RPM 115 V 3414L


TORQUES(LB-FT): PO=2.38 PU=1.68 LR=2.83 LRA=21.6


Typical performance - not guaranteed values.




34LY6864







FRONT END DETAIL



PULLEY END DETAIL

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION


REV. DESC: LOAD TO SOLIDWORKS - REV F			
REV: G	VERSION: 07	REVISED: 03:04:45 12/16/2022	TDR: 000001201165
34LY6864	MODEL NO. 34LY6864		REF: -
	BY: ENFRAJ0		

BALDOR - RELIANCE®

HORZ X34L 56 XPFC, CL-I GP-C&D, CL-II GP-F&G, .75 NPT

34LY6864

CD0565




	LINE A	LINE B	JOIN	JOIN
HIGH STD	1	4	2,3,8	J,5
HIGH OPP	1	4	2,3,5	J.8
LOW STD	1,3,8	4	–	2,J,5
LOW OPP	1,3,5	4	–	2,J,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CONNECTIONS FOR TWO–TERMINAL THERMAL



REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: C	BY: JLP	REVISED: 04/08/99 3:25	TDR: 0178636
CD0565		FILE: AAA00014311	MDL: –
		MTL: –	

BALDOR ELECTRIC Co.

TYPE L, DV, REV, THERMAL, 7 LD, 34XP

CD0565