

ABB BALDOR RELIANCE III

Customer information packet

M3532

, RPM, 3PH, HZ, 56, 3516M, TEFC, F1, N

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.250 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	900 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ 208.0 V @ 60 HZ
Agency Approvals	C UR US
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.200 A @ 230.0 V 2.000 A @ 208.0 V 1.100 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	55.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.1 a
Insulation Class	F

Part Detail

Revision	K
Type	AC
Mech. spec.	35A011
Base	
Status	PRD/A
Elec. spec.	35WGG345
Layout	35LYA011
Eff. date	01-02-2026
CD Diagram	CD0005
Poles	08
Leads	9#18
Proprietary	False
Created date	02-23-2023

Inverter Code	Not Inverter
IP Rating	NONE
KVA Code	R
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3516M
Mounting Arrangement	F1
Number of Poles	8
Overall Length	12.23 IN
Power Factor	39
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.35
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	870 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L											
CAT.NO.	M3532										
SPEC.	35A011G345G1										
HP	.25										
VOLTS	208-230/460										
AMP	2-2.2/1.1										
RPM	870										
FRAME	56		HZ	60			PH	3			
SER.F.	1.35		CODE	R	DES	B	CLASS	F			
NEMA-NOM-EFF	55		PF	39							
RATING	40C AMB-CONT										
CC											
DE	6205		ODE	6203							
ENCL	TEFC		SN								
	SFA 2-2.2/1.1										

Accessories

Part number	Description	Multiplier
35-8762	C FACE KIT	A8
35EP1506A01SP	D-FLANGE KIT	A8

AC Induction Motor Performance Data

Record # 87800

Preliminary Data Sheet

Winding: 35WGG345-R003			Type: 3516M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		.25	Full Load Torque		1.5 LB-FT		
Volts		208-230/460	Start Configuration		direct on line		
Full Load Amps		2-2.2/1.1	Breakdown Torque		8.6 LB-FT		
R.P.M.		870	Pull-up Torque		4.9 LB-FT		
Hz	60 Phase	3	Locked-rotor Torque		5.3 LB-FT		
NEMA Design Code		B	KVA Code		R	Starting Current	4.7 A
Service Factor (S.F.)		1.35	No-load Current		1.04 A		
NEMA Nom. Eff.		55	Power Factor		39	Line-line Res. @ 25°C	54 Ω
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		54°C		
S.F. Amps		2-2.2/1.1	Temp. Rise @ S.F. Load		59°C		
			Locked-rotor Power Factor		69.8		
			Rotor inertia		0.116 lb-ft²		

Load Characteristics 460 V, 60 Hz, 0.25 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	21	27	33	39	44	50	48
Efficiency	27.7	42.1	50.5	56.6	60.3	62.1	63.6
Speed	895	890	884	878	871	861	863
Line amperes	1.03	1.04	1.04	1.06	1.09	1.13	1.02

ABB Motors and Mechanical Inc.

WINDING # 35WGG345

Typical performance - not guaranteed values.

0.25 HP 3 PH 60 HZ 870 RPM 460 V 3516M

TORQUES (LB-FT): PO=8.6 PU=4.9 LR=5.3 LRA=4.7



