



Customer information packet

M1024T

5/2.2HP, 1725/1140RPM, 3PH, 60HZ, 215T, 3735M

Class - None

Division - Not Applicable

Specifications

Enclosure	OPEN
Frame	215T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ 2.200 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	12.800 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	7.0 a
Insulation Class	F
Inverter Code	Not Inverter

Part detail

Revision	AG
Type	AC
Mech. spec.	37B001
Base	
Status	PRD/A
Elec. spec.	37WGW024
Layout	37LYB001
Eff. date	05-10-2024
CD Diagram	CD0013
Poles	04/06
Leads	6#14
Proprietary	False
Created date	01-01-0001

KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3735M
Mounting Arrangement	F1
Number of Poles	4 6
Overall Length	16.32 IN
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1140 rpm 1725 rpm
Speed Code	2S-2W-VT
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.	M1024T								
SPEC.	37B01W24								
HP	5/2.2								
VOLTS	230								
AMP	12.8/7								
RPM	1725/1140								
FRAME	215T		HZ	60		PH	3		
SER.F.	1.15	CODE	J	DES	B	CLASS	F		
NEMA-NOM-EFF		PF							
RATING	40C AMB-CONT								
CC									
DE	6307		ODE	6206					
ENCL	OPEN	SN							

Accessories

Part number	Description	Multiplier
37-1404	C FACE KIT	A8

AC Induction Motor Performance Data

Record # 37312

Typical performance - not guaranteed values

Winding: 37GW024-R003		Type: 3735M	Enclosure: TEFC
Nameplate Data		230 V, 60 Hz: High Speed Connection	
Rated Output (HP)	5/2.2	Full Load Torque	15 LB-FT
Volts	230	Start Configuration	direct on line
Full Load Amps	12.8/7	Breakdown Torque	50 LB-FT
R.P.M.	1725/1140	Pull-up Torque	38 LB-FT
Hz	60 Phase	Locked-rotor Torque	49 LB-FT
NEMA Design Code	B KVA Code	Starting Current	92 A
Service Factor (S.F.)	1.15	No-load Current	4.6 A
NEMA Nom. Eff.	0 Power Factor	Line-line Res. @ 25°C	1.05 Ω
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	57°C
S.F. Amps		Temp. Rise @ S.F. Load	70°C

Load Characteristics 230 V, 60 Hz, 5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	56	73	83	86	88	91	87
Efficiency	76.3	82.4	83.2	81.6	80	76.9	80.6
Speed	1779	1759	1738	1715	1689	1658	1699
Line amperes	5.6	7.8	10.2	13	16	19	14.8


ABB Motors and Mechanical Inc.

WINDING # 37WGW024

5 HP 3 PH 60 HZ 1715 RPM 230 V 3735M

Typical performance - not guaranteed values.

TORQUES (LB-FT) : PO=50 PU=38 LR=49 LRA=92



9/12/2024 ACPERF, record # 37312

AC Induction Motor Performance Data

Record # 37313

Typical performance - not guaranteed values

Winding: 37GW024-R003		Type: 3735M	Enclosure: TEFC
Nameplate Data		230 V, 60 Hz: Low Speed Connection	
Rated Output (HP)	5/2.2	Full Load Torque	10 LB-FT
Volts	230	Start Configuration	direct on line
Full Load Amps	12.8/7	Breakdown Torque	29 LB-FT
R.P.M.	1725/1140	Pull-up Torque	20 LB-FT
Hz	60 Phase	Locked-rotor Torque	21 LB-FT
NEMA Design Code	B KVA Code	Starting Current	42 A
Service Factor (S.F.)	1.15	No-load Current	4.2 A
NEMA Nom. Eff.	0 Power Factor	Line-line Res. @ 25°C	2.17 Ω
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	33°C
S.F. Amps		Temp. Rise @ S.F. Load	39°C

Load Characteristics 230 V, 60 Hz, 2.2 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	37	53	64	73	78	81	76
Efficiency	65.9	76.2	78.6	79.1	78.5	76.8	78.7
Speed	1189	1179	1170	1159	1147	1133	1152
Line amperes	4.4	5.2	6.2	7.2	8.4	9.8	7.92


ABB Motors and Mechanical Inc.

WINDING # 37WGW024


Typical performance - not guaranteed values.

2.2 HP 3 PH 60 HZ 1159 RPM 230 V 3735M



TORQUES (LB-FT) : PO=29 PU=20 LR=21 LRA=42



9/12/2024 ACPERF, record # 37313



CD0013



NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0013

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: D	BY: JLP	REVISED: 01/22/99 8:50	TDR: 0171435
Ω 10000		FILE: AAA00005143	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, SV, 6 LEADS, 2-SPEED 2-WINDING