

ABB BALDOR RELIANCE III

Customer information packet

M1519

.75/.33HP, 1730/1165RPM, 3PH, 60HZ, 56, 3524M

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 60 HZ .330 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.600 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.8 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K

Part Detail

Revision	D
Type	AC
Mech. spec.	35A011
Base	
Status	PRD/A
Elec. spec.	35WGG349
Layout	35LYA011
Eff. date	06-24-2025
CD Diagram	CD0013
Poles	04/06
Leads	6#18 Y
Proprietary	False
Created date	02-23-2023

Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3524M
Mounting Arrangement	F1
Number of Poles	4 6
Overall Length	13.23 IN
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1165 rpm 1730 rpm
Speed Code	2S-2W-VT
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.	M1519								
SPEC.	35A011G349								
HP	.75/.33								
VOLTS	230								
AMP	2.6/1.8								
RPM	1730/1165								
FRAME	56		HZ	60			PH	3	
SER.F.	1.15		CODE	K	DES	B	CLASS	F	
NEMA-NOM-EFF			PF						
RATING	40C AMB-CONT								
CC									
DE	6205		ODE	6203					
ENCL	TEFC		SN						
	SFA 2.77								

Accessories

Part number	Description	Multiplier
35-8762	C FACE KIT	A8
35EP1506A01SP	D-FLANGE KIT	A8

AC Induction Motor Performance Data

Record # 87809

Preliminary Data Sheet

Winding: 35WGG349-R002			Type: 3524M	Enclosure: TEFC			
Nameplate Data			230 V, 60 Hz: High Speed Connection				
Rated Output (HP)		.75/.33	Full Load Torque		2.28 LB-FT		
Volts		230	Start Configuration		direct on line		
Full Load Amps		2.6/1.8	Breakdown Torque		7.79 LB-FT		
R.P.M.		1730/1165	Pull-up Torque		4.68 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		6.1 LB-FT	
NEMA Design Code		B	KVA Code	K	Starting Current		16.24 A
Service Factor (S.F.)		1.15		No-load Current		1.81 A	
NEMA Nom. Eff.		0	Power Factor	0	Line-line Res. @ 25°C		10.2 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load			
				Locked-rotor Power Factor		89.7	
				Rotor inertia		0.173 lb-ft²	

Load Characteristics 230 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	35	52	67	74	81	85	78
Efficiency	54.4	68.2	72.9	74.1	73.4	71.3	73.7
Speed	1783	1768	1752	1733	1709	1682	1719
Line amperes	1.9	2.06	2.21	2.56	2.91	3.35	2.77


ABB Motors and Mechanical Inc.

WINDING # 35WGG349

Typical performance - not guaranteed values.

0.75 HP 3 PH 60 HZ 1733 RPM 230 V 3524M

TORQUES (LB-FT): PO=7.79 PU=4.68 LR=6.1 LRA=16.24



AC Induction Motor Performance Data

Record # 87810

Preliminary Data Sheet

Winding: 35WGG349-R002			Type: 3524M		Enclosure: TEFC		
Nameplate Data				230 V, 60 Hz: Low Speed Connection			
Rated Output (HP)		.75/.33		Full Load Torque		1.48 LB-FT	
Volts		230		Start Configuration		direct on line	
Full Load Amps		2.6/1.8		Breakdown Torque		6.14 LB-FT	
R.P.M.		1730/1165		Pull-up Torque		2.77 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		4.09 LB-FT	
NEMA Design Code		B	KVA Code	K	Starting Current		8.58 A
Service Factor (S.F.)		1.15		No-load Current		1.71 A	
NEMA Nom. Eff.		0	Power Factor	0	Line-line Res. @ 25°C		19.7 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load			
				Locked-rotor Power Factor		88.2	
				Rotor inertia		0.173 lb-ft²	

Load Characteristics 230 V, 60 Hz, 0.33 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	27	36	45	53	61	67	58
Efficiency	34.1	50.2	59	64.1	67	68.5	65.8
Speed	1193	1187	1181	1175	1168	1160	1171
Line amperes	1.71	1.72	1.76	1.82	1.9	2.01	1.87


ABB Motors and Mechanical Inc.

WINDING # 35WGG349

Typical performance - not guaranteed values.

0.33 HP 3 PH 60 HZ 1175 RPM 230 V 3524M

TORQUES (LB-FT): PO=6.14 PU=2.77 LR=4.09 LRA=8.58



9/2/2026 ACPERF, record # 87810



