ABB BALDOR RELIANCE

Customer information packet

M1556T

2-.5HP, 1730-865RPM, 3PH, 60HZ, 145T, 3528M, T
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/18/2026 11:04:35 AM

Specifications

Enclosure	TEFC
Frame	145T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.500 HP @ 60 HZ
	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	900 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	208.0 V @ 60 HZ
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	6.490 A @ 208.0 V
	2.740 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.7 a
Insulation Class	F

Part Detail

Revision	D
Type	AC
Mech. spec.	35AA001
Base	
Status	PRD/A
Elec. spec.	35WGG364
Layout	35LYAA001
Eff. date	10-28-2025
CD Diagram	CD0032
Poles	04/08
Leads	6#18
Proprietary	False
Created date	02-23-2023

Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3528M
Mounting Arrangement	F1
Number of Poles	4
	8
Overall Length	13.31 IN
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1730 rpm
	865 rpm
Speed Code	2S-1W-VT
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L											
CAT.NO.	M1556T										
SPEC.	35AA001G364G1										
HP	2-.5										
VOLTS	208-230										
AMP	6.49-2.74										
RPM	1730-865										
FRAME	145T	**HZ**	60			**PH**	3				
SER.F.	1.15	**CODE**	K	**DES**	B	**CLASS**	F				
NEMA-NOM-EFF		**PF**									
RATING	40C AMB-CONT										
CC											
DE	6205	**ODE**	6203								
ENCL	TEFC	**SN**									
	SFA 7.11-7.07										

Accessories

Part number	Description	Multiplier
35-8762	C FACE KIT	A8
35EP1506A01SP	D-FLANGE KIT	A8

AC Induction Motor Performance Data
Record # 87880
Typical performance - not guaranteed values

Winding: 35WGG364-R002	**Type:** 3528M	**Enclosure:** OPEN

Nameplate Data			
Rated Output (HP)			2/.5
Volts			208-230
Full Load Amps			6.49/2.74
R.P.M.			1730/865
Hz	60	**Phase**	3
NEMA Design Code	B	**KVA Code**	K
Service Factor (S.F.)			1.15
NEMA Nom. Eff.	0	**Power Factor**	0
Rating - Duty			40C AMB-CONT
S.F. Amps			

230 V, 60 Hz: High Speed Connection	
Full Load Torque	6.01 LB-FT
Start Configuration	direct on line
Breakdown Torque	20.99 LB-FT
Pull-up Torque	15.62 LB-FT
Locked-rotor Torque	16.73 LB-FT
Starting Current	40.21 A
No-load Current	4.12 A
Line-line Res. @ 25ºC	3 Ω
Temp. Rise @ Rated Load	51°C
Temp. Rise @ S.F. Load	61°C
Locked-rotor Power Factor	81.9
Rotor inertia	0.202 lb-ft²

Load Characteristics 230 V, 60 Hz, 2 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	31	49	64	70	77	83	74
Efficiency	71	80.4	82.1	81.1	79.7	77.9	80.3
Speed	1753	1768	1750	1729	1709	1690	1717
Line amperes	4.27	4.81	5.33	6.49	7.46	8.45	7.07


ABB Motors and Mechanical Inc.

WINDING # 35WGG364

2 HP 3 PH 60 HZ 1729 RPM 230 V 3528M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=20.99 PU=15.62 LR=16.73 LRA=40.21



AC Induction Motor Performance Data
Record # 87881
Typical performance - not guaranteed values

Winding: 35WGG364-R002	**Type:** 3528M	**Enclosure:** OPEN

Nameplate Data			
Rated Output (HP)			2/.5
Volts			208-230
Full Load Amps			6.49/2.74
R.P.M.			1730/865
Hz	60	**Phase**	3
NEMA Design Code	B	**KVA Code**	K
Service Factor (S.F.)			1.15
NEMA Nom. Eff.	0	**Power Factor**	0
Rating - Duty			40C AMB-CONT

230 V, 60 Hz: Low Speed Connection	
Full Load Torque	3.02 LB-FT
Start Configuration	direct on line
Breakdown Torque	10.7 LB-FT
Pull-up Torque	5.52 LB-FT
Locked-rotor Torque	7.67 LB-FT
Starting Current	10.4 A
No-load Current	2.47 A
Line-line Res. @ 25ºC	12 Ω
Temp. Rise @ Rated Load	
Locked-rotor Power Factor	81.9
Rotor inertia	0.202 lb-ft²

Load Characteristics 230 V, 60 Hz, 0.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	24	34	43	52	59	66	56
Efficiency	39.5	55.5	63.4	67.5	69.4	69.9	68.6
Speed	892.2	885.3	877.8	869.6	860.6	850.5	864
Line amperes	2.47	2.5	2.57	2.69	2.84	3.05	2.78


ABB Motors and Mechanical Inc.


WINDING # 35WGG364

0.5 HP 3 PH 60 HZ 869.6 RPM 230 V 3528M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=10.7 PU=5.52 LR=7.67 LRA=10.4




35LYAA001
510-520 = 12.28
521-528 = 13.28
529-535 = 14.16
536-546 = 15.53
3.75
2.50
2.25
GREASE FITTING
(EACH END)
NAMEPLATE
Ø7.19
.19 KEY
1.38 LONG
Ø .8750
.8745
4.00
2.25
5.00
.50
5.94
6 HOLES
.38 DIA.
6.61
5.71
4.55
6.78
3.50
3.44
THERMAL
(WHEN
REQ'D)
LEAD HOLE
1.09 DIA.
2.75
2.75
4.59
3.25
6.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD THERMAL DIMS AND THERMAL WHEN REQUIRED NOTE
REV: F
VERSION: 06
REVISED: 12:55:25 03/10/2023
TDR: 000001205626
MODEL NO. 35LYAA001
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
STD HORZ 143-5T TEFC 35M W/1.09 LEAD HOLE
35LYAA001

CD0032





NOTES:
1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0032

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/22/99 8:27	TDR: 0171435
CD0032		FILE: AAA00005145	MDL: –
		MTL: –	3PH, SV, 6 LEADS, 2–SPEED 1–WINDING VARIABLE TORQUE