ABB BALDOR RELIANCE

Customer information packet

M3615T-57

5HP, 1455RPM, 3PH, 50HZ, 184T, 3646M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/20/2026 3:07:33 AM

Specifications

Enclosure	TEFC
Frame	184T
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	1500 RPM @ 50 HZ
Voltage @ Frequency	230.0 V @ 50 HZ
	400.0 V @ 50 HZ
Agency Approvals	CSA
	CE
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	13.000 A @ 230.0 V
	7.500 A @ 400.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	87.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	N
Type	AC
Mech. spec.	36A001
Base	
Status	NLA/A
Elec. spec.	36WGS811
Layout	36LYA001
Eff. date	10-28-2016
CD Diagram	CD0022
Poles	04
Leads	6#16
Proprietary	False
Created date	09-20-2011

High Voltage Full Load Amps	7.5 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3646M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.04 IN
Power Factor	81
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1455 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP2717L									
CAT NO	M3615T-57								
SPEC.	36A001S811H1								
HP	5					**PH**	3		
VOLTS	230/400								
AMP	13/7.5								
FRAME	184T		**HZ**	50			**I.P.**	54	
SER.F.	1.15	**CODE**	J	**DES**	B	**CL**	F		
NEMA-NOM-EFF	87.5							**% (100%)**	
PF	81								
RATING	40C AMB-CONT			**CC**					
DE BRG	6206		**ODE**	6205					
ENCL	TEFC	**SN**							
BLANK	IE2-88.0(75%)86.5(50%)								

AC Induction Motor Performance Data
Record # 35242
Typical performance - not guaranteed values

Winding: 36WGS811-R001	**Type:** 3646M	**Enclosure:** TEFC

Nameplate Data				**400 V, 50 Hz: High Voltage Connection**	
Rated Output (HP)			5	**Full Load Torque**	18.1 LB-FT
Volts			230/400	**Start Configuration**	direct on line
Full Load Amps			13/7.5	**Breakdown Torque**	81.1 LB-FT
R.P.M.			1455	**Pull-up Torque**	36.7 LB-FT
Hz	50	**Phase**	3	**Locked-rotor Torque**	48.3 LB-FT
NEMA Design Code	B	**KVA Code**	J	**Starting Current**	53 A
Service Factor (S.F.)			1.15	**No-load Current**	3.87 A
NEMA Nom. Eff.	87.5	**Power Factor**	81	**Line-line Res. @ 25ºC**	2.12 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	80°C
S.F. Amps				**Temp. Rise @ S.F. Load**	100°C
				Locked-rotor Power Factor	44
				Rotor inertia	0.428 LB-FT2

Load Characteristics 400 V, 50 Hz, 5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	38	61	73	81	84	87	83
Efficiency	82.7	86.5	88	88.1	86.8	84.9	87.4
Speed	1490	1479	1467	1454	1440	1423	1446
Line amperes	4.16	4.98	6.18	7.54	9.23	10.9	8.55


ABB Motors and Mechanical Inc.

WINDING # 36WGS811


5 HP 3 PH 50 HZ 1455 RPM 400 V 3646M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=81.1 PU=36.7 LR=48.3 LRA=53





11/20/2026 ACPERF, record # 35242


36LYA001
614 - 623 = 15.17
624 - 634 = 16.54
635 - 646 = 18.04
635-646
OR WHEN REQ'D
GREASE FITTING
(EACH END)
3.56
2.75
4.27
.25 KEY
1.75 LONG
NAMEPLATE
Ø8.60
Ø 1.1250
1.1245
6 HOLES
Ø.44
4.50
2.75
5.50
.50
6.50
Ø7.87
6.88
2.24
8.43
4.50
4.44
LEAD HOLE
Ø1.09
3.75
3.75
5.76
4.31
8.63
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD "WHEN REQ'D" TO LIFTING CALLOUT
REV: Y
VERSION: 08
REVISED: 02:20:29 01/16/2026
TDR: 000001270424
MODEL NO. 36LYA001
REF: -
BY: USTRTAY1
B
BALDOR - RELIANCE®
STD HORZ 182-4T TEFC 36M
36LYA001

CD0022







NOTES:
1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: F	BY: JLP	REVISED: 01/21/99 3:54	TDR: 0171435
CD0022		FILE: AAA00005144	MDL: –
		MTL: –	3PH, DV, 6 LEADS, DELTA/WYE CONNECTION

CD0022