

ABB BALDOR RELIANCE III

Customer information packet

M1720T

1/.44HP, 1740/1170RPM, 3PH, 60HZ, 145T, 3528M

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	145T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ .440 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.900 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.2 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K

Part Detail

Revision	E
Type	AC
Mech. spec.	35AA001
Base	
Status	PRD/A
Elec. spec.	35WGG347
Layout	35LYAA001
Eff. date	01-15-2026
CD Diagram	CD0013
Poles	04/06
Leads	6#18 Y
Proprietary	False
Created date	02-23-2023

Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3528M
Mounting Arrangement	F1
Number of Poles	4 6
Overall Length	13.31 IN
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1170 rpm 1740 rpm
Speed Code	2S-2W-VT
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.	M1720T								
SPEC.	35AA001G347								
HP	1/.44								
VOLTS	460								
AMP	1.9/1.21								
RPM	1740/1170								
FRAME	145T		HZ	60			PH	3	
SER.F.	1.15	CODE	K	DES	B	CLASS	F		
NEMA-NOM-EFF		PF							
RATING	40C AMB-CONT								
CC									
DE	6205		ODE	6203					
ENCL	TEFC	SN							
	SFA 1.74								

Accessories

Part number	Description	Multiplier
35-8762	C FACE KIT	A8
35EP1506A01SP	D-FLANGE KIT	A8

AC Induction Motor Performance Data

Record # 87889

Preliminary Data Sheet

Winding: 35WGG347-R002			Type: 3528M		Enclosure: TEFC		
Nameplate Data				460 V, 60 Hz: High Speed Connection			
Rated Output (HP)		1/.44		Full Load Torque		3.07 LB-FT	
Volts		460		Start Configuration		direct on line	
Full Load Amps		1.9/1.21		Breakdown Torque		10.46 LB-FT	
R.P.M.		1740/1170		Pull-up Torque		6.25 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		10.1 LB-FT	
NEMA Design Code		B	KVA Code	K	Starting Current		10.99 A
Service Factor (S.F.)		1.15		No-load Current		1.13 A	
NEMA Nom. Eff.		0	Power Factor	0	Line-line Res. @ 25°C		28.9 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load			
				Locked-rotor Power Factor		87.2	
				Rotor inertia		0.202 lb-ft²	

Load Characteristics 460 V, 60 Hz, 1 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	36	54	68	77	83	86	81
Efficiency	59.5	71.8	76.3	77.3	76.7	74.7	76.9
Speed	1784	1771	1756	1739	1719	1696	1727
Line amperes	1.15	1.25	1.39	1.6	1.84	2.15	1.74


ABB Motors and Mechanical Inc.

WINDING # 35WGG347

Typical performance - not guaranteed values.

1 HP 3 PH 60 HZ 1739 RPM 460 V 3528M

TORQUES (LB-FT): PO=10.46 PU=6.25 LR=10.1 LRA=10.99



AC Induction Motor Performance Data

Record # 87890

Preliminary Data Sheet

Winding: 35WGG347-R002			Type: 3528M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: Low Speed Connection				
Rated Output (HP)		1/.44	Full Load Torque		1.98 LB-FT		
Volts		460	Start Configuration		direct on line		
Full Load Amps		1.9/1.21	Breakdown Torque		7.7 LB-FT		
R.P.M.		1740/1170	Pull-up Torque		4.83 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		5.29 LB-FT	
NEMA Design Code		B	KVA Code	K	Starting Current		5.18 A
Service Factor (S.F.)		1.15		No-load Current		0.922 A	
NEMA Nom. Eff.		0	Power Factor	0	Line-line Res. @ 25°C		60.5 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load			
				Locked-rotor Power Factor		84.6	
				Rotor inertia		0.202 lb-ft²	

Load Characteristics 460 V, 60 Hz, 0.44 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	26	38	48	57	65	72	62
Efficiency	42.5	58.5	66.1	70	71.8	72.3	71.1
Speed	1192	1186	1178	1171	1162	1153	1166
Line amperes	0.923	0.94	0.974	1.03	1.1	1.19	1.07


ABB Motors and Mechanical Inc.


WINDING # 35WGG347

Typical performance - not guaranteed values.


0.44 HP 3 PH 60 HZ 1171 RPM 460 V 3528M

TORQUES (LB-FT): PO=7.7 PU=4.83 LR=5.29 LRA=5.18






CD0013




LOW SPEED



LINE

HIGH SPEED



LINE

- NOTES:
1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0013

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: D	BY: JLP	REVISED: 01/22/99 8:50	TDR: 0171435
CD0013		FILE: AAA00005143	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, SV, 6 LEADS, 2-SPEED 2-WINDING