


ABB Motors and Generators		Technical Data Sheet - DOL			
		Project		Location	
Department/Author		Customer name		Customer ref.	Item name
Our ref.		Rev/Changed by	Date of issue	Saving ident	Pages 1(3)

No.	Definition	Data	Unit	Remarks
1	Product	TEFC, 3-phase, squirrel cage induction motor		
2	Product code	MM11044-EX1 (3GGP112330-ASH+332)		
3	Type/Frame	M3GP 112 MC 4		
4	Mounting	IM1001, B3(foot)		
5	Rated output P _N	4	kW	
6	Service factor	1		
7	Type of duty	S1(IEC) 100%		
8	Rated voltage U _N	230	VD	± 5 % (IEC 60034-1)
9	Rated frequency f _N	50	Hz	± 2 % (IEC 60034-1)
10	Rated speed n _N	1458	r/min	
11	Rated current I _N	14.5	A	
12	No-load current	9.6	A	
13	Starting current I _s /I _N	8.7		Fullfilled IEC 60034-12 design N,H
14	Nominal torque T _N	26.2	Nm	
15	Locked rotor torque T _S /T _N	3		
16	Maximum torque T _{max} /T _N	3.8		
17	Minimum torque T _{min} /T _N	2.8		
18	Speed at minimum torque	225	r/min	
19	Load characteristics (IEC 60034-2-1:2007)	Load %	Current A	Efficiency % Power factor
20	PLL determined from residual loss	100	14.5	88.2 / IE2 0.78
21		75	12	87.8 0.71
22		50	9.7	85.6 0.6
23		Start	126	0.51
24	Maximum starting time from hot	15	s	
25	Maximum starting time from cold	27	s	
26	Insulation class / Temperature class	F / B		
27	Ambient temperature	40	°C	
28	Altitude	1000	m.a.s.l.	
29	Enclosure	IP55		
30	Cooling system	IC411 self ventilated		
31	Bearing DE/NDE	6206-2Z/C3 - 6206-2Z/C3		
32	Type of Grease	Greased for life		
33	Sound pressure level (LP dB(A) 1m)	52	dB(A)	at load
34	Moment of inertia J = ¼ GD2	0.013	kg-m2	
35	Balancing	Half Key		
36	Vibration class	Grade A		
37	Position of terminal box	Top		
38	Terminal box entries; no, dims.	2xM32x1.5 + 1xM20x1.5		
39	Number of power terminals	6		
40	Direction of rotation	CW or CCW		
41	Weight of rotor	9	kg	
42	Total weight of motor	72	kg	
43				
Ex-motors				
44	Type of protection	*Ex nA II T3		
45				
Variant Codes / Definition				
	332 = Baldor catalog number			
Remarks:				
Data based on situation 11/5/2012				
All data subject to tolerances in accordance with IEC				
Guaranteed values on request				
* For more information on the Atex/IECEx rating, please contact your local Baldor representative.				







ABB Motors and Generators		Technical Data Sheet - DOL			
		Project		Location	
Department/Author		Customer name		Customer ref.	Item name
Our ref.		Rev/Changed by	Date of issue	Saving ident	Pages 1(3)

No.	Definition	Data	Unit	Remarks
1	Product	TEFC, 3-phase, squirrel cage induction motor		
2	Product code	MM11044-EX1 (3GGP112330-ASH+332)		
3	Type/Frame	M3GP 112 MC 4		
4	Mounting	IM1001, B3(foot)		
5	Rated output P _N	4	kW	
6	Service factor	1		
7	Type of duty	S1(IEC) 100%		
8	Rated voltage U _N	400	VY	± 5 % (IEC 60034-1)
9	Rated frequency f _N	50	Hz	± 2 % (IEC 60034-1)
10	Rated speed n _N	1458	r/min	
11	Rated current I _N	8.3	A	
12	No-load current	5.5	A	
13	Starting current I _s /I _N	8.7		Fullfilled IEC 60034-12 design N,H
14	Nominal torque T _N	26.2	Nm	
15	Locked rotor torque T _s /T _N	3		
16	Maximum torque T _{max} /T _N	3.8		
17	Minimum torque T _{min} /T _N	2.8		
18	Speed at minimum torque	225	r/min	
19	Load characteristics (IEC 60034-2-1:2007)	Load %	Current A	Efficiency % Power factor
20	PLL determined from residual loss	100	8.3	88.2 / IE2 0.78
21		75	6.9	87.8 0.71
22		50	5.6	85.6 0.6
23		Start	73	0.51
24	Maximum starting time from hot	15	s	
25	Maximum starting time from cold	27	s	
26	Insulation class / Temperature class	F / B		
27	Ambient temperature	40	°C	
28	Altitude	1000	m.a.s.l.	
29	Enclosure	IP55		
30	Cooling system	IC411 self ventilated		
31	Bearing DE/NDE	6206-2Z/C3 - 6206-2Z/C3		
32	Type of Grease	Greased for life		
33	Sound pressure level (LP dB(A) 1m)	52	dB(A)	at load
34	Moment of inertia J = ¼ GD2	0.013	kg-m2	
35	Balancing	Half Key		
36	Vibration class	Grade A		
37	Position of terminal box	Top		
38	Terminal box entries; no, dims.	2xM32x1.5 + 1xM20x1.5		
39	Number of power terminals	6		
40	Direction of rotation	CW or CCW		
41	Weight of rotor	9	kg	
42	Total weight of motor	72	kg	
43				
Ex-motors				
44	Type of protection	*Ex nA II T3		
45				
Variant Codes / Definition				
	332 = Baldor catalog number			
Remarks:				
Data based on situation 11/5/2012				
All data subject to tolerances in accordance with IEC				
Guaranteed values on request				
* For more information on the Atex/IECEx rating, please contact your local Baldor representative.				






ABB Motors and Generators		Technical Data Sheet - DOL				
		Project		Location		
Department/Author		Customer name		Customer ref.		Item name
Our ref.		Rev/Changed by	Date of issue	Saving ident		Pages 1(3)

No.	Definition	Data	Unit	Remarks	
1	Product	TEFC, 3-phase, squirrel cage induction motor			
2	Product code	MM11044-EX1 (3GGP112330-ASH+332)			
3	Type/Frame	M3GP 112 MC 4			
4	Mounting	IM1001, B3(foot)			
5	Rated output P _N	4	kW		
6	Service factor	1			
7	Type of duty	S1(IEC) 100%			
8	Rated voltage U _N	415	VY	± 5 % (IEC 60034-1)	
9	Rated frequency f _N	50	Hz	± 2 % (IEC 60034-1)	
10	Rated speed n _N	1461	r/min		
11	Rated current I _N	8.4	A		
12	No-load current	5.9	A		
13	Starting current I _s /I _N	9.2		Fullfilled IEC 60034-12 design N,H	
14	Nominal torque T _N	26.1	Nm		
15	Locked rotor torque T _S /T _N	3.3			
16	Maximum torque T _{max} /T _N	4.1			
17	Minimum torque T _{min} /T _N	3			
18	Speed at minimum torque	225	r/min		
19	Load characteristics (IEC 60034-2-1:2007)	Load %	Current A	Efficiency %	Power factor
20	PLL determined from residual loss	100	8.4	88.1 / IE2	0.75
21		75	6.9	87.5	0.69
22		50	5.8	84.9	0.56
23		Start	77		0.52
24	Maximum starting time from hot	15	s		
25	Maximum starting time from cold	30	s		
26	Insulation class / Temperature class	F / B			
27	Ambient temperature	40	°C		
28	Altitude	1000	m.a.s.l.		
29	Enclosure	IP55			
30	Cooling system	IC411 self ventilated			
31	Bearing DE/NDE	6206-2Z/C3 - 6206-2Z/C3			
32	Type of Grease	Greased for life			
33	Sound pressure level (LP dB(A) 1m)	52	dB(A)	at load	
34	Moment of inertia J = ¼ GD2	0.013	kg-m2		
35	Balancing	Half Key			
36	Vibration class	Grade A			
37	Position of terminal box	Top			
38	Terminal box entries; no, dims.	2xM32x1.5 + 1xM20x1.5			
39	Number of power terminals	6			
40	Direction of rotation	CW or CCW			
41	Weight of rotor	9	kg		
42	Total weight of motor	72	kg		
43					
Ex-motors					
44	Type of protection	*Ex nA II T3			
45					
Variant Codes / Definition					
	332 = Baldor catalog number				
Remarks:					
Data based on situation 11/5/2012					
All data subject to tolerances in accordance with IEC					
Guaranteed values on request					
* For more information on the Atex/IECEx rating, please contact your local Baldor representative.					

