

ABB Motors and Generators		Technical Data Sheet - DOL		
Project		Location		
Department/Author	Customer name	Customer ref.		Item name 1.00001
Our ref.	Rev/Changed by A	Date of issue 2/1/2016	Saving ident untitled.xls	Pages 1(3)
No.	Definition	Data	Unit	Remarks
1	Product	TEFC, 3-phase, squirrel cage induction motor		
2	Product code	MM20304-PPN (3GBP202410-A) Calc. ref. 3GZF021020-202		
3	Type/Frame	M3BP 200MLA 4		
4	Mounting	IM1001, B3(foot)		
5	Rated output P_N	30	kW	
6	Service factor	1		
7	Type of duty	S1(IEC) 100%		
8	Rated voltage U_N	400	VD	$\pm 5\%$ (IEC 60034-1)
9	Rated frequency f_N	50	Hz	$\pm 2\%$ (IEC 60034-1)
10	Rated speed n_N	1480	r/min	
11	Rated current I_N	55.1	A	
12	No-load current	18.6	A	
13	Starting current I_s/I_N	7.4		Fullfilled IEC 60034-12 design N,H
14	Nominal torque T_N	194	Nm	
15	Locked rotor torque T_s/T_N	2.8		
16	Maximum torque T_{max}/T_N	3		
17	Minimum torque T_{min}/T_N	2.2		
18	Speed at minimum torque	1050	r/min	
Load characteristics (IEC 60034-2-1:2007)		Load %	Current A	Efficiency %
19	PLL determined from residual loss	100	55.1	93.2 / IE2
20		75	43	94
21		50	31.9	93.7
22		Start	408	0.47
23	Maximum starting time from hot	15	s	
24	Maximum starting time from cold	27	s	
25	Insulation class / Temperature class	F / B		
26	Ambient temperature	40	°C	
27	Altitude	1000	m.a.s.l.	
28	Enclosure	IP55		
29	Cooling system	IC411 self ventilated		
30	Bearing DE/NDE	6312/C3 - 6210/C3		
31	Type of Grease			
32	Sound pressure level (LP dB(A) 1m)	63	dB(A)	at load
33	Moment of inertia $J = \frac{1}{4} GD^2$	0.309	kg-m2	
34	Balancing			
35	Vibration class			
36	Position of terminal box	Top		
37	Terminal box entries; no, dimens.			
38	Number of power terminals			
39	Direction of rotation	CW or CCW		
40	Total weight of motor	291	kg	
41	Dimension drawing no.			
42				
43				
44				
45				
Ex-motors				
46				
47				
48				
Option Variant Codes / Definition				
49				
50				
51				
52				
Remarks:				
Data based on situation 9/11/2015				
All data subject to tolerances in accordance with IEC				
Guaranteed values on request				

ABB Motors and Generators Load Curves			
Department/Author	Customer name	Customer ref.	Item name 1.00001
Our ref.	Rev/Changed by A	Date of issue 2/1/2016	Saving ident untitled.xls Pages 2(3)
Product	TEFC, 3-phase, squirrel cage induction motor		
Type/Frame	M3BP 200MLA 4	Calc. ref.	3GZF021020-202
Product code	3GBP 202 410-ADG		
Rated output P _N	30	kW	
Type of duty	S1(IEC) 100%		
Voltage (V)	400	Current I _N (A)	55.1
Frequency (Hz)	50	Speed (r/min)	1480
		Power factor at P _N	0.84
		Efficiency (%) at P _N	93.2
Load characteristics (IEC 60034-2-1:2007) Data based on situation 9/11/2015 All data subject to tolerances in accordance with IEC			

ABB Motors and Generators Starting Curves			
Department/Author	Customer name	Customer ref.	Item name 1.00001
Our ref.	Rev/Changed b Date of issue A 2/1/2016	Saving ident untitled.xls	Pages 3(3)
Type of product	TEFC, 3-phase, squirrel cage induction motor		
Type/Frame	M3BP 200MLA 4	Calc. ref.	3GZF021020-202
Product code	3GBP 202 410-ADG	Frequency (Hz)	50
Rated output P _N	30 kW	Rated current I _N	55.1 A
Type of duty	S1(IEC) 100%		
J _{motor} (kgm ²)	0.31	Voltage (V) 100%	400
J _{load} (kgm ²)		T _{start} /T _N	2.8
Speed (r/min)	1480	Starting time (s)	
T _N (Nm)	194	Speed (r/min)	
T _{load} (Nm)		I _s /I _N	7.4
Nbr. of Consecutive Starts at UN		T _{max} /T _N	3
Load characteristics (IEC 60034-2-1:2007) Data based on situation 9/11/2015 All data subject to tolerances in accordance with IEC			

ABB Motors and Generators		Technical Data Sheet - DOL		
Project		Location		
Department/Author	Customer name	Customer ref.		Item name 1.00001
Our ref.	Rev/Changed by A	Date of issue 2/1/2016	Saving ident untitled.xls	Pages 1(3)
No.	Definition	Data	Unit	Remarks
1	Product	TEFC, 3-phase, squirrel cage induction motor		
2	Product code	MM20304-PPN (3GBP202410-A) Calc. ref. 3GZF021020-202		
3	Type/Frame	M3BP 200MLA 4		
4	Mounting	IM1001, B3(foot)		
5	Rated output P_N	30	kW	
6	Service factor	1		
7	Type of duty	S1(IEC) 100%		
8	Rated voltage U_N	415	VD	$\pm 5\%$ (IEC 60034-1)
9	Rated frequency f_N	50	Hz	$\pm 2\%$ (IEC 60034-1)
10	Rated speed n_N	1482	r/min	
11	Rated current I_N	53.7	A	
12	No-load current	20	A	
13	Starting current I_s/I_N	7.9		Fullfilled IEC 60034-12 design N,H
14	Nominal torque T_N	193	Nm	
15	Locked rotor torque T_s/T_N	3		
16	Maximum torque T_{max}/T_N	3.3		
17	Minimum torque T_{min}/T_N	2.2		
18	Speed at minimum torque	1050	r/min	
Load characteristics (IEC 60034-2-1:2007)		Load %	Current A	Efficiency %
19	PLL determined from residual loss	100	53.7	93.4 / IE2
20		75	42	94
21		50	31.7	93.5
22		Start	424	0.48
23	Maximum starting time from hot	15	s	
24	Maximum starting time from cold	27	s	
25	Insulation class / Temperature class	F / B		
26	Ambient temperature	40	°C	
27	Altitude	1000	m.a.s.l.	
28	Enclosure	IP55		
29	Cooling system	IC411 self ventilated		
30	Bearing DE/NDE	6312/C3 - 6210/C3		
31	Type of Grease			
32	Sound pressure level (LP dB(A) 1m)	63	dB(A)	at load
33	Moment of inertia $J = \frac{1}{4} GD^2$	0.309	kg-m2	
34	Balancing			
35	Vibration class			
36	Position of terminal box	Top		
37	Terminal box entries; no, dimens.			
38	Number of power terminals			
39	Direction of rotation	CW or CCW		
40	Total weight of motor	291	kg	
41	Dimension drawing no.			
42				
43				
44				
45				
Ex-motors				
46				
47				
48				
Option Variant Codes / Definition				
49				
50				
51				
52				
Remarks:				
Data based on situation 9/11/2015				
All data subject to tolerances in accordance with IEC				
Guaranteed values on request				

ABB Motors and Generators Load Curves			
Project		Location	
Department/Author	Customer name	Customer ref.	Item name 1.00001
Our ref.	Rev/Changed by A	Date of issue 2/1/2016	Saving ident untitled.xls Pages 2(3)
Product	TEFC, 3-phase, squirrel cage induction motor		
Type/Frame	M3BP 200MLA 4	Calc. ref.	3GZF021020-202
Product code	3GBP 202 410-ADG		
Rated output P _N	30	kW	
Type of duty	S1(IEC) 100%		
Voltage (V)	415	Current I _N (A)	53.7
Frequency (Hz)	50	Speed (r/min)	1482
		Power factor at P _N	0.83
		Efficiency (%) at P _N	93.4
Load characteristics (IEC 60034-2-1:2007) Data based on situation 9/11/2015 All data subject to tolerances in accordance with IEC			

ABB Motors and Generators Starting Curves			
		Project	Location
Department/Author	Customer name	Customer ref.	Item name 1.00001
Our ref.	Rev/Changed b	Date of issue	Saving ident untitled.xls
	A	2/1/2016	Pages 3(3)
Type of product	TEFC, 3-phase, squirrel cage induction motor		
Type/Frame	M3BP 200MLA 4	Calc. ref.	3GZF021020-202
Product code	3GBP 202 410-ADG	Frequency (Hz)	50
Rated output P _N	30 kW	Rated current I _N	53.7 A
Type of duty	S1(IEC) 100%		
J _{motor} (kgm ²)	0.31	Voltage (V) 100%	415
J _{load} (kgm ²)		T _{start} /T _N	3
Speed (r/min)	1482	Starting time (s)	
T _N (Nm)	193	Speed (r/min)	
T _{load} (Nm)		I _s /I _n	7.9
Nbr. of Consecutive Starts at UN		T _{max} /T _n	3.3
Load characteristics (IEC 60034-2-1:2007) Data based on situation 9/11/2015 All data subject to tolerances in accordance with IEC			

ABB Motors and Generators		Technical Data Sheet - DOL		
Project		Location		
Department/Author	Customer name	Customer ref.		Item name 1.00001
Our ref.	Rev/Changed by A	Date of issue 2/1/2016	Saving ident untitled.xls	Pages 1(3)
No.	Definition	Data	Unit	Remarks
1	Product	TEFC, 3-phase, squirrel cage induction motor		
2	Product code	MM20304-PPN (3GBP202410-A) Calc. ref. 3GZF021020-202		
3	Type/Frame	M3BP 200MLA 4		
4	Mounting	IM1001, B3(foot)		
5	Rated output P_N	30	kW	
6	Service factor	1		
7	Type of duty	S1(IEC) 100%		
8	Rated voltage U_N	690	VY	± 5 % (IEC 60034-1)
9	Rated frequency f_N	50	Hz	± 2 % (IEC 60034-1)
10	Rated speed n_N	1480	r/min	
11	Rated current I_N	32	A	
12	No-load current	10.6	A	
13	Starting current I_s/I_N	7.4		Fullfilled IEC 60034-12 design N,H
14	Nominal torque T_N	194	Nm	
15	Locked rotor torque T_s/T_N	2.8		
16	Maximum torque T_{max}/T_N	3		
17	Minimum torque T_{min}/T_N	2		
18	Speed at minimum torque	1050	r/min	
Load characteristics (IEC 60034-2-1:2007)		Load %	Current A	Efficiency %
19	PLL determined from residual loss	100	32	93.2 / IE2
20		75	24.9	94
21		50	18.5	93.7
22		Start	237	0.47
23	Maximum starting time from hot	15	s	
24	Maximum starting time from cold	27	s	
25	Insulation class / Temperature class	F / B		
26	Ambient temperature	40	°C	
27	Altitude	1000	m.a.s.l.	
28	Enclosure	IP55		
29	Cooling system	IC411 self ventilated		
30	Bearing DE/NDE	6312/C3 - 6210/C3		
31	Type of Grease			
32	Sound pressure level (LP dB(A) 1m)	63	dB(A)	at load
33	Moment of inertia $J = \frac{1}{4} GD^2$	0.309	kg-m2	
34	Balancing			
35	Vibration class			
36	Position of terminal box	Top		
37	Terminal box entries; no, dimens.			
38	Number of power terminals			
39	Direction of rotation	CW or CCW		
40	Total weight of motor	291	kg	
41	Dimension drawing no.			
42				
43				
44				
45				
Ex-motors				
46				
47				
48				
Option Variant Codes / Definition				
49				
50				
51				
52				
Remarks:				
Data based on situation 9/11/2015				
All data subject to tolerances in accordance with IEC				
Guaranteed values on request				

ABB Motors and Generators Load Curves			
Project _____ Location _____			
Department/Author _____	Customer name _____	Customer ref. _____	Item name 1.00001
Our ref. _____	Rev/Changed by A _____	Date of issue 2/1/2016	Saving ident untitled.xls Pages 2(3)
Product	TEFC, 3-phase, squirrel cage induction motor		
Type/Frame	M3BP 200MLA 4	Calc. ref.	3GZF021020-202
Product code	3GBP 202 410-ADG		
Rated output P _N	30	kW	
Type of duty	S1(IEC) 100%		
Voltage (V)	690	Current I _N (A)	32
Frequency (Hz)	50	Speed (r/min)	1480
		Power factor at P _N	0.84
		Efficiency (%) at P _N	93.2
Load characteristics (IEC 60034-2-1:2007) Data based on situation 9/11/2015 All data subject to tolerances in accordance with IEC			

ABB Motors and Generators Starting Curves			
Project		Location	
Department/Author	Customer name	Customer ref.	Item name 1.00001
Our ref.	Rev/Changed b Date of issue A 2/1/2016	Saving ident untitled.xls	Pages 3(3)
Type of product	TEFC, 3-phase, squirrel cage induction motor		
Type/Frame	M3BP 200MLA 4	Calc. ref.	3GZF021020-202
Product code	3GBP 202 410-ADG	Frequency (Hz)	50
Rated output P _N	30 kW	Rated current I _N	32 A
Type of duty	S1(IEC) 100%		
J _{motor} (kgm ²)	0.31	Voltage (V) 100%	690
J _{load} (kgm ²)		T _{start} /T _N	2.8
Speed (r/min)	1480	Starting time (s)	
T _N (Nm)	194	Speed (r/min)	
T _{load} (Nm)		I _s /I _n	7.4
Nbr. of Consecutive Starts at UN		T _{max} /T _n	3
Load characteristics (IEC 60034-2-1:2007) Data based on situation 9/11/2015 All data subject to tolerances in accordance with IEC			

ABB Motors and Generators		Technical Data Sheet - DOL		
Project		Location		
Department/Author	Customer name	Customer ref.		Item name 1.00001
Our ref.	Rev/Changed by A	Date of issue 2/1/2016	Saving ident untitled.xls	Pages 1(3)

No.	Definition	Data	Unit	Remarks	
1	Product	TEFC, 3-phase, squirrel cage induction motor			
2	Product code	MM20304-PPN (3GBP202410-A) Calc. ref. 3GZF021020-202			
3	Type/Frame	M3BP 200MLA 4			
4	Mounting	IM1001, B3(foot)			
5	Rated output P _N	30	kW		
6	Service factor	1			
7	Type of duty	S1(IEC) 100%			
8	Rated voltage U _N	460	VD	± 5 % (IEC 60034-1)	
9	Rated frequency f _N	60	Hz	± 2 % (IEC 60034-1)	
10	Rated speed n _N	1783	r/min		
11	Rated current I _N	48.2	A		
12	No-load current	17	A		
13	Starting current I _s /I _N	8.4		Fullfilled IEC 60034-12 design N,H	
14	Nominal torque T _N	161	Nm		
15	Locked rotor torque T _s /T _N	3			
16	Maximum torque T _{max} /T _N	3.3			
17	Minimum torque T _{min} /T _N	2.4			
18	Speed at minimum torque	1260	r/min		
Load characteristics (IEC 60034-2-1:2007)		Load %	Current A	Efficiency %	
19	PLL determined from residual loss	100	48.2	93.8 / IE2	
20		75	37.9	94	
21		50	28.7	93.1	
22		Start	405	0.44	
23	Maximum starting time from hot	15	s		
24	Maximum starting time from cold	27	s		
25	Insulation class / Temperature class	F / B			
26	Ambient temperature	40	°C		
27	Altitude	1000	m.a.s.l.		
28	Enclosure	IP55			
29	Cooling system	IC411 self ventilated			
30	Bearing DE/NDE	6312/C3 - 6210/C3			
31	Type of Grease				
32	Sound pressure level (LP dB(A) 1m)	71	dB(A)	at load	
33	Moment of inertia J = ¼ GD2	0.309	kg-m2		
34	Balancing				
35	Vibration class				
36	Position of terminal box	Top			
37	Terminal box entries; no, dimens.				
38	Number of power terminals				
39	Direction of rotation	CW or CCW			
40	Total weight of motor	291	kg		
41	Dimension drawing no.				
42					
43					
44					
45					
Ex-motors					
46					
47					
48					
Option Variant Codes / Definition					
49					
50					
51					
52					
Remarks:					
Data based on situation 9/11/2015					
All data subject to tolerances in accordance with IEC					
Guaranteed values on request					

ABB Motors and Generators Load Curves			
Department/Author	Customer name	Customer ref.	Item name 1.00001
Our ref.	Rev/Changed by A	Date of issue 2/1/2016	Saving ident untitled.xls Pages 2(3)
Product	TEFC, 3-phase, squirrel cage induction motor		
Type/Frame	M3BP 200MLA 4	Calc. ref.	3GZF021020-202
Product code	3GBP 202 410-ADG		
Rated output P _N	30	kW	
Type of duty	S1(IEC) 100%		
Voltage (V)	460	Current I _N (A)	48.2
Frequency (Hz)	60	Speed (r/min)	1783
		Power factor at P _N	0.83
		Efficiency (%) at P _N	93.8
Load characteristics (IEC 60034-2-1:2007) Data based on situation 9/11/2015 All data subject to tolerances in accordance with IEC			

ABB Motors and Generators Starting Curves			
Project		Location	
Department/Author	Customer name	Customer ref.	Item name 1.00001
Our ref.	Rev/Changed b Date of issue A 2/1/2016	Saving ident untitled.xls	Pages 3(3)
Type of product	TEFC, 3-phase, squirrel cage induction motor		
Type/Frame	M3BP 200MLA 4	Calc. ref.	3GZF021020-202
Product code	3GBP 202 410-ADG	Frequency (Hz)	60
Rated output P _N	30 kW	Rated current I _N	48.2 A
Type of duty	S1(IEC) 100%		
J _{motor} (kgm ²)	0.31	Voltage (V) 100%	460
J _{load} (kgm ²)		T _{start} /T _N	3
Speed (r/min)	1783	Starting time (s)	
T _N (Nm)	161	Speed (r/min)	
T _{load} (Nm)		I _s /I _N	8.4
Nbr. of Consecutive Starts at UN		T _{max} /T _N	3.3
Load characteristics (IEC 60034-2-1:2007) Data based on situation 9/11/2015 All data subject to tolerances in accordance with IEC			